

## 120GB, 240GB SxS PRO X Series Memory Card



### Overview

**Ultra Fast Transfer Speed up to 10Gps(1250MB/s)\***

**Stable 4K video capture of high bit rate**

**Proven Reliability for Professionals**

**Memory Media Utility**

**Robustness and durability\***

**Compatible Devices**





## PMW-F55LIVE

Super 35 mm 4K CMOS sensor compact CineAlta camera records HD/2K/4K on SxS memory plus 16-bit RAW 2K/4K output



## PXW-Z450

4K HDR 2/3-type CMOS sensor shoulder camcorder with advanced network features, low power consumption and optimised weight balance



## SBAC-T40

SxS memory card Thunderbolt 3 reader/writer



## PMW-F5

Super 35 mm 4K CMOS sensor compact CineAlta camera records HD/2K on SxS memory plus 16-bit RAW 2K/4K output



## VENICE

Next generation camera with forward thinking full frame sensor, phenomenal colour science and user-friendly operation.

## Gallery

