

FWD-32W800

32" BRAVIA HD Professional
Display



Overview

The professional display that's designed for business

Present a clear, professional image with the FWD-32W800 BRAVIA Professional Display. It's the superior way to get your message across, with crisp HD-ready picture quality and reliable operation.

For even greater peace of mind there's the added reassurance of our 3 Years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible. You can also choose to extend your support for an additional 2 years.

Features

See finer, clearer detail

BRAVIA features X-Reality™ PRO picture processing that analyses every frame, matching scenes with our special image database to refine picture details and reduce noise.

BRAVIA also brings you images and videos in vividly detailed HDR. It handles a variety of HDR formats, including HDR10 and Hybrid Log-Gamma.

Flexible mounting and installation

BRAVIA Professional Displays offer flexible installation options,

with VESA standard mounting for easy integration into a wide range of environments.

Greater peace of mind

There's the added reassurance of our 3 Years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible. You can also choose to extend your support for an additional 2 years.

Specifications

Display features

| | |
|---------------------------------|---------------|
| Brightness (cd/m ²) | 380 |
| Contrast Ratio | 1200:1 |
| Dynamic contrast ratio | 1200:1 |
| Response time (ms) | 8 |
| Panel type | IPS |
| Backlight dimming type | Frame Dimming |
| Display type | LCD |

Display specifications

Screen Size for
WEB(diagonal, cm,
integer or 1st decimal) 80.0 cm

| | |
|---|-------------------|
| Backlight type | Direct LED |
| Display resolution (H x V, pixels) | 1366x768 |
| Screen Size (inch, measured diagonally) | 32" (31.5") |
| Viewing Angle (Right/Left) | 178(89/89) degree |
| Viewing Angle (Up/Down) | 178(89/89) degree |
| Display Resolution | WXGA |
| Aspect Ratio | 16:09 |

Professional features

| | |
|---|------------|
| HDMI Auto Wake Up | No |
| Compatible with TDM Digital Signage/ TEOS Solutions | No |
| Operating System | Android 10 |
| On-board Storage (GB) | 8GB |

Display system

| | |
|--------------------------------------|-------------------|
| TV System (Digital Terrestrial) | DVB-T/T2 |
| TV System (Digital Cable) | DVB-C |
| TV System (Digital Sat) | DVB-S/S2 |
| Number of Tuners (Terrestrial/Cable) | 1(Digital/Analog) |
| Number of Tuners (Sat) | 1 |

Network features

| | |
|---------------------|--------------------|
| Apple AirPlay | No |
| Wi-Fi Direct | No |
| Wi-Fi Certified | Yes |
| Chromecast built-in | Yes |
| Internet Browser | iWedia(HbbTV only) |
| Wireless LAN | Integrated |

Convenience features

USB playback codecs VP9/H.265/MPEG1/MPEG2/MPEG4/DivX/XviD/Sorenson

HDMI-CEC No

i-Manual Yes

On Screen Clock Yes

Sleep Timer Yes

On/Off Timer Yes

Display Language ALB,MAY,BUL,CAT,DEU,HRV,CZE,DAN,DUT,ENG,EST,FIN,

Control specs

IP Control No

Pro Mode No

Inputs & outputs

1080p(30,50,60Hz), 1080/24p,

| | |
|--|--|
| HDMI Signal | 1080i(50,60Hz), 720p(50,60Hz),576p, 576i, 480p, 480i |
| HDCP | HDCP1.4 |
| AC Power Input | Rear |
| RF (Terrestrial/Cable) Connection Input(s) | 1 (Bottom) |
| IF (Satellite) Input(s) | No |
| Composite Video Input(s) | No |
| HDMI inputs total | 3 (1Side,2bottom) |
| Digital Audio Output(s) | 1 (bottom) |
| Audio Output(s) | No |
| Headphone Output(s) | 1 (Side) |
| Ethernet inputs | 1 (bottom) |
| PCMCIA Slot(s) | 1 (Side) |

Audio specifications

| | |
|--------------------|------------------------------|
| Speaker Position | Down Firing |
| Audio Power Output | 5W + 5W |
| Digital audio out | PCM/Dolby Digital Plus/Dolby |

| | |
|--------------------------------|--|
| (Optical) format | Digital |
| HDMI Audio Return Channel(ARC) | Yes (ARC) |
| HDMI input Audio format | Two channel linear PCM: 32/44.1/48kHz 16/20/24bits, Dolby Audio |
| ARC output format | Dolby Digital, Dolby Digital Plus, PCM |

Video specifications

| | |
|---------------------------------------|--|
| Wide Mode | Automatic,Full,Wide screen,Suprt Zoom,Unscaled,4:3,Movie expand 14:9,Movie expand 16:9 Full,Superzoom,Unscaled |
| 4:3 Default | No |
| Video Processing | No |
| Motion enhancer | No |
| 4K Processor | Bravia Engine |
| HDR (High Dynamic Range) compatiblity | Yes(HDR10, HLG) |
| Panel Refresh Rate (Native Hertz) | 50Hz |

| | |
|---------------------------|-----|
| Dynamic Contrast Enhancer | Yes |
|---------------------------|-----|

Design features

| | |
|-------------|-------|
| Stand Color | Black |
|-------------|-------|

| | |
|--------------|--------------|
| Bezel Design | Narrow Bezel |
|--------------|--------------|

| | |
|------------------|----|
| Cable Management | No |
|------------------|----|

| | |
|-------------|-------|
| Frame color | Black |
|-------------|-------|

| | |
|--------------|------------|
| Stand Design | Slim stand |
|--------------|------------|

| | |
|-------------------------------|-----|
| VESA® Hole Spacing Compatible | Yes |
|-------------------------------|-----|

| | |
|-------------------------|----------------|
| VESA® Hole Pitch(W x H) | 10.0 x 20.0 cm |
|-------------------------|----------------|

Eco & energy saving

| | |
|-----------------------------------|--------------|
| On mode power 1000h SDR(New lot5) | 32 kWh/1000h |
|-----------------------------------|--------------|

| | |
|-----------------------------|-----|
| Peak luminance ratio for EU | 74% |
|-----------------------------|-----|

| | |
|---------------------|-----|
| Mercury content(mg) | 0.0 |
|---------------------|-----|

| | |
|--------------------|------|
| Power Requirements | 50Hz |
|--------------------|------|

(frequency)

| | |
|-------------------------|-----|
| Rated Power Consumption | 60W |
|-------------------------|-----|

| | |
|--------------------------------|--------|
| Power Consumption (in Standby) | 0.50 W |
|--------------------------------|--------|

| | |
|------------------------------|------------------|
| Power Requirements (voltage) | 220 V - 240 V AC |
|------------------------------|------------------|

| | |
|--------------------------------------|---|
| Power consumption(Networked Standby) | 2.00W(Wi-Fi) / 2.00W(LAN) / 1.0W(Bluetooth) |
|--------------------------------------|---|

| | |
|---|-----|
| Power Saving Mode / Back Light Off Mode | Yes |
|---|-----|

Dimensions

| | |
|--------------------------|------------------------------|
| Display Only (W x H x D) | Approx. 73.3 x 44.2 x 7.8 cm |
|--------------------------|------------------------------|

| | |
|--------------------------------|-------------------------------|
| Display with Stand (W x H x D) | Approx. 73.3 x 46.8 x 18.9 cm |
|--------------------------------|-------------------------------|

| | |
|----------------------------|-------------------------------|
| Package Carton (W x H x D) | Approx. 80.1 x 51.6 x 14.2 cm |
|----------------------------|-------------------------------|

Weights (Approx.)

| | |
|--------------|----------------|
| Display Only | Approx. 4.9 Kg |
|--------------|----------------|

| | |
|--------------------|----------------|
| Display with Stand | Approx. 5.0 Kg |
|--------------------|----------------|

| | |
|--------------------------|--------------|
| Package Carton(Gross) | Approx. 7 kg |
|--------------------------|--------------|

Supplied accessories

Voice

| | |
|-------------------|------------|
| Remote Control | RMF-TX520E |
|-------------------|------------|

| | |
|-----------|------|
| Batteries | LR03 |
|-----------|------|

| | |
|-----------------------|----------------------------------|
| AC Power Cord Spec | (C7) (EUROPE2) (2pin) (Straight) |
|-----------------------|----------------------------------|

| | |
|---------------------------|--|
| Operating Instructions | GB,FR,DE,NL,ES,PT,IT,DK,NO,SE,FI,PL,CZ,SK,HU,RO,BG |
|---------------------------|--|

| | |
|--|--|
| Quick Setup Guide / Supplement CUE (GA) | GB,FR,DE,NL,ES,PT,IT,DK,NO,SE,FI,PL,CZ,SK,HU,RO,BG |
|--|--|

| | |
|--------------------|-----------------------------|
| Table Top Stand | Separate(assembly required) |
|--------------------|-----------------------------|

Optional accessories

| | |
|-------------------|--|
| Wallmount Bracket | SU-WL450(Terminal access limitation, refer to SU-WL450 product page) |
|-------------------|--|

PrimeSupport

| | |
|-----------------------|---|
| Included PrimeSupport | 3 Years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible. |
|-----------------------|---|

| | |
|----------------------------------|---|
| Optional PrimeSupport Extensions | Optional 2-year support extension available: PSP.FWD32W800.2X |
|----------------------------------|---|

Gallery



