

HDCU-3100

IP enabled next generation Camera Control Unit



NETWORKED LIVE

Overview

Add IP production capabilities to system cameras

The HDCU-3100 camera control unit adds IP capabilities to our full range of broadcast and studio system cameras, from the flagship 4K HDC-4300 to the HDC-2000/1700 series and HSC fibre system cameras.

Connecting to compatible cameras via optical fibre cable, the compact HDCU-3100 supplies power to the camera, performs signal processing and provides an interface with external equipment.

Combined with the HKCU-SFP30 option board, designed for the SMPTE ST 2110 Professional Media Over Managed IP Network suite of standards, the HDCU-3100 camera control unit supports essential functionalities required for live IP production including tally, intercom and return.

By installing the optional 4K/HDR Processor Board HKCU-UHD30, the HDCU-3100 can output 4K signals when connected with an HDC-Series System Camera. In addition, adding the optional 12G-SDI Interface Kit HKCU-SDI30 allows transfer of 4K signals through a single BNC cable.

*1 For more details on the JT-NM Tested program in March 2020 and test results, please go to https://jt-nm.org/jt-nm_tested.

*2 For more details on the JT-NM Tested program at IBC 2019 and its test results please see http://jt-nm.org/jt-nm_tested.

This product contains pre-installed software and requires the purchase of licence keys to activate some functions.

Features

Compact and versatile

The 1.5 RU-size Camera Control Unit creates a standardised 19-inch rack system that is ideal for space-limited production areas.

IP functionality for live production

The optional HKCU-SFP30 interface kit adds essential functionality required for IP live production such as Tally, Intercom and Return.

Eight built-in SDI outputs

The HDCU-3100 is equipped with eight built-in SDI outputs, including four 3G-SDI outputs. A built-in USB connector slot and support of 12G-SDI will both be available in future updates.

4K output option

By installing an optional 4K/HDR Processor Board HKCU-UHD30, the HDCU-3100 can output 4K signals when connected to an HDC-Series System Camera. In addition the HDCU-3100 with an optional 12G-SDI Interface Kit HKCU-SDI30 can transfer 4K signals through a single BNC cable.

High quality long distance signal transmission

The optical fibre transmission system maintains high picture quality across cable runs of up to 2000 m. Combined with the HKCU-SM30 interface kit, the compact HDCU-3100 can be directly connected on Single Mode Fibre (SMF) for long distance transmission up to 10Km, making it ideal for space-limited operations like OB Trucks.

MENU setting from web browser

The CCU support menu control from web browser. The status monitoring of multiple CCU, setting file import/export and remote firmware update enhance the efficiency and convenience of the operation.

Specifications

General	
Power requirements	100 V to 240 V AC, 50/60 Hz
Current consumption	4.5 A (max.)
Operating temperature	5 °C to 40 °C (41 °F to 104 °F)
Storage temperature	−20 °C to +60 °C (−4 °F to +140 °F)
Weight	Approx. 7.3 kg (16 lb. 1.5 oz.)
Input/output connectors	
CAMERA	Optical fiber connector (x1)
INTERCOM/TALLY/IO PORT	D-sub 50-pin connector (x1) INTERCOM (PROD/ENG), 4 W: 0 dBu, RTS: 0 dBu, CC: −14 dBu PGM, 3 systems, 0 dBu/−20 dBu TALLY (R, G, Y) FLAG
RCP / CNU	8-pin multi-connector (x1)
TRUNK	12-pin (x1)
LAN-COM	8-pin (x1)
NETWORK TRUNK	8-pin (x1)
SDI OUT	SDI OUT 1 to 4 : 3G/HD/SD SDI OUTPUT BNC (x4) 3G-SDI: SMPTE ST424/425 Level-A/B, 0.8 Vp-p, 75 Ω, 2.970 Gbps/2.967 Gbps HD-SDI: SMPTE ST292, 0.8 Vp-p, 75 Ω, 1.485 Gbps/1.4835 Gbps SD-SDI: SMPTE ST259, 0.8 Vp-p, 75 Ω, 270 Mbps

Input/output connectors

SDI I/O	SDI I/O 1 to 4 : 3G/HD/SD SDI I/O BNC (x4) 3G-SDI: SMPTE ST424/425 Level-A/B, 0.8 Vp-p, 75 Ω , 2.970 Gbps/2.967 Gbps HD-SDI: SMPTE ST292, 0.8 Vp-p, 75 Ω , 1.485 Gbps/1.4835 Gbps SD-SDI: SMPTE ST259, 0.8 Vp-p, 75 Ω , 270Mbps
SDI RET	SDI RET 1 to 4 : BNC (x4) 3G-SDI: SMPTE ST424/425, 2.970 Gbps/2.967 Gbps HD-SDI: SMPTE ST292, 1.485 Gbps/1.4835 Gbps SD-SDI: SMPTE ST259, 270 Mbps
REFERENCE IN/OUT	BNC (x2), loop-through output HD: 3-level sync, 0.6 Vp-p, 75 Ω , SD: 2-level sync, 0.3 Vp-p, 75 Ω
PROMPTER 1 PROMPTER 2/VBS-RET	BNC (x2), loop-through output during 1CH mode, terminate internally at 75 Ω during 2CH mode, analog signal, 1.0 Vp-p, 75 Ω
AUDIO OUT	AUDIO OUT CH1, CH2 : XLR 3-pin, male (x2), 0 dBu/-20 dBu/+4 dBu
CHARACTER / AES / EBU	BNC (x1), VBS: 1 Vp-p, 75 Ω , AES/EBU: 0.5 Vp-p, 75 Ω
AC IN	100 V to 240 V AC (x1)

Supplied accessories

Supplied accessories	Number plates (1 set), Before Using this Unit (1), Operating Instructions (CD-ROM) (1)
----------------------	--

Related products



HDC-2000B

3G double-speed multi-format HD studio system camera (black)



HDC-2000W

3G double-speed multi-format HD studio system camera (beige)



HDC-2500

3G double-speed multi-format HD system camera



HDC-2400

3G multi format HD system camera



HDC-1700

Multi format HD portable system camera



BPU-4000

4K base band processor unit



BPU-4500A

4K/HD baseband processor unit for IP network production



MSU-1000

Master setup unit, multi camera remote control panel for HDC / HSC cameras (horizontal type)



RCP-1000

Joystick type of simple Remote Control Panel for HDC/HSC/HXC series cameras.6 units in 19-inch EIA rack.



HZCU-CNFG50

ember+ protocol license for HDCU-5500, 3500, 3170 and 3100 camera control units



HZCU-SNMP50

SNMP Agent license for HDCU-5500, 3500, 3170 and HDCU-3100 camera control unit



HDC-3100

2/3-type 3-CMOS sensor portable system camera for fibre operation



HDC-3500

2/3-type 4K 3-CMOS sensor portable system camera with HD 4x HFR capability



HKCU-SDI30

12G-SDI Interface Kit



HKCU-SM30

Single Mode Fibre Extension Kit



HKCU-UHD30

4K HDR Processor Board Kit



HDVF-EL30

0.7-type Full HD OLED viewfinder with 3.5-type sub-LCD display. Compatible with F65, 4K/HD system cameras, and shoulder-type HD camcorders.



HDVF-EL75

7.4-inch OLED Viewfinder for portable cameras



HDCE-TX30

IP camera extension adaptor for remote live production (transmitter)



RCP-3500

Remote-control panel for HDC/HSC/HXC series cameras



RCP-3501

Remote-control panel for HDC/HSC/HXC series cameras



MSU-3000

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



MSU-3500

Master setup unit, multi camera remote control panel for system cameras (vertical type)



HDC-3200

2/3-type 4K 3-CMOS sensor portable system camera with HD 2x HFR capability



HDC-3500RV

2/3-type 4K 3-CMOS sensor
portable system camera with
pre-installed variable ND
filter and HD 4x HFR
capability

HDC-3500R

2/3-type 4K 3-CMOS sensor
portable system camera with
HD 4x HFR capability

Gallery



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.

Export PDF : October 11 2026