

## SRG-X400

Standard 4K30P IP PTZ Camera with 30x (w/CIZ) zoom and NDI®|HX capability for a wide range of applications



### Overview

#### **Capture every point of view with excellent 4K\* picture quality and efficient IP production workflow**

The versatile SRG-X400 remotely controlled PTZ camera is ideal for a wide range of applications - from classrooms and meeting spaces to houses of worship, lecture halls and medical environments.

The camera's 1/2.5-type Exmor R™ sensor captures up to 4K\* resolution images with excellent sensitivity, very low noise and rich, natural colour reproduction. It's complemented by the integrated high-resolution lens that offers zoom capability up to 40x in Full HD\*\*\* (30x in 4K), with an expansive approx. 70° wide angle coverage to capture every point of view.

High speed movement during preset recall captures the speaker's every movement, while Picture Freeze during transitions ensures your audience isn't disturbed by rapid camera movements. PTZ Motion Sync\*\*\* function allows smooth blending of separate pan, tilt and zoom movements for seamless, professional-looking transition.

Efficient IP-based live production is augmented with support for NDI®|HX allowing flexible configuration with other networked

NDI®-enabled devices.

Images also can be reviewing remotely via a web browser, with support for RTSP (Real Time Streaming Protocol), RTMP\*\*\* (Real Time Messaging Protocol) and SRT\*\*\* (Secure Reliable Transport) ensuring smooth, stable streaming of video plus audio (from an optional microphone, available separately) over an IP network.

Installation and set-up is easy, with a new Picture Setting File\*\*\*\* allowing the same settings to be applied to multiple cameras through a web interface from a laptop or PC.

\* NDI® is a registered trademark of Vizrt NDI AB

\*\* With Clear Image Zoom and Tele Convert Mode

\*\*\* Requires firmware V3.00

\*\*\*\* Requires firmware V2.00

Note 1: This product contains pre-installed software and requires the purchase of licence keys to activate some functions.

Note 2: When using RM-IP500 firmware should be updated to V2.10 and for RM-IP10, firmware should be updated to V2.17.

## Features

### **Excellent images, even in low light**

The sensitive 1/2.5-type Exmor R™ sensor captures high-quality images with very low noise, even in dimly-lit environments.

### **4K upgrade option**

Upgrade to 4K shooting via optional license.

### **Up to 40x zoom**

Powerful zoom up to 40x\* (in Full HD) allows finely detailed frame-filling close-ups. Responsive autofocus ensures that

images stay clear and sharp, even at high zoom settings.

\* With Clear Image Zoom

### **Wide viewing angle**

Cover the whole scene in meetings and lecture theatres with a horizontal viewing angle of approx. 70°.

### **Ideal for lecture capture**

Use the camera in conjunction with the AI-based REA-C1000 Edge Analytics Appliance to smoothly track the speaker's movements and automatically generate a cut-out image of speaker.

### **High speed movement and Picture Freeze Preset**

Accurately capture the presenter's movements with maximum 300°/s pan and tilt movement during preset recall. Picture Freeze Preset maintains a steady image while the camera moves to a new preset position – with no uncomfortable transitions for your audience.

### **Smooth pan-tilt-zoom**

PTZ Motion Sync function\* allows smooth blending of separate pan, tilt and zoom movements for seamless, professional-looking transitions.

\* Requires firmware V2.00.

### **Simpler installation, lower costs**

A single network cable carries camera power, video output and control signals to simplify installation and reduce cabling costs.

### **Support for NDI®\*|HX**

NDI®|HX compatibility enables cost-effective school studio system integration, allowing flexible configuration with other networked NDI®-enabled devices.

\* NDI® is a registered trademark of Vizrt NDI AB

## Flexible and efficient IP-based production

In addition to RTSP, RTMP(S)\* and SRT\* (Secure Reliable Transport) are supported. Video can be streamed directly from camera to online streaming service, also can be transmitted more securely, with lower latency and more stably even in unstable network environment.

\* Requires firmware V3.00.

## Fast, fuss-free set-up

The new Picture Setting File\* function can apply the same camera settings among multiple cameras for fast set-up.

\* Requires firmware V2.00.

## Specifications

Camera	
Image Sensor	1/2.5 Exmor R CMOS
Image Sensor (Number of Effective Pixels)	Approx. 8.5M pixels
Signal System	2160 <sup>*1</sup> / 29.97p, 25p, 23.98p 1080/59.94p, 50p, 29.97p, 25p, 23.98p 1080/59.94i, 50i 720/59.94p, 50p
4K Capability	Yes (requires 4K optional license)
Minimum Illumination	1.6 lux (1/30s 50IRE F2 high-

(50IRE)	sensitivity OFF)
Horizontal Resolution	1700 TV lines (Center) (4K <sup>*1</sup> ) 1000 TV lines or higher (Center) (FHD)
Gain	Auto/Manual (0 to +48 dB) (High Sensitivity On)
Shutter Speed	1/1 to 1/10000 sec (59.94 Hz system) 1/1 to 1/10000 sec (23.98 Hz system) 1/1 to 1/10000 sec (50 Hz system)
Exposure Control	Auto, Manual, Priority AE (Shutter, Iris)
White Balance	Auto1, Auto2, One Push WB, Indoor, Outdoor, Manual
Zoom capability	30x (4K <sup>*1</sup> with CIZ**), 40x (HD with CIZ) **CIZ = Clear Image Zoom
Focusing System	Auto/Manual
Horizontal Viewing Angle	Approx. 70° (Wide)
Focal Length	f=4.4 mm (Wide) to 88.0 mm (Tele) F2.0 to F3.8

Minimum Object Distance	80 mm (Wide)~ 800 mm (Tele)
Pan/Tilt Angle	Pan: $\pm 170^\circ$ Tilt: $+90^\circ/-20^\circ$
Pan/Tilt Speed (Max.)	Pan: $300^\circ/s$ Tilt: $126^\circ/s$
Pan/Tilt Speed	Pan: $1.1^\circ$ to $101^\circ/s$ Tilt: $1.1^\circ$ to $91^\circ/s$
Pan/Tilt Speed (Slow)	Pan: $0.5^\circ$ to $60^\circ/s$ Tilt: $0.5^\circ$ to $60^\circ/s$
Pan/Tilt Slow Mode	Yes
Pan/Tilt Operation Noise	NC30 or less* * Sony measurement conditions
Preset Position	256 (CGI) 100 (VISCA)
Picture Freeze Preset	Yes
PTZ Motion Sync	Yes

## Network

IP Video Resolution	$3840 \times 2160$ <sup>*1</sup> , $1920 \times 1080$ , $1280 \times 720$ , $720 \times 576$ , $720 \times 480$ , $640 \times 360$
---------------------	---

Compression Format	H.264: High, Main, Baseline Profile H.265: Main Profile
Maximum Frame Rate	H.264: 60 fps H.265: 60 fps
Bitrate Compression Mode	CBR/VBR (selectable)
Range of Bitrate Setting	512 Kbps ~50 Mbps
Multi Streaming Capability	3
Maximum Number of Clients	5
Protocols	IPv4, IPv6, TCP, UDP, ARP, ICMP, IGMP, HTTP, HTTPS, DHCP, DNS, RTP/RTCP, RTSP, UPnP, VISCA over IP
NDI® HX Capability	Yes (requires a license sold separately)

## Camera Features

Auto ICR (Auto mode of IR Cut filter Removal)	Yes
--	-----

Day/Night	Yes
Visibility Enhancer	Yes
Image Stabilization	Yes
Image Flip	Yes
Picture Setting File	Yes
Flicker Cancel	On/Off
Hide OSD Menu	On/Off
Standby Mode	Yes
Remote Standby	Yes

## Web UI

Ver Up	Yes
--------	-----

## Audio

Channel	2ch
Audio Codec	AAC LC 128 kbps/ST (IP) AAC LC 256 kbps/ST (IP)
	Auto Level Control (ALC): On/Off Equalizer: Off, Low cut, Voice enhancement



Setting Option	Input selection: Microphone/Line Mic volume: -10~+10 (21 steps) Audio codec
----------------	---

Embedded Audio in Baseband Video	Yes (3G-SDI, HDMI)
----------------------------------	--------------------

Embedded Audio in IP Streaming	Yes
--------------------------------	-----

## Interface

4K Video Output	HDMI x1 and IP (streaming) x1 <sup>*1</sup>
-----------------	---

HD Video Output	3G-SDI x1, HDMI x1, IP (streaming) x1
-----------------	---------------------------------------

Remote Video Format Switching	Yes
-------------------------------	-----

HDMI Color Space	YCbCr, 4:2:2 8 bit RGB, 4:4:4 8 bit
------------------	--

Camera Control Interface	VISCA RS-422 RJ45 (In/Out) VISCA over IP RJ-45
--------------------------	---

IR Remote Control	Yes
-------------------	-----

Microphone Input	Mini-phone (φ3.5mm) x2 (Mic/Line Selectable)
------------------	--

Sync. System	INT
Power Connector Type	IEC60130-10 (JEITA standard RC-5320A) TYPE4
<h2>General</h2>	
Power Requirements	DC 12V (DC 10.8 to 13.2V), PoE+ (IEEE802.3at compliant)
Power Consumption	25.5 W Max.
Operating Temperature	0 °C to 40 °C 32 °F to 104 °F
Storage Temperature	-20 °C to +60 °C -4 °F to +140 °F
Dimensions (W x H x D)	158.4 x 177.5 x 200.2 mm 6 1/4 x 7 x 8 inch
Mass *2	Approx. 1.8 kg 3 lb 15.5 oz
Camera Body Color	White/Black
Size of Screw Hole for Tripod	1/4-20UNC x1
Mountable Angle	< ±15°
Ceiling Mount	Yes

Supplied Accessories	AC power adaptor (1)
	IR Remote Commander Unit (1)
	Ceiling bracket (2)
	Wire rope (1)
	Screw M3 x 8 (9)
	Screw M2.6 x6 BLACK (1)
	HDMI cable fixing plate (1)
	Safety regulation (1)
	Download site information (1)
	Warranty (1)

## Notes

\*1 Available after an upgrade via a 4K optional license

\*2 The values for dimensions and mass are approximate

## Related products



**RM-IP500**  
PTZ Camera Remote Controller



**RM-IP10**  
IP remote control panel for BRC cameras



**REA-C1000**  
**Edge Analytics Appliance**  
Edge Analytics Appliance



**MCX-500**  
Multi-Camera Live Producer



## SRG-XP1

Compact 4K60P IP  
POV Remote Camera  
with and 101° wide  
viewing angle lens



## SRG-XB25

Compact 4K60P IP  
BOX-style Remote  
Camera with 25x  
optical zoom



## SRGL-4K

4K license for SRG-  
X400/SRG-X120



## NUCLeUS

The smart digital  
imaging platform for  
medical environments

## Gallery

