

## VPL-EW578

4,300 lumens WXGA high brightness compact projector with HDBaseT™



### Overview

#### **Present clear, bright images, with flexible connectivity and low running costs**

The VPL-EW578 projector is ideal for mid-sized classrooms and meeting rooms.

Quiet, compact and powerful, it delivers detail-packed WXGA images with 4,300 lumens colour light output and high 20,000:1 contrast ratio that can be seen clearly even in bright rooms and with larger projection screens, with Sony's 3LCD technology assuring natural, vivid colours.

Image quality is further improved compared with previous models, with a new colour/white balance setting for crisp reproduction of on-screen text and a new 'Vivid' picture mode ensuring even richer, more vibrant colours

The VPL-EW578 is an ideal partner for today's integrated AV/IT environments, expanding your connectivity options with HDBaseT support, dual HDMI ports and Direct USB Display connection. A convenient input label function makes life simpler, confirming on screen the name of connected devices.

Add the VPL-EW578 to a network and see presentations from up to four connected PC/Mac computers simultaneously. Slip in an

optional Wi-Fi dongle and present directly wirelessly from laptops.

A range of energy-saving features plus up to 10,000 hours recommended lamp replacement time contribute to low ownership costs. Routine maintenance is quick and easy with a convenient rear lamp access feature.

## Features

### **Bright, clear images with maximum 4,300 lumens colour light output**

With a 4,300 lumen maximum light output (in high mode), the VPL-EW578 delivers crisp, high-contrast presentations that can be seen clearly in bright rooms or on larger screens. There's a choice of three brightness modes to suit any environment, from bright daylight to darkened rooms.

### **3LCD BrightEra™ technology**

The efficient 3LCD panel system is enhanced by advanced BrightEra™ technology for impressively bright, consistent, high resolution images with excellent colour accuracy and impressive reliability.

### **WXGA resolution**

WXGA (1280 x 800) 16:10 display resolution gives plenty of crisp detail: ideal for making presentations direct from a laptop, mobile device or DVD player.

### **Powerful 16W audio**

The powerful built-in 16W speaker (mono) lets your audience hear video soundtracks with no need for additional amplification.

### **Energy efficient with long-lasting lamp life up to 10,000 hours**

High-performance lamp technology offers reduced ownership

costs plus reduced maintenance, with a recommended lamp replacement time of approx. 10,000 hours (with brightness in low mode - may vary depending on environment or how the projector is used).

## **Advanced energy-saving features**

Advanced lamp technology enables a range of energy-saving features. Auto Light Dimming mode saves energy when the projector is left on without being used. Auto Picture Mode automatically adjusts light output to suit the projected scene. Touching a button on the remote mutes the picture temporarily, dramatically reducing power consumption.

## **Quiet operation**

Near-silent projector fan ensures discreet, unobtrusive operation in classrooms and meeting rooms.

Lamp Mode : High 35 dB / Standard 33db / Low 28dB

## **Auto power on**

Save time and start presenting faster: the projector automatically turns on when signals are detected from a connected PC.

## **Quick go**

Don't waste time when you're in a hurry to leave the room: turn off the projector and unplug immediately, with no lengthy waiting for cool-down.

## **Networked and wireless presentations**

Project presentations from PC or Mac via network and wireless. Up to four users can project PC/Mac images simultaneously, while up to eight users can connect to one projector. The Projector Station for Network Presentation application for Windows/Mac is included.

## **Control and management from any networked PC**

Projector functions and status can be managed and monitored remotely from any networked PC, using the included Projector

Station for Network Control application.

### **Remote Control app for iOS/Android**

Download the free Projector Remote app and control the projector from anywhere in the room with your handheld device, with simple easy-to-read buttons on your phone or tablet screen.

### **USB media viewer**

Slip in a USB drive and display photos, images and graphics with no PC needed.

### **Supports HDBaseT**

Simpler, more cost-effective installation and connectivity over long distances with digital transmission of HD video, audio, power and networking/control signals over a single Ethernet cable.

### **Dual HDMI inputs**

Two HDMI input terminals make it easy to connect HDMI-equipped devices like PCs and media streaming devices.

### **IP control sync for easy system expansion**

Control signals (power on/off, input select) from a master projector can be distributed over an IP network to additional 'sub' projectors.

### **USB Display function for easy one-cable PC connection**

Present pictures and audio\* from a connected PC or Mac with a single USB cable - you don't even need to install a software driver.

\* There may be a time lag between video and audio. For low-latency applications it is recommended to use projector's line-in or HDMI-in connection.

### **Customised input naming labels**

Define your own input labels like 'BD Player', 'PC' and 'Document'

Camera', making it easier to see on screen what devices are connected and being used.

### Easy maintenance

Convenient lamp access at the rear of the projector body makes lamp swaps simpler when the projector is hanging from a ceiling mount.

## Specifications

### Display System

Display System	3 LCD system
----------------	--------------

### Display device

Size of effective display area	0.75”(19mm) x 3 BrightEra LCD Panel Aspect ratio 16:10
--------------------------------	--------------------------------------------------------

Number of pixels	3,072,000 (1280x800 x 3) pixels
------------------	---------------------------------

### Projection lens

Focus	Manual
-------	--------

Zoom Powered/Manual	Manual
------------------------	--------

Zoom - Ratio	Approx. x 1.6
--------------	---------------

Throw Ratio	1.10:1 to 1.79:1
-------------	------------------

## Light source

Type	Ultra high pressure mercury lamp
Wattage	225 W type

## Recommended lamp replacement time \*3

Lamp mode: High	4000 H
Lamp mode: Standard	6000 H
Lamp mode: Low	10000 H

## Filter cleaning / replacement cycle (Max.)

Filter cleaning / replacement cycle (Max.)	10,000 H
--------------------------------------------	----------

## Screen size

Screen size	30" to 300" (0.76 m to 7.62 m) (measured diagonally)
-------------	---------------------------------------------------------

## Light output \*1

Lamp mode: High	4300 lm
Lamp mode: Standard	3200 lm

---

Lamp mode: Low	2400 lm
----------------	---------

---

## Color light output \*1

Lamp mode: High	4300 lm
-----------------	---------

---

Lamp mode: Standard	3200 lm
---------------------	---------

---

Lamp mode: Low	2400 lm
----------------	---------

---

## Contrast ratio (full white / full black) \*2

Contrast ratio (full white / full black) *2	20000:1
---------------------------------------------	---------

---

## Speaker

Speaker	Speaker 16 W (monaural)
---------	-------------------------

---

## Displayable scanning frequency

Horizontal	15 kHz to 92 kHz
------------	------------------

---

Vertical	48 Hz to 92 Hz
----------	----------------

---

## Display resolution

Computer signal input	Maximum display resolution: 1600 x 1200 dots, fV:60Hz
-----------------------	-------------------------------------------------------

---

---

Video signal input	NTSC, PAL, SECAM, 480/60i, 576/50i, 480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i, 1080/60p, 1080/50p
--------------------	----------------------------------------------------------------------------------------------------------------

---

## Colour system

Colour system	NTSC3.58, PAL, SECAM, NTSC4.43, PAL-M, PAL-N, PAL60
---------------	-----------------------------------------------------

---

## Keystone Correction (Max) \*4

Vertical	+/-20 degrees
----------	---------------

---

## OSD languages

OSD languages	27-languages (English, French, German, Italian, Spanish, Portuguese, Japanese, Simplified Chinese, Traditional Chinese, Korean, Russian, Dutch, Norwegian, Swedish, Thai, Arabic, Turkish, Polish, Vietnamese, Farsi, Finnish, Indonesian, Hungary, Greek, Czech, Slovakia, Romania)
---------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

---

## INPUT OUTPUT (Computer/Video/Control)



INPUT A	<p>RGB / Y PB PR input connector: Mini D-sub 15 pin female</p> <p>Audio input connector: Stereo mini jack</p>
INPUT B	<p>RGB input connector: Mini Dsub 15 pin female</p> <p>Audio input connector: Stereo mini jack</p>
INPUT C	<p>HDMI input connector: HDMI 19-pin, HDCP support</p> <p>Audio input connector: HDMI audio support</p>
INPUT D	<p>HDMI input connector: HDMI 19-pin, HDCP support</p> <p>Audio input connector: HDMI audio support</p>
S VIDEO IN	<p>S Video input connector: Mini DIN 4-pin</p>
VIDEO IN	<p>Video input connector: Phono jack</p>
OUTPUT	<p>MONITOR output connector: Mini D-sub 15 pin female</p> <p>Audio output connector: Stereo mini jack</p>
REMOTE	<p>D-sub 9-pin male/RS232C</p>
HDBaseT	<p>RJ-45. 4 Play</p>

LAN	RJ-45, 10BASE-T/100BASE-TX
USB	Type-A
USB	Type-B
MICROPHONE IN	Microphone jack: Mini Jack

## Acoustic Noise \*5

Lamp mode: Low	29dB
----------------	------

## Operating temperature / Operating humidity

Operating temperature / Operating humidity	0°C to 40°C (32°F to 104°F) /20-80% (no condensation)
--------------------------------------------	-------------------------------------------------------

## Storage temperature / Storage humidity

Storage temperature /Storage humidity	-10 °C to +60°C (14°F to +140°F) /20% to 80% (no condensation)
---------------------------------------	----------------------------------------------------------------

## Power requirements

Power requirements	AC 100 V to 240 V, 3.5 A to 1.5 A, 50 Hz / 60 Hz
--------------------	--------------------------------------------------

## Power consumption

AC 100 V to 120 V	Lamp mode: High 344 W
-------------------	-----------------------

AC 220 V to 240 V	Lamp mode: High 328 W
-------------------	-----------------------

## Power Consumption (Standby Mode)

AC 100 V to 120 V	0.50 W (when "Standby mode" is set to "Low")
-------------------	----------------------------------------------

AC 220 V to 240 V	0.50 W (when "Standby mode" is set to "Low")
-------------------	----------------------------------------------

## Power Consumption (Networked Standby Mode)

AC 100 V to 120 V	19.8W (LAN)
	14.3W (optional WLAN module)
	20.8W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")

AC 220 V to 240 V	26.7W (LAN)
	19.1W (optional WLAN module)
	27.6W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")

---

## Standby Mode Networked Standby Mode Activated

Standby Mode	
Networked Standby Mode Activated	Approx. 10 Minutes

---

## Wireless Network(s) On/Off Switch

Wireless Network(s) On/Off Switch	<ol style="list-style-type: none"><li>1) Press the MENU button, then select [Connection/Power]</li><li>2) [WLAN Settings]</li><li>3) [WLAN Connection]</li><li>4) Select On or Off</li></ol>
-----------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

---

## Heat dissipation

AC 100 V to 120 V	1174 BTU/h
AC 220 V to 240 V	1119 BTU/h

---

## Dimensions (W x H x D)

Dimensions (W x H x D) (without protrusions)	Aprox. 365 x 96.2 x 252mm (14 3/8 x 3 25/32 x 9 29/32")
----------------------------------------------	---------------------------------------------------------

---

## Mass

---

Mass	Approx. 4.1kg (9 lb)
------	----------------------

## Supplied accessories

Remote commander	RM-PJ8
------------------	--------

## Wireless LAN Module

Optional Lamp	LMP-E221
---------------	----------

Optional Accessories	IFU-WLM3
----------------------	----------

## Notes

*1	The values are estimate
----	-------------------------

*2	This value is average with lamp dimming.
----	------------------------------------------

*3	The figures are approximate. They vary depending on the environment or how the projector is used.
----	---------------------------------------------------------------------------------------------------

*4	The picture quality may deteriorate when the V Keystone function is used for it is an electrical correction.
----	--------------------------------------------------------------------------------------------------------------

The figures are approximate. They

\*5

vary depending on the environment or how the projector is used.

---

Environmental notice for customers in the USA

Lamp in this product contains mercury. Disposal of these materials may be regulated due to environmental considerations. For disposal or recycling information, please contact your local authorities or see [www.sony.com/mercury](http://www.sony.com/mercury) for additional information.

---

## Gallery

