

PSS-650P

Projector Ceiling Bracket for Installation



Overview

Projector Ceiling Bracket for Installation

Specifications

Adjustable range

	1,000 ~ 1,675 mm / 39 3/8 ~ 65 15/16 inches
Up/down position	650 ~ 975 mm / 25 19/32 ~ 38 3/8 inches (cut)
	1,700 ~ 2,975 mm / 66 15/16 ~ 117 1/8 inches (x 2 units) (25mm pitch adjustment)

Dimensions (W x H x D)

Dimensions (W x H x D)	51 x 695 x 58.5 mm / 2 x 27 3/8 x 2 5/16 inches
------------------------	---

Dimensions (W x H x D) *without protrusions (Adjustment knob)

Dimensions (W x H x D) *without protrusions	51 x 695 x 58.5 mm / 2 x 27 3/8 x 2 5/16 inches
---	---

Gallery

