

## ECM-77BMP

Discrete omni-directional lavalier  
Electret condenser microphone



### Overview

The ECM-77 is used widely in both studio production and on location. Its popularity is based on a combination of excellent sound quality, robust construction and an attractive cosmetic design. This microphone is the ECM-77BMP which is supplied with a 3.5 mm locking jack for use with UWP-D series wireless transmitters.

#### **Hands Free**

As a lavalier microphone, the ECM-77 is an alternative to the traditional hand held microphone and being 'hands free' it allows the presenter to concentrate on her/his performance.

#### **Professional Image**

The ECM-77 is probably the most seen microphone on TV and its compact design creates a professional image.

#### **Easy and Familiar Operation**

The ECM-77 is an essential tool for achieving good quality voice recording. The microphone's capsule is designed for voice pick-up with an extended frequency response and impressive sensitivity. The popularity of the microphone in TV production means that most sound people will be familiar with using the ECM-77.

## Features

### **Designed for high quality voice pick-up**

The ECM-77's capsule features a voice emphasis curve, extended frequency response and sensitivity.

### **Minute size**

The capsule has a diameter of only 5.6mm and is 12.5mm long.

### **Ready for wireless systems**

The ECM-77BMP is compatible with UWP-D wireless transmitters, providing high quality wireless microphone systems for video production.

## Specifications

### Audio Section

Capsule Type	Electret Condenser
Frequency Response	40 Hz to 20 kHz
Directivity	Omni-directional
Sensitivity *[1]	-39.0 dB (11.2 mV)
Output Impedance * [2]	2.5kΩ±30%, Unbalanced
Dynamic Range	90 dB or more
Signal-to-Noise Ratio *[3]	64 dB or more
Inherent Noise *[4]	30 dB SPL or less
Induction Noise From	

External Magnetic Field *[5]	5 dB SPL or less
Wind Noise *[6]	40 dB SPL or less (with windscreen)
Maximum Input Sound Pressure Level *[7]	120 dB SPL

## General Section

Connector	BMP type. Supplied with ø3.5 mm, 3-pole mini plug.
Mic Cable	3.9 feet 1.2 m
Power Requirements	DC 1.1 V to 10.0V
Power Consumption	0.4 mA or less
Dimensions *[8]	ø5.6 X 12.5 mm (Mic head) ø1/4 X 1/2 inches (Mic head)
Mass	Approx. 22.7 g Approx. 0.8 oz
Supplied Accessories	Single/horizontal type tie clip (1) Metal-mesh type windscreen (1)
	Wind screen pack Vertical clip pack

- Optional Accessories
- Safety pin type clip pack
  - Horizontal double-clip pack
  - Horizontal single-clip pack
  - ECM-77 accessory kit
  - Colored wind screen kit
  - Black windscreen for ECM-77

## Notes

- Note
- \*[1] 0 dB = 1 V/Pa, at 1 kHz
  - \*[2] Output impedance at 1 kHz
  - \*[3] A-weighted, 1 kHz, 1 Pa.
  - \*[4] 0dB SPL = 20  $\mu$ Pa
  - \*[5] dB SPL/1E-7 T, 0 dB SPL = 20  $\mu$ Pa
  - \*[6] Wind noise at 2m/s (0 dB SPL = 20  $\mu$ Pa)
  - \*[7] 0 dB SPL = 20  $\mu$ Pa
  - \*[8] The values for dimensions are approximate.

## Related products



### UWP-D11

UWP-D bodypack wireless microphone package



### UWP-D12

UWP-D handheld wireless microphone package



### UWP-D16

UWP-D bodypack and XLR plug-on wireless microphone package

## Gallery

