

MDR-M1

New reference closed monitor headphones for creators with ultra-wideband playback.



Specifications

| General | |
|-------------------------|---|
| Type | Closed dynamic |
| Driver Unit | 40 mm (1.58 in) |
| Power Handling Capacity | 1,500 mW (IEC *1) |
| Impedance | 50 Ω at 1kHz |
| Sensitivity | 102 dB/mW |
| Frequency Response | 5 Hz - 80,000 Hz (JEITA) |
| Mass | Approx. 216 g (without cable) |
| Included Items | Headphones cable (approx. 1.2m/2.5 m, Stereo mini plug); Plug adaptor (Stereo standard plug - Stereo mini plug); Warranty card; Reference Guide |

Notes

*1

IEC International Electrotechnical
Commission

Related products



MDR-MV1

Open back Studio
Monitor Headphones
for creating spatial
and stereo sound
with wide frequency
range and soundstage
feel



MDR-7506

Stereo professional
headphones

Gallery

