

CBK-CE01

50-pin camera interface and digital extender for PMW-400/350/300



Overview

Converts camcorder to a system camera

The optional CBK-CE01 50-pin interface converts the PMW-400 shoulder camcorder to a system camera, with compatibility with CA-TX70 digital triax and CA-FB70 fibre adapters. The 50-pin interface is also used to dock the XDCA-55 to the PMW-350 and PMW-320 camcorders. Thanks to this mechanism, no other connection cables are required.

Digital triax and fibre optional control

Integrates seamlessly with a live production environment as part of a multi-camera shoot.

Features

Digital triax and fibre optional control

The CBK-CE01 allows the PMW-400 camcorder to interface with the CA-TX70 digital triax and CA-FB70 fibre adapters. The camcorder will then integrate seamlessly with a live production environment as part of a multi-camera shoot.

Related products



CA-FB70



CA-TX70

Fibre adapter for HXC-
D70 and PMW-
320/350/400/500
camcorders

Digital triax adapter
for HXC-D70

Gallery

