

## CCFN-50

50 metre optical fibre hybrid cable with opticalCON connector



### Overview

#### **Used with the HXC-D70 multi-transmission studio camera system**

Optical fibre transmission for CA-FB70 and HXCE-FB70. 50m length cable.

#### **Power and optical fibre hybrid cable**

Used with CCFN-JC1 coupler, doubles the distance between the HXC-D70 camera and the recording system.

### Features

#### **Power and optical fibre hybrid cable**

Used with CCFN-JC1 coupler, doubles the distance between the HXC-D70 camera and the recording system.

### Related products



#### **CA-FB70**

Fibre adapter for HXC-D70 and PMW-320/350/400/500 camcorders



#### **CA-TX70**

Digital triax adapter for HXC-D70



#### **HXC-P70**

Affordable, three 2/3-inch Exmor CMOS sensor, full HD/SD compact system camera with direct optical fibre cable connection



#### **HXC-FB80**

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera

## Gallery

