

## ECM-322BMP

Ear-set Electret condenser microphone



### Overview

The ECM-322BMP is an earset microphone, ideal for a variety of multimedia presentation applications ranging from seminars, conferences to lectures and workshops.

### Features

#### **Optimum Sound Pickup**

Incorporating an omni-directional microphone capsule for reduced pop-and-wind noises, the ECM-322BMP earset microphone delivers a high sensitivity of -43 dB (7.1 mV) (\*1) and allows clear voice pickup from any direction. (\*1) 0 dB=1 V/Pa, at 1 kHz

#### **Ear-Clip Style**

Featuring an ear-clip style design, the ECM-322BMP earset microphone can be worn on either the left or right ear.

#### **Adjustable Microphone Position**

The slim and flexible microphone boom allows perfect positioning of the ECM-322BMP microphone.

#### **Secure and Comfortable Fit**

With its soft-texture ear hook, the ECM-322BMP earset microphone is comfortable to wear and fits stably on the ear, even during lengthy presentations.

#### **Compact and Lightweight Design**

The ECM-322BMP has been designed as a compact and ultra-lightweight earset microphone, weighing only 15 g (0.5 oz) (\*2).  
 (\*2) Excluding the cable

## Supplied with a 3-pole mini-jack with a stable lock mechanism

Supplied with 3-pole mini-jack with a stable lock mechanism for use with the UWP series bodypack transmitter.

## Specifications

Audio Section	
Capsule Type	Electret Condenser
Frequency Response	50 Hz to 18 kHz
Directivity	Omni-directional
Sensitivity *[1]	-42 dB (7.91 mV) $\pm$ 3 dB
Output Impedance * [2]	1.4k $\Omega$ $\pm$ 30%, Unbalanced
Dynamic Range	81 dB or more
Signal-to-Noise Ratio *[3]	60 dB or more
Inherent Noise *[4]	34 dB SPL or less
Wind Noise *[5]	55 dB SPL or less
Maximum Input Sound Pressure Level	115 dB SPL

\*[6]

## General Section

Connector	BMP type. Supplied with ø3.5 mm, 3-pole mini plug.
Mic Cable	3.9 feet 1.2 m
Power Requirements	DC 2 V to 10 V
Power Consumption	1.3 mA or less
Dimensions *[7]	ø8.4 x 168 mm (Mic head) ø11/32 x 6 5/8 inches (Mic head)
Mass	Approx. 10 g without connectors Approx. 0.4 oz without connectors
Supplied Accessories	Operating instructions (1) Headband (1) Clip (1) Carrying case (1)

## Notes

\*[1] 0 dB = 1 V/Pa, at 1 kHz

\*[2] Output impedance at 1 kHz

\*[3] A-weighted, 1 kHz, 1 Pa.

\*[4] 0dB SPL = 20? Pa.

Note

\*[5] Wind noise at 2m/s (0 dB SPL = 20 Pa.)

\*[6] 0 dB SPL = 20 Pa.

\*[7] The values for dimensions are approximate.

---

## Related products



### **UWP-D11**

UWP-D bodypack wireless microphone package



### **UWP-D12**

UWP-D handheld wireless microphone package



### **UWP-D16**

UWP-D bodypack and XLR plug-on wireless microphone package

## Gallery

