

## FW-65BZ40H

65" BRAVIA 4K Ultra HD HDR  
Professional Display



### Overview

#### **Present a better image for your business**

Optimised for professional use, the slim, energy-efficient BRAVIA FW-65BZ40H combines bright 4K HDR image quality with easy operation, flexible networking/control and extensive integration options.

Every BRAVIA 4K Professional Display takes full advantage of latest consumer television technologies to ensure vibrant, high-brightness 4K HDR images that add impact to all your content. Beautiful pictures are balanced by Acoustic Multi-Audio™ for clear, immersive sound.

The BRAVIA FW-85BZ40H is designed for dependable 24/7 operation in a wide range of B2B applications. Side-mounted terminals allow easy access for cable connections. The display's elegantly minimal design is enhanced further for professional use with a four-sided aluminium bezel and full protective rear.

Pro mode allows quick and easy customisation to suit different environments including corporate, education and hospitality, while One Step Setting optimises display settings for signage and conference rooms at the touch of a single button. A powerful SoC platform with improved processing speeds allow apps and animation to run smoothly and efficiently alongside a stress-free

user interface for easy operation.

Creating attractive digital signage is simple, mixing and displaying media files and online content with no need for additional hardware. The display's Android platform broadens control and customisation options, while a wide range of API (Application Programming Interface) options enable remote control/monitoring and integration with external systems.

## Features

### **4K image resolution (3840 x 2160 pixels)**

4K offers four times the detail of Full HD, with a resolution of over 8 million pixels bringing extra clarity to corporate display, education and digital signage applications.

### **Very high brightness and contrast**

The high brightness, high contrast panel with Full Array local dimming is ideal for presenting 4K HDR (High Dynamic Range) content, revealing subtle detail in bright highlights and areas of dark shadow.

### **See finer detail**

4K X-Reality PRO upscales pictures closer to true 4K quality. Images are sharpened and refined in real time, revealing extra detail from lower-resolution picture sources.

### **Rich, natural colour with TRILUMINOS Display**

TRILUMINOS Display maps colours from a wider palette, faithfully reproducing a world of more vivid, lifelike hues and tones.

### **Smooth, fluid on-screen action**

X-Motion Clarity™ ensures smoother, more natural reproduction of rapidly-moving on-screen images.

### **Quick set-up with Pro Mode**

Customise and store display settings and features, then copy easily to multiple displays via USB flash memory.

## **One Step Setting**

A time-saver in corporate environments, One Step Setting optimises picture and networking settings to suit meeting rooms and signage applications at the touch of a single button.

## **Easily create digital signage**

Integrated support for HTML5 makes it easy to produce compelling digital signage. Combine graphics, text, video and live web content to create attractive signage in minutes with no extra hardware or special training.

## **Reliable 24/7 operation**

BRAVIA is engineered for dependable round-the-clock operation in the most demanding corporate and AV presentation environments.

## **Cast content with Apple AirPlay2**

With Apple AirPlay2 it's easy to stream video and sound to BRAVIA right from an iPhone, iPad or Mac.

## **Google Chromecast built in**

Cast videos and apps from a mobile device directly to BRAVIA with Google Chromecast. Just tap the Cast button on your Android or iOS device screen and instantly enjoy super-sized on BRAVIA.

## **Versatile remote control**

Control BRAVIA remotely – including on/off, input signal select and adjust volume – over IP via RJ45 by web API or via RS-232C.

## **Connectivity when you need it most**

The FW-65BZ40H supports Wi-Fi 5GHz and 2.4GHz as well as Bluetooth 4.2.

## **Flexible mounting and installation**

The display offers flexible mounting options (vertical, tilt, and table-top), with VESA-standard mounting for easy integration into

a wide range of environments.

## Specifications

### Display Features

Dimming Type	Local Dimming
Display Device	LCD
Backlight Type	Direct (Full Array LED)
Brightness (cd/m <sup>2</sup> ) (*1)	620 (Peak Brightness: 850 *1)
Contrast Ratio (*1)	6000:1
Dynamic Contrast Ratio	550000:1
Response Time (ms) (*1)	8

### Video Specs

Wide Mode	Auto / Wide Zoom / Normal / Full / Zoom
4:3 Default	Yes
Video Processing	4K X-Reality PRO
Motionflow	X-Motion Clarity, Auto mode

Compatible with HDR	Yes (HDR10, HLG, Dolby Vision)
---------------------	--------------------------------

Video Signal	4096 x 2160p (24,50,60Hz), 3840 x 2160p (24,25,30,50,60Hz), 1080p (30,50,60,100,120Hz), 1080/24p, 1080i (50,60Hz), 720p (30,50,60Hz), 720/24p, 576p, 480p
--------------	---

## Audio Specs

Speaker Position	Side Back + Down Firing
------------------	-------------------------

Audio Power Output	10W + 10W
--------------------	-----------

## Network Specs

Wi-Fi direct	Yes
--------------	-----

Wi-Fi Certified	Yes
-----------------	-----

DLNA	Home Network Client, Home Network Renderer
------	--

Miracast (screen mirroring)	Yes (in Pro mode)
-----------------------------	-------------------

Firmware Update	Yes
-----------------	-----

Wireless LAN	Integrated
--------------	------------

## Convenience Features

USB Play (contents)	MPEG1:MPEG1 / MPEG2PS:MPEG2 / MPEG2TS (HDV,AVCHD):MPEG2,AVC / MP4 (XAVCS):AVC,MPEG4,HEVC / AVI:Xvid,MotionJpeg / ASF (WMV):VC1 / MOV:AVC,MPEG4,MotionJpeg / MKV:Xvid,AVC,MPEG4,VP8.HEVC / WEBM:VP8 / 3GPP:MPEG4,AVC / MP3 / ASF (WMA) / LPCM / WAV / MP4AAC / FLAC / JPEG
On Screen Clock	Yes
Sleep Timer	Yes
On/Off Timer	Yes
Chromecast Built-in	Yes
Apple AirPlay	Yes

## Inputs and Outputs

HDCP	HDCP 2.3 (for HDMI 1 / 2 / 3 / 4)
Composite Video Input(s)	1 (Side)
HDMI™ Connection(s) (Total)	4 (4 Side)

---

Analog Audio Input(s) (Total)	1 (Side)
----------------------------------	----------

---

Digital Audio Output(s)	1 (Side)
-------------------------	----------

---

USB	2 (Side)
-----	----------

---

Ethernet Connection(s)	1 (Side)
---------------------------	----------

---

## Design Features

Bezel Color	Black
-------------	-------

---

Table Top Stand	Separate (assembly required)
-----------------	------------------------------

---

VESA® Hole Spacing Compatible	Yes
----------------------------------	-----

---

VESA® Hole Pitch	300 mm x 300 mm
------------------	-----------------

---

## Eco and Energy Saving

Screen Size (measured diagonally)	65" (64.5")
--------------------------------------	-------------

---

Power Consumption (Rated / Standard)	214W
---	------

---

Power Consumption (in Standby)	0.50W
-----------------------------------	-------

---

Lead content	Yes
Mercury content (mg)	0,0
Power Requirements	AC220-240V Taiwan: AC110V
Power Saving Mode / Back Light Off Mode	Yes
Dynamic Backlight Control	Yes
Light Sensor	Yes
AC Power Input	C8 INLET (REAR)

## Measurements

Display Only (W x H x D) (Approx.)	1450 x 833 x 70 mm
Display with Stand (W x H x D) (Approx.)	1450 x 903 x 338 mm
Package Carton (W x H x D) (Approx.)	1576 x 961 x 186 mm

## Weight

Display Only	22.2 kg
--------------	---------



Display with Stand	23.2 kg
--------------------	---------

Package Carton	31 kg
----------------	-------

## Display Specifications

Viewing angle (Right/Left)	178 (89/89) degree
-------------------------------	--------------------

Viewing angle (Up/Down)	178 (89/89) degree
----------------------------	--------------------

Display Resolution	QFHD
--------------------	------

Aspect Ratio	16:9
--------------	------

OS	Android 9.0 Pie
----	-----------------

## Signage Specs

Easy HTML5 Signage Embedded	Yes
--------------------------------	-----

Multicast / IPTV	Yes
------------------	-----

## Control Specs

RS-232C Control	1 (Side)
-----------------	----------

Pro Mode	Yes
----------	-----

IP Control	Yes
------------	-----

---

HDMI Auto Wake-up	Yes
-------------------	-----

---

## Notes

*1	Typical value of the panel specification
----	--

---

## Further Information

Product

Information Sheet <https://eprel.ec.europa.eu/screen/product/electronic>

---

## Gallery



