

MDR-7520

High quality studio professional headphones



Overview

Precision made for precision work.

As Sony's highest level of professional headphone, the 7520 is designed for critical listening applications. These headphones utilize ultra wideband 50mm HD driver units incorporating liquid crystal polymer film diaphragms. That's why the listener gets high power handling capability with great durability and unparalleled sound quality.

The 7520 employs newly developed noise isolation earpads with a pliable cushion material that conforms to the natural shape of the ear, providing comfort and high acoustic isolation. This model has a lightweight magnesium alloy housing to decrease weight and increase comfort, reduce fatigue, and help prevent unnecessary vibration, plus a detachable cable.

Features

50mm Driver Unit with LCP Diaphragm

Closed-Ear Design

Wide Frequency Response

High Power Handling Capacity 4,000mW

Stereo Unimatch Plug

Gold Connectors and OFC Cord

Supplied Soft Case

Specifications

Group heading

Headphone Type	Dynamic. Closed
----------------	-----------------

Magnet Type	Neodymium
-------------	-----------

Driver Size	50.0mm
-------------	--------

Frequency Response	5-80kHz
--------------------	---------

Impedance	24 Ohms
-----------	---------

Sensitivity	108 dB/mW
-------------	-----------

Power Handling	4,000mW
----------------	---------

Plug Type	Gold, Stereo Unimatch 3.5mm/6.3mm adapter
Cord Length	3m (9.8 ft)
Weight	269g (9.5 oz)

Gallery

