

# BC-U1A

Battery charger/AC adaptor for BP-U90/U60/U60T/U30 Lithium-ion battery



## Overview

### **Charges one BP-U90/U60/U60T/U30 battery**

The BC-U1A battery charger charges one compact BP-U90, BP-U60/U60T, BP-U30 Lithium-ion battery at high speed.

### **Built-in AC adaptor provides 12 V DC power output**

The BC-U1A also has 12 V DC power output cable to power a camcorder directly.

### **Compact design for ease of use**

The BC-U1A has a mass of only 340 g (12 oz) and dimensions (W x H x D) of 128 x 45 x 98 mm (5 1/8 x 1 13/16 x 3 7/8 inches).

NOTE: BC-U1A is compliant with safety standard IEC62368-1.

## Specifications

General	
Power Requirements	AC100V ~ 240V 50/60Hz
Power consumption	46W
DC supply	[36W] 12V / 3.0A
Charging Voltage	16.4V
Dimensions (W x H x D)	128x45x98 (mm)
Mass	340 (g)
Operating Temperature	[DC supply]-5 °C ~ +45°C [Charge] 0°C ~ +45°C
Approximate charge times	
BP-U90	190 minutes
BP-U60	150 minutes
BP-U30	130 minutes
Supplied Accessories	
Supplied Accessories	Instruction manual Warranty Paper

Related products



**PXW-FS7**

4K Super 35mm Exmor CMOS sensor XDCAM camera with  $\alpha$  Mount lens system, 4K/2K RAW and XAVC recording options



**PXW-X200**

Three 1/2-type Exmor™ CMOS Full HD sensor XDCAM camcorder with 17x zoom lens and XAVC recordings



**PXW-FS7M2**

4K Super 35mm Exmor CMOS sensor XDCAM camera with Variable ND Filter, E-Mount (Lever Lock), 4K/2K RAW and XAVC recording



**PXW-X180**

Three 1/3-inch type Exmor™ CMOS Full HD sensor XDCAM camcorder with 25x zoom lens and wireless operations, including XAVC recordings



**PXW-Z280**

World's first 4K Handheld Camcorder with 1/2-type 3CMOS with 4K 50p/60p recording capability, 12G-SDI, Dual Link Cellular capability, 17x zoom lens, advanced Face Detection AF



**PXW-FS5**

Grab and Shoot with handheld Super 35



**PXW-Z190**

4K Handheld Camcorder with all-new 1/3-type 3CMOS with 4K 50p/60p\* recording capability, 25x zoom lens and advanced Face Detection AF



**PXW-X160**

Three 1/3-inch type Exmor™ CMOS Full HD sensor XDCAM camcorder with 25x zoom lens and XAVC recordings



**PMW-300K1**

Three 1/2-inch Exmor™ CMOS sensors semi-shoulder XDCAM camcorder with interchangeable 14x zoom HD lens system recording XAVC HD 100 Mbps and MPEG HD422 at 50 Mbps



**PXW-FS5M2**

'Grab and shoot' Super35 handheld camcorder with stunning new creative look, 4K 120fps HFR and HDR,  $\alpha$  Mount lens system, Variable ND Filter, 4K/2K RAW and XAVC recording



**PMW-300K2**

Three 1/2-inch Exmor™ CMOS sensors semi-shoulder XDCAM camcorder with interchangeable 16x zoom HD lens system recording XAVC HD 100 Mbps and MPEG HD422 at 50 Mbps

## Gallery

