

## BKM-341HS

HD / SD-SDI input adaptor



### Overview

#### **Increases functionality of LMD monitors**

The Sony BKM-341HS is an HD/SD-SDI input adaptor board for the LMD entry-level production and medical monitors.

### Features

#### **HD / SD-SDI input**

The unit has a BNC input connector supporting SD-SDI 270 Mbps 10 bit 4:2:2 component digital video and HD-SDI 1.48 Gbps 10 bit 4:2:2 component digital video.

#### **Low power consumption**

BKM-341HS has a low power consumption of approx. 1.8 W allowing it to be powered from the monitor.

#### **Convenient installation and footprint**

The BKM-341HS can be fixed to the monitor, its short depth making it convenient for all installations and configurations.

### Specifications

#### Input

BNC (x1)

Input impedance: 75 ohms

SDI Input	unbalanced Sampling frequency HD-SDI: Y/Cb/Cr 74.25 MHz/37.125 MHz/37.125 MHz SD-SDI: Y/Cb/Cr:13.5 MHz/6.75 MHz/6.75 MHz Quantization HD-SDI: 10 bits/sample SD-SDI: 10 bits/sample
-----------	---

---

## Output

Option Output	D-sub 9 pin (x1)
---------------	------------------

---

## General

Voltage	+5 V DC (supplied from the main unit)
Power Consumption	Approx. 1.8 W
Operating Temperature	32°F to 95°F (Recommended: 68°F to 86°F) 0°C to 35°C (Recommended: 20°C to 30°C)

---

Operating Humidity	0% to 90% (no condensation)
Storage/Transport Temperature	-4°F to +140°F -20°C to +60°C
Storage/Transport Humidity	0% to 90%
Operating/Storage/Transport Pressure	700 hPa to 1060 hPa
Dimensions (W x H x D) *[1]	47 x 75 x 36 mm 1 7/8 x 3 x 1 1/2 inches
Mass	Approx. 4.2 oz Approx. 120 g
Supplied Accessories	Operating Instructions (1)

## Notes

Note

\*[1] The values for dimensions are approximate.  
[\*1] The DisplayPort input is available from V1.1.

Related products



**LMD-  
1530W**

15-inch entry-level  
LCD monitor

**LMD-  
1510W**

15.6-inch entry-level  
LCD monitor

**LMD-  
2110W**

21.5-inch entry-level  
LCD monitor

**LMD-  
2110MD**

21.5-inch Full HD 2D  
LCD medical monitor

## Gallery

