

## FWD-75X80H/T

75" BRAVIA 4K Ultra HD HDR  
Professional Display

### Overview

#### **High quality 4K HDR images and smart connectivity**

Take your business communications to the next level with the FWD-75X80H/T BRAVIA Professional Display that combines lifelike 4K HDR image quality with easy operation, flexible networking/control and extensive integration options.

Optimised for professional applications, the FWD-75X80H/T BRAVIA Professional Display delivers richly coloured, high-contrast 4K HDR images, while 4K X-Reality PRO upscales lower-resolution images closer to true 4K quality.

The display's clean, minimal design keeps your audience focused on what really matters, while Dolby Atmos delivers pure, immersive sound.

Enrich your audience's display experience with seamless TEOS integration and a choice of built-in solutions to add extra functionality, from meeting room support to automation, with no need for any external devices or players.

With advanced control, Pro Mode, optional interactive compatibility and an embedded HTML5 platform, it makes it easy to create attractive digital signage so you always present a clear image.

For even greater peace of mind there's the added reassurance of our 3 Years warranty with Repair or if necessary advanced

exchange handled by local partner, on premise where possible. You can also choose to extend your support for an additional 2 years.

## Features

### **4K image resolution (3840 x 2160 pixels)**

4K offers four times the detail of Full HD, with a resolution of over 8 million pixels bringing extra clarity to corporate display, education and digital signage applications.

### **More contrast, colour and clarity**

Our 4K HDR Processor X1™ cleans and refines picture signals, using advanced algorithms to cut noise and boost detail. Even lower-resolution images are upscaled closer to 4K with lifelike colour and textures, for a more impactful signage.

### **See finer detail**

4K X-Reality PRO upscales pictures closer to true 4K quality. Images are sharpened and refined in real time, revealing extra detail from lower-resolution picture sources.

### **Wider colour with TRILUMINOS Display**

Powered by our X1 processor, TRILUMINOS Display maps colours from a wider palette, faithfully reproducing a world of more vivid, lifelike hues and tones.

### **Smoother movement**

Motionflow XR inserts additional picture frames between the originals, ensuring smoother, sharper detail in fast-moving sequences.

### **High quality sound that flows around you**

X-Balanced Speaker technology (55" models and above) brings extra clarity to all videos and sound. Dolby Atmos creates an immersive soundstage that comes from above as well as from the sides, letting you hear objects moving overhead with even more realism.

## **Refined style to match your space**

BRAVIA features a slim, contemporary blade design, with a narrow screen bezel that adds an extra touch of refinement to any interior.

## **Do more with Android TV**

Discover a world of apps and online content powered by Android. Use Voice Search to find content easily without typing.

## **Google Chromecast built-in and Apple Airplay**

With Google Chromecast built-in, and Apple Airplay, easily mirror your content and enjoy it on your BRAVIA.

## **Quick set-up with Pro Mode**

Customise and store display settings and features, then copy easily to multiple displays via USB flash memory.

## **Easily create digital signage**

Integrated support for HTML5 makes it easy to produce compelling digital signage. Combine graphics, text, video and live web content to create attractive signage in minutes with no extra hardware or special training.

## **Versatile remote control**

Control BRAVIA remotely – including on/off, input signal select and adjust volume – over IP via RJ45 by web API.

## **TEOS integration**

BRAVIA integrates seamlessly with TEOS, Sony's suite of workspace management applications that orchestrate control of devices and content in boardrooms, meeting areas and public spaces.

## **Greater Peace of Mind**

There's the added reassurance of our 3 Years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible. You can also choose to

extend your support for an additional 2 years.

## Specifications

### Display Features

Brightness (cd/m <sup>2</sup> )	500
Native Contrast Ratio	1400:1
Dynamic Contrast Ratio	450000:1
Response Time (ms)	8
Panel Type	IPS
Dimming Type	Frame Dimming
Display Device	LCD
Bezel Size (Top, Side, Bottom)	15.9 / 15.9 / 20.0
Operation Time	18/7

### Display Specifications

Screen Size for WEB (diagonal, cm, integer or 1st decimal)	189 cm
Backlight Type	Direct LED

Display Resolution (H x V, pixels)	3840 x 2160
------------------------------------	-------------

Screen Size (inch, measured diagonally)	75" (74.5")
---	-------------

Viewing Angle (Right/Left)	178 (89/89) degree
----------------------------	--------------------

Viewing Angle (Up/Down)	178 (89/89) degree
-------------------------	--------------------

Display Resolution	QFHD
--------------------	------

Aspect Ratio	16:09
--------------	-------

## Professional Features

Professional Hidden Mode	Yes
--------------------------	-----

HDMI Auto Wake-Up	Yes
-------------------	-----

Multicast/ IPTV	Yes
-----------------	-----

Compatible with TDM Digital Signage / TEOS Solutions	Yes
--	-----

Operating System	Android 9.0 Pie
------------------	-----------------

On-board Storage (GB)	16GB
-----------------------	------

## Display System

TV System (Digital Terrestrial)	DVB-T/T2
---------------------------------	----------

TV System (Digital Cable)	DVB-C
---------------------------	-------

TV System (Digital Sat)	DVB-S/S2
-------------------------	----------

Number of Tuners (Terrestrial/Cable)	1 (Digital/Analog)
--------------------------------------	--------------------

Number of Tuners (Sat)	1
------------------------	---

## Network Features

Wi-Fi Direct	Yes
--------------	-----

Wi-Fi Certified	Yes
-----------------	-----

Apple AirPlay	Yes
---------------	-----

Chromecast Built-in	Yes
---------------------	-----

Internet Browser	Vewd
------------------	------

Wireless LAN	Integrated
--------------	------------

## Convenience Features

---

USB Playback Codecs	MPEG1:MPEG1 / MPEG2PS:MPEG2 / MPEG2TS (HDV, AVC) LPCM / WAV / MP4AAC / FLAC / JPEG
HDMI-CEC	Yes
i-Manual	Yes
On Screen Clock	Yes
Sleep Timer	Yes
On/Off Timer	Yes
Display Language	AFR,AMH,ARA,ASM,AZE,BEL,BUL,BEN,BOS,CAT,CZE,DAN

---

## Control Specs

IP Control	Yes
Pro Mode	Yes

---

## Inputs & Outputs

4096 x 2160p (24,50,60 Hz), 3840 x

HDMI Signal	2160p (24,25,30,50,60 Hz), 1080p (30,50,60 Hz), 1080/24p, 1080i (50,60 Hz), 720p (30,50,60 Hz), 720/24p, 576p, 480p
HDCP	HDCP2.3 (for HDMI 1/2/3/4)
AC Power Input	C8 INLET (REAR)
RF (Terrestrial/Cable) Connection Input(s)	1 (Side)
IF (Satellite) Input(s)	1 (Side)
Composite Video Input(s)	1 (Side)
HDMI Inputs Total	4 (4 Side)
USB Ports	2 (Side)
Ethernet Inputs	1 (Side)
PCMCIA Slot(s)	1 (Top)

## Audio Specifications

Speaker Position	Down Firing
Audio Power Output	10W + 10W

## Video Specifications



Wide Mode	Auto / Wide zoom / Normal / Full / Zoom / 14:9
4:3 Default	Yes
Video Processing	4K X-Reality PRO
Motion Enhancer	Motionflow XR 400Hz (Native 50Hz)
4K Processor	X1 4K HDR Processor
HDR (High Dynamic Range) Compatibility	Yes (HDR10,HLG,Dolby Vision)
Panel Refresh Rate (Native Hertz)	50Hz

## Design Features

Cable Management	Yes
Frame Colour	Black
Stand Design	Slim Blade Stand
VESA® Hole Spacing Compatible	Yes
VESA® Hole Pitch(W x H)	30.0 x 30.0 cm

## Eco & Energy Saving

Energy Label Rating	B
On-mode Power Consumption	227.0W
Standby Power Consumption	0.50W
Peak Luminance Ratio for EU	69%
Mercury Content (mg)	0.0
Power Saving Mode / Back Light Off Mode	Yes
Power Requirements (voltage)	AC 220-240V
Power Consumption (Networked Standby)	2.00W (Wi-Fi) / 2.00W (LAN) / 1.00W (Bluetooth)

## Dimensions

Display Only (W x H x D)	Approx. 168.6 x 96.9 x 7.2 (1.5) cm
Display with Stand (W x H x D)	Approx. 168.6 x 104.2 x 41.4 cm

## Weights (Approx.)

Display Only	Approx. 31.8 kg
Display with Stand	Approx 32.9 kg
Package Carton (Gross)	Approx. 43 kg

## Optional Accessories

Wallmount Bracket	SU-WL450 (Terminal access limitation, refer to SU-WL450 product page), SU-WL850 (Refer to Country / Area Handling Chart)
-------------------	--

## PrimeSupport

Included PrimeSupport	3 years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible.
Optional PrimeSupport Extensions	Optional 2-year support extension available: PSP.FDWXH8075.2X