

HDLA1507

Large viewfinder adaptor



Overview

Enables a large viewfinder to be used with select portable cameras

A convenient peripheral for portable cameras HDC-1400R, 1450R, 1500R, 1550R.

Allows select cameras to be used with a portable lens and a large CRT viewfinder

Using a newly developed interlocking mechanism, the power, video, and control signals are passed on directly from the portable cameras to the HDLA Series adaptor. This unique mechanism also allows the portable cameras to be attached and detached without removing the large lens. The interlocking mechanism allows for an astonishingly quick and smooth setup.

Features

Allows select cameras to be used with a portable lens and a large CRT viewfinder

Using a newly developed interlocking mechanism, the power, video, and control signals are passed on directly from the portable cameras to the HDLA Series adaptor. This unique mechanism also allows the portable cameras to be attached and detached without removing the large lens. The interlocking mechanism allows for an astonishingly quick and smooth setup.

Related
products



**HDVF-
EL780**

Full HD 7.4-inch OLED
viewfinder

Gallery

