

## SAL70400G2

70–400mm F4–5.6 G SSM II super telephoto zoom lens



### Overview

#### **Sharper image quality meets faster focus**

The 2nd edition of this popular super telephoto zoom now has a Nano AR Coating to reduce flare and even faster autofocus subject tracking – ideal for wildlife shots.

#### **Full frame A-mount**

This 35mm full frame lens works with Sony  $\alpha$  A-Mount cameras, using the LA-EA4 lens adapter for E-Mount cameras.

### Features

#### **See the difference with G Lens**

Renowned for their descriptive power, G Series lenses maintain excellent peripheral light characteristics and maximum contrast even at the edges of the frame.

#### **Smooth defocusing**

Instead of a standard polygon-shaped lens aperture, this lens features a 9-blade circular aperture for more natural, rounded defocusing or 'bokeh'.

#### **Refined optical performance**

Nano AR Coating reduces unwanted reflections to control flare and ghosting. ED (Extra-low Dispersion) glass elements minimise aberration throughout the image.

## **Even faster autofocus**

Faster autofocus subject tracking, internal focusing, and built-in SSM (Super Sonicwave Motor) ensure agile, silent and responsive focusing when you need it most.

## **Say goodbye to blur**

Pair the lens with a camera by Sony featuring built-in SteadyShot™ image stabilisation and you'll enjoy smooth, blur-free results when shooting handheld.

## Gallery

