

SCA-S30



Features

Easy to install

Related products



SNC- VB635

Box-type 1080p/60 fps Camera with Half-inch Exmor™ CMOS Sensor Powered by IPELA ENGINE EX™ - V Series



SNC- VB630

Box-type 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



SNC- VB600

Box-type 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



SNC- VM632R

Outdoor IR Ruggedized 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



SNC- VM602R

Outdoor IR Ruggedized 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



SNC- VM631

Vandal-resistant Minidome 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



SNC- VM630

Minidome 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



SNC- VM601

Vandal-resistant Minidome 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



SNC- VM600

Minidome 720p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series

Gallery

