

VPL-PWZ10

5,000 lm (5,200 lm center) WXGA laser light source projector



Overview

Cost effective laser projection with excellent picture quality, easy installation and low running costs

The VPL-PWZ10 laser projector is a versatile, affordable choice for installation in a wide range of education, business and entertainment environments.

The powerful Z-Phosphor laser light source is teamed with Sony's advanced BrightEra 3LCD projection engine to deliver extremely bright, detail-packed WXGA resolution images with generous 5000 lumens brightness and rich, stable colours. This laser light source allows up to 20,000 hours* of virtually zero maintenance operation without the worry of sudden lamp failures. An automated filter system cuts the hassle of regular dust cleaning. Near-zero maintenance needs are complemented by a range of energy-saving features, significantly driving down total lifetime ownership costs. Constant Bright maintains consistent light output levels throughout the laser's 20,000 hours (at light output mode "Middle") recommended lifespan.

Offering a stylish blend-in design and low fan noise, the VPL-PWZ10 fits smoothly into almost any environment – from academic institutions to corporate environments. Mount the projector at any angle, even on its side or upside down. Set-up's easier than ever with a friendly new installation menu.

*Actual hours may vary depending on usage environment.

Features

Very high image quality with Sony's advanced BrightEra 3LCD projection engine and Z-Phosphor laser light source

The Z-Phosphor laser light source is coupled with Sony's acclaimed BrightEra 3LCD projection engine to ensure high 5000 lumen image brightness with vivid, natural colour reproduction.

Constant Brightness

Constant Bright maintains the same brightness throughout the 20,000 hours (at light output mode "Middle") hours recommended life span.

Advanced picture refinement technologies

Picture quality is boosted by advanced processing featured on Sony's home cinema projectors. Reality Creation uses a powerful pattern-matching database to optimise every pixel. Contrast Enhancer actively analyses and refines dark and light image areas for sparkling highlights and rich, deep blacks.

Crisp, detail-packed WXGA resolution images

See fine detail in PC presentations, videos or multimedia signage with WXGA (1280 x 800) 16:10 resolution.

Up to 20,000 hours* operation with virtually no maintenance

The advanced laser light source offers up to 20,000 hours* operation without lamp exchange, reducing lifetime running costs compared with traditional projectors.
*Actual hours may vary depending on usage environment.

Hassle-free automatic filter cleaning

Focus on great-looking images instead of arduous maintenance tasks: new automated filter cleaning system removes dust every 100 hours.

Energy saving features

Reduce running costs even further with convenient energy-saving features: Picture Mute and Auto Dimming.

Save time with every presentation

Quick power On/Off dramatically cuts warm-up time after switch-on before you can start presenting at full brightness.

360° free-angle installation capability

Enjoy greater installation flexibility: position the projector freely at any angle – or its side or even upside down.

Supports HDBaseT

Simpler, more cost-effective installation and connectivity with digital transmission of HD video, audio and networking/control over a single Ethernet cable.

Quiet operation

Low fan noise ensures discreet, unobtrusive operation in quiet environments for academic and corporate use.

Slim, attractive blend-in design

The slim, stylish case design features a flat top surface that blends in discreetly when the projector is ceiling mounted.

Picture Mode

Picture Mode ensures great-looking pictures in any presentation conditions. Select Standard, Dynamic, or Brightness Priority mode for optimised image quality, with any source and in every room.

Simple set-up with friendly new Installation menu

Easily adjust projector settings with remote commander.

Specifications

Display system

Display system	3 LCD system
----------------	--------------

Display device

Size of effective display area	0.76" (19.3 mm) x 3 BrightEra LCD Panel, Aspect ratio: 16:10
--------------------------------	---

Number of pixels	3,072,000 (1280 x 800 x 3) pixels
------------------	-----------------------------------

Projection lens

Focus	Manual
-------	--------

Zoom - Powered/Manual	Manual
-----------------------	--------

Zoom - Ratio	Approx. x 1.45
--------------	----------------

Projection lens

Throw ratio	1.28:1 to 1.88:1
-------------	------------------

Lens shift - Powered/Manual	Manual
-----------------------------	--------

Lens shift - Range Vertical	+20% to +55%
-----------------------------	--------------

Lens shift - Range Horizontal	+/- 10%
-------------------------------	---------

Light source

Type	Laser diode
------	-------------

Filter cleaning / replacement cycle (Max.)

Filter cleaning / replacement cycle (Max.)	20,000 H (service maintenance)
--	--------------------------------

Screen size

Screen size	40" to 300" (1.02 m to 7.62 m)
-------------	--------------------------------

Light output *1

Mode: Standard	5,000lm *2
----------------	------------

Mode: Standard (Centre)	5,200lm *3
-------------------------	------------

Color light output *1

Mode: Standard	5,000 lm
----------------	----------

Contrast ratio (full white / full black) *1

Contrast ratio (full white / full black)	500,000:1
--	-----------

Speaker

Speaker	16 W (monaural)
---------	-----------------

Displayable scanning frequency

Horizontal	15 kHz to 92 kHz
------------	------------------

Vertical	48 Hz to 92 Hz
----------	----------------

Accepted signal resolution

Computer signal input	Maximum signal resolution: 1920 x 1200 *4
-----------------------	---

Accepted signal resolution

Video signal input	NTSC, PAL, SECAM, 480/60p, 576/50i, 720/60p, 720/50p, 1080/60i, 1080/50i The following items are available for HDMI input only; 1080/60p, 1080/50p, 1080/24p
--------------------	---

Color System

Color System	NTSC3.58, PAL, SECAM, NTSC4.43, PAL-M, PAL-N, PAL60
--------------	---

Keystone correction (Max.)

Horizontal	+/- 30 degrees
Vertical	+/- 20 degrees

INPUT OUTPUT (Computer/Video/Control)

INPUT A	RGB / Y PB PR input connector: Mini D-sub 15 pin (female) Audio input connector: Stereo mini jack
INPUT B	HDMI input connector: HDMI 19-pin, HDCP support Audio input connector: HDMI audio support
INPUT C	HDMI input connector: HDMI 19-pin, HDCP support Audio input connector: HDMI audio support
INPUT D	HDBaseT interface connector: RJ45, 4 play (Video, Audio, LAN, Control)
VIDEO IN	Video input connector: BNC Audio input connector: Shared with INPUT A
OUTPUT	Audio output connector: Stereo mini jack
REMOTE	D-sub 9-pin (male) / RS232C
LAN	RJ45, 100BASE-TX (Shared with INPUT D)
USB	TYPE-A
USB	TYPE-B

Acoustic Noise *1

Lamp Mode: Standard / Middle / Low	36 dB / 28 dB / 25 dB
------------------------------------	-----------------------

Operating temperature / Operating humidity

Operating temperature / Operating humidity	0° to 40°C (32°F to 104°F) / 20 % to 80 % (no condensation)
--	---

Storage temperature / Storage humidity

Storage temperature / Storage humidity	-10° to +60°C (14°F to 140°F) / 20 % to 80 % (no condensation)
---	---

Power requirements

Power requirements	AC 100 V to 240 V, 4.0 A to 1.6 A, 50 Hz / 60 Hz
--------------------	--

Power Consumption

AC 100 V to 120 V	Mode: Standard: 399 W
-------------------	-----------------------

AC 220 V to 240 V	Mode: Standard: 377 W
-------------------	-----------------------

Power Consumption (Standby Mode)

AC 100 V to 120 V	0.5 W (when "Standby mode" is set to "Low")
-------------------	---

AC 220 V to 240 V	0.5 W (when "Standby mode" is set to "Low")
-------------------	---

Power Consumption (Networked Standby Mode)

AC 100 V to 120 V	12.5 W (LAN) 13.2 W (optional WLAN module) 16.8 W (HDBaseT) 17.4 W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")
-------------------	--

AC 220 V to 240 V	11.9W (LAN) 12.6W (optional WLAN module) 17.0W (HDBaseT) 17.6W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")
-------------------	--

Standby Mode / Networked Standby Mode Activated

Standby Mode / Networked Standby Mode Activated	Approx. 2 Minutes
--	-------------------

Heat dissipation

AC 100 V to 120 V	1361 BTU/h
-------------------	------------

AC 220 V to 240 V	1286 BTU/h
-------------------	------------

Dimensions (W x H x D)

Dimensions (W x H x D) (without protrusions)	510 x 113 x 354.6 mm (20 3/32 x 4 7/16 x 13 31/32 inches)
---	--

Mass

Mass Approx. 8.7kg (19 lb)

Supplied accessories

Remote commander RM-PJ8

Notes

*1 The figures are approximate. They vary depending on the environment or how the projector is used.

*2 The value is in accordance with ISO 21118, and may differ depending on the actual unit. Brightness and contrast vary depending on use conditions and environments.

*3 The value is light output measured at center area of screen in Standard mode, and average of all products shipped.

*4 Available for VESA Reduced Blanking signal.

This projector has a total constant brightness of 4500 lumens for up to 14,000 hours depending on usage environment. This enables users to experience the projectors' original level of image quality for years, while achieving a maximum 5,000 lumens brightness when the constant brightness mode is off.

Information on EU Data Act: [Click here](#) to check if your Sony product and/or related service is subject to the EU Data Act.

Gallery



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.