

BRAVIA BZ30J Series

Standard 4K Ultra HD HDR
Professional Displays with
business-friendly features in
screen sizes from 32” to 75”



Overview

Beautiful pictures, made for business

Available in a choice of screen sizes from 32”-75”, BRAVIA BZ30J offers sumptuous 4K HDR picture quality pictures with an extra-wide viewing angle – adding impact to signage and all your visual communications in business, retail, educational and public environments. It’s the business-friendly professional display, with reliable 24/7 operation, productivity-focused apps on board, easy customisation and simple content sharing.

BRAVIA BZ30J Series brings greater clarity, colour and contrast to corporate meetings, presentations and digital signage. Advanced Sony picture processing technologies add even more impact and realism to videos, photos, charts, graphics and text. 4K X-Reality PRO upscales lower-resolution picture sources closer to true 4K quality, sharpening and refining in real time to reveal extra detail. The panel’s extra-wide viewing angle ensures that everyone in the room can enjoy clear, bright images wherever they’re positioned.

Features

Exquisitely rich, natural colour

Sony’s power-packed 4K HDR Processor X1 and TRILUMINOS PRO technology ensure that BRAVIA BZ30J Series faithfully reproduces a phenomenal range of rich, true-to-life colours.

Fluid, blur-free movement

Motionflow XR technology ensures that on-screen content always remains smooth, clear and blur-free – even with fast-moving video scenes.

Smart apps

BRAVIA BZ30J Series helps your business move forward with in-built apps and solutions including screen mirroring, digital signage and meeting room management. There are even more smart apps to explore at Google Play Store.

Round the clock reliability

Because business never sleeps. BRAVIA BZ30J Series is ruggedly engineered for reliable 24/7 operation – ideal for applications like signage where your message always needs to be clearly visible.

Stunning images in any orientation

BRAVIA fits right in with your business needs. The display can be mounted horizontally (landscape) or vertically (portrait) to suit any environment, from corporate boardrooms to digital signage. Tilt your BRAVIA to help capture your audience's attention*.

*The tilt degree varies by model

Quick set-up

Pro Mode lets you customise and store display settings to suit different environments, then copy them easily to multiple displays via USB flash memory. One Step Setting optimises picture and network settings for meeting rooms and signage applications at the touch of a button.

Signage made simple

In-built support for HTML5 makes it easy to display interactive signage content on BRAVIA BZ30J Series without the need for a dedicated set-top box, media player or PC.

Cast your content wirelessly

With AirPlay2 and Chromecast built in it's easy to cast videos, apps and other content wirelessly from your own device directly to BRAVIA BZ30J Series. There's also support for other third-party wireless collaboration tools.

With BRAVIA, sustainability in every scene

With growing demand for ever larger display screens, there is also the risk of greater resource and energy use. However, Sony's sustainability commitments are realising efficiency gains from product development right through to watching TV and viewing screens.

Convenient connections

Signal connections, networking and other interfaces are conveniently side mounted for easy access when the displays in portrait position.

24/7

Because business never sleeps: BRAVIA is engineered for dependable 24/7 operation in the most challenging corporate and commercial environments.

Energy Saving

BRAVIA incorporates advanced energy saving features to reduce power consumption and keep running costs in check.

Easy integration

BRAVIA BZ30J Series is made for today's connected world. There's seamless support for today's leading automation and control platforms, while open APIs simplify integration with a wide range of solutions from other vendors.

Specifications

Display Features

32" Screen: 300 ,43" Screen: 400,

| | |
|---------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| Brightness (cd/m ²) | 50"Screen: 440 , 55"Screen: 440 , 65" Screen: 440, 75" Screen: 440 |
| Native Contrast Ratio | 32" Screen: 3000:1, 43" Screen: 1200:1 50"Screen: 5000:1, 55"Screen: 1200:1, 65" Screen: 1200:1, 75" Screen: 1200:1 |
| Dynamic Contrast Ratio | 32" Screen: 260000:1, 43" Screen: 400000:1, 50"Screen: 300000:1, 55"Screen: 300000:1, 65" Screen: 300000:1, 75" Screen: 300000:1 |
| Response Time (ms) | 6 |
| Panel type | 32" Screen: VA 43" Screen: IPS 50" Screen: VA 55" Screen: IPS 65" Screen: IPS1 75" Screen: IPS |
| Dimming Type | Local Dimming |
| Display Device | LCD |
| Backlight Type | Direct LED |
| Operation Time | 24/7 |
| Portrait Mode | Yes |

Display Specifications

| | |
|------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
| Screen Size for WEB (diagonal, cm, integer or 1st decimal) | Option 1: 80cm , Option 2: 108cm , Option 3: 126cm , Option 4: 139cm , Option 5: 164cm , Option 6: 189cm |
| Display resolution (H x V, pixels) | 3840 x 2160 |
| Screen Size (inch, measured diagonally) | Option 1: 32"(31.5)" , Option 2: 43" (42.5)" , Option 3: 50"(49.5)" , Option 4: 55"(54.6)" , Option 5: 65"(64.5)" , Option 6: 75"(74.5)" |
| Viewing Angle (Right/Left/Up/Down) | 178(89/89) degree |
| Display Resolution | QFHD |
| Aspect Ratio | 16:9 |

Professional Features

| | |
|---------------------------------------------|-----|
| Professional Hidden Mode | Yes |
| HDMI Auto Wake-up | Yes |
| Multicast/ IPTV | Yes |
| Compatible with TDM Digital Signage/TEOS | Yes |

Solutions

| | |
|-----------------------|------------|
| Operating System | Android TV |
| On-board Storage (GB) | 16GB |

Network Features

| | |
|--------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Wi-Fi Direct | Yes |
| Wi-Fi Certified | Yes |
| Wi-Fi Standard | a/b/g/n/ac |
| Wi-Fi Frequency | 2.4GHz/5GHz(for Wi-Fi Direct: 2.4GHz Only) |
| Codec for Home Network | MPEG1:MPEG1 / MPEG2PS:MPEG2 / MPEG2TS (HDV,AVCHD):MPEG2,AVC / MP4 (XAVCS):AVC,MPEG4,HEVC / AVI:Xvid,MotinJpeg / ASF (WMV):VC1 / MOV:AVC,MPEG4,MotionJpeg / MKV:Xvid,AVC,MPEG4,VP8.HEVC / WEBM:VP8 / 3GPP:MPEG4,AVC / MP3 / ASF(WMA) / LPCM / WAV / MP4AAC / FLAC / JPEG |
| Apple AirPlay (Internet) | Yes |

required)

| | |
|---------------------|-----|
| Chromecast built-in | Yes |
|---------------------|-----|

| | |
|--------------|------------|
| Wireless LAN | Integrated |
|--------------|------------|

Convenience Features

| | |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| USB Playback Codecs | MPEG1:MPEG1 / MPEG2PS:MPEG2 / MPEG2TS (HDV,AVCHD):MPEG2,AVC / MP4 (XAVCS):AVC,MPEG4,HEVC / AVI:Xvid,MotionJpeg / ASF (WMV):VC1 / MOV:AVC,MPEG4,MotionJpeg / MKV:Xvid,AVC,MPEG4,VP8.HEVC / WEBM:VP8 / 3GPP:MPEG4,AVC / MP3 / ASF (WMA) / LPCM / WAV / MP4AAC / FLAC / JPEG |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

| | |
|----------|-----|
| HDMI-CEC | Yes |
|----------|-----|

| | |
|-----------------|-----|
| On Screen Clock | Yes |
|-----------------|-----|

| | |
|-------------|-----|
| Sleep Timer | Yes |
|-------------|-----|

| | |
|--------------|-----|
| On/Off Timer | Yes |
|--------------|-----|

AFR, AMH, ARA, ASM, AZE, BEL, BUL, BEN, BOS, CAT, CZE, DAN, DEU, GRE, ENG, SPA, EST, BAQ,

| | |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Display Language | PER, FIN, FRA, GLG, GUJ, HIN, HRV, HUN, IND, ISL, ITA, HEB, JPN, KAZ, KAN, KOR, KIR, LAO, LIT, LAV, MAC, MAL, MON, MAR, MAY, BUR, NOB, NEP, NLD, ORI, PAN, POL, POR, RUM, RUS, SOL, SLV, ALB, SRP, SWE |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Control Specs

| | |
|-----------------|----------|
| IP Control | Yes |
| RS-232C Control | 1 (Side) |
| Pro mode | Yes |

Inputs & Outputs

| | |
|--------------------------|------------------------------------------------------------------------------------------------------------------|
| HDMI Signal | 4096x2160p(24,60Hz), 3840x2160p(24,30,60Hz), 1080p(30,60Hz), 1080/24p, 1080i(60Hz), 720p(30,60Hz), 720/24p, 480p |
| HDCP | HDCP2.3(for HDMI1/2/3/4) |
| AC Power Input | C8 INLET(REAR) |
| Composite Video Input(s) | 1(Side, Mini jack) |

| | |
|-------------------------|-----------|
| HDMI Inputs Total | 4 (4Side) |
| Digital Audio Output(s) | 1(Side) |
| Headphone Output(s) | 1(Side) |
| USB Ports | 2(Side) |
| Ethernet Inputs | 1(Side) |
| RS-232C Input(s) | 1(Side) |

Audio Specifications

| | |
|------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| Speaker Position | Down Firing |
| Audio Power Output | 32" Screen: 5W + 5W , 43" Screen: 10W + 10W , 50"Screen: 10W + 10W , 55"Screen: 10W + 10W , 65" Screen: 10W + 10W, 75" Screen: 10W + 10W |
| Digital Audio Out (Optical) Format | Two channel linear PCM: 48kHz 16bits, Dolby Audio, DTS |
| Dolby Atmos | Yes |
| Speaker Type-2 | X-Balanced Speaker (not available for 32" Screen) |
| Clear Phase | Yes |
| Dolby Audio Format Support | Dolby Audio, Dolby Atmos |

| | |
|--------------------------------|-----------------------------------------------------------------------------------------------------------|
| HDMI Audio Return Channel(ARC) | Yes (eARC/ARC) |
| HDMI Input Audio Format | 5.1 channel linear PCM: 32/44.1/48/88.2/96/176.4/192kHz 16/20/24bits, Dolby Audio, Dolby Atmos, DTS |
| ARC Output Format | Two channel linear PCM: 48kHz 16bits, Dolby Audio, Dolby Atmos, DTS |

Video Specifications

| | |
|----------------------------------------|-----------------------------------------------|
| Wide Mode | Wide Zoom/Normal/Full/Zoom |
| 4:3 Default | Yes |
| Video Processing | 4K X-Reality PRO |
| Motion Enhancer | Motionflow XR 240 (Native 60Hz), Auto mode |
| 4K Processor | 4K HDR Processor X1 |
| HDR (High Dynamic Range) compatibility | Yes (HDR10,HLG,Dolby Vision) |
| Panel Refresh Rate (Native Hertz) | 60Hz |

Design Features

| | |
|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Cable Management | Yes |
| Frame color | Black |
| Stand Design | Slim Blade stand |
| VESA® Hole | Yes |
| VESA® Hole Pitch(W x H) | 32" Screen: 100 x 200 mm , 43" Screen: 200 x 200 mm , 50"Screen: 200 x 200 mm , 55"Screen: 300 x 300 mm , 65" Screen: 300 x 300 mm , 75" Screen: 300 x 300 mm |

Eco & Energy saving

| | |
|------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|
| Rating | G |
| On-Mode Power Consumption ¹ (Lot 5) | 32" Screen: 66 W , 43" Screen: 107 W , 50"Screen: 146 W , 55"Screen: 196 W , 65" Screen: 230 W , 75" Screen: 297 W |
| Power Consumption (in Standby) | 0.50W |
| Peak Luminance Ratio for EU | 75% |

| | |
|------------------------------------|-------------------------------|
| Mercury Content (mg) | 0 |
| Power Saving Mode / Back Light Off | Yes |
| Power Requirements (voltage) | Input 220 V - 240 V AC, 50 Hz |

Regulatory approvals

| | |
|----------------------|-----------------|
| Regulatory approvals | CE CB EAC |
|----------------------|-----------------|

Dimensions

| | |
|--------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Display Only (W x H x D) | 32" Screen: Approx. 72.6 x 43.0 x 7.6 (2.60) cm 43" Screen: Approx. 97.2 x 56.7 x 7.0 cm , 50"Screen: Approx. 112.6 x 65.3 x 7.0 cm , 55"Screen: Approx. 124.3 x 71.9 x 7.1 cm , 65" Screen: Approx. 146.2 x 84.2 x 7.1 cm 75" Screen: Approx. 168.6 x 96.9 x 7.2 cm |
|--------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

| | |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Display with Stand (W x H x D) | 32" Screen: Approx. 72.6 x 45.4 x 17.2 cm , 43" Screen:Approx. 97.2 x 63.2 x 28.6 cm, 50"Screen:Approx. 112.6 x 71.8 x 28.6 cm , 55"Screen: Approx. 124.3 x 78.7 x 33.8 cm 65" |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Screen: Approx. 146.2 x 91.2 x 33.8 cm , 75" Screen: Approx. 168.6 x 104.5 x 41.0 cm

| | |
|-----------------------------------------|--------------------------------------------------------------------------|
| Dimension of Package Carton (W x H x D) | 32" Screen: 43" Screen: 50"Screen: 55"Screen: 65" Screen: 75" Screen: |
|-----------------------------------------|--------------------------------------------------------------------------|

Weights (Approx.)

| | |
|--------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Display Only | 32" Screen: Approx. 7.5 kg , 43" Screen: Approx. 10 kg , 50"Screen: 12.3 kg , 55"Screen: Approx. 15.7 kg , 65" Screen: Approx. 21.6 kg, 75" Screen: 31.6 kg |
|--------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|

| | |
|--------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Display with Stand | 32" Screen: Approx. 7.7 kg , 43" Screen: Approx. 10.5 kg , 50"Screen: 12.9 kg , 55"Screen: Approx. 16.6 kg , 65" Screen: Approx. 22.5 kg, 75" Screen: 32.9 kg |
|--------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|

| | |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|
| Package Carton (Gross) | 32" Screen: Approx. 11 kg , 43" Screen: Approx. 14 kg , 50"Screen: 17 kg , 55"Screen: Approx. 23 kg , 65" Screen: Approx. 30 kg, 75" Screen: 45 kg |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|

Optional Accessories

SU-WL450 (Terminal access limitation, refer to SU-WL450 product page), SU-WL850, SU-WL500

PrimeSupport

3 Years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible.

Further Information

Product Information Sheet <https://eprel.ec.europa.eu/qr/526771>

Notes

1 Lot 5 On mode power demand in Standard Dynamic Range SDR kWh/1000h

Related products



BRAVIA

Signage **Free**

Standalone simple
digital signage (Free)

Gallery



