

CBK-NA1

3G/4G/LTE and Wi-Fi network adapter kit for XDCAM camcorders



Overview

Optimises LAN connection for PXW-X180, PXW-X200 and PXW-X500 camcorders working with CBK-WA100 and CBK-WA101 wireless adapters

The CBK-NA1 network adapter kit consists of a CBK-NA1E modem attachment for 3G/4G/LTE and Wi-Fi communication, and a CBK-NA1R USB/RJ-45 adapter. The CBK-NA1E allows you to attach the modem to the camcorder's handle to avoid interfering with the camcorder operation and to improve the signal transmission. The CBK-NA1R allows you to use the camcorder's streaming features with a wired connection. The unit has a cable clamp mechanism to avoid the USB connector being damaged by a cable stress.

Network module extension adapter

The CBK-NA1E allows you to attach a 3G/4G/LTE modem to a Sony camcorder and is optimised for the PXW-X180, PXW-X200 and PXW-X500 camcorders. The module is fixed on a 1/4-inch accessory shoe.

USB/RJ-45 adapter

The CBK-NA1R converts the USB terminal* to the RJ-45 terminal of the camcorder or wireless adapter CBK-WA100 and CBK-WA101. It allows you to connect the camcorder to a network using a LAN cable for streaming with a wired connection. A cable clamp secures the USB connector.

* The terminal name differs depending on the attaching device (USB wireless LAN module terminal or connecting terminal for external devices).

Features

Network module extension adapter

The CBK-NA1E allows you to attach a 3G/4G/LTE modem to a Sony camcorder and is optimised for the PXW-X180, PXW-X200 and PXW-X500 camcorders. The module is fixed on a 1/4-inch accessory shoe. The adapter allows you to avoid interfering with the camcorder operation and to improve the signal transmission.

USB/RJ-45 adapter

The CBK-NA1R converts the USB terminal* to the RJ-45 terminal of the camcorder or wireless adapter CBK-WA100 and CBK-WA101. It allows you to connect the camcorder to a network using a LAN cable for streaming with a wired connection. A cable clamp secures the USB connector. A supplied belt secures the network cable connected to the USB/RJ-45 adapter.

* The terminal name differs depending on the attaching device (USB wireless LAN module terminal or connecting terminal for external devices).

Specifications

Network Module Extension Adapter: CBK-NA1E

| | |
|--------------|-------------------------------|
| USB | USB 2.0 Type A |
| Cable length | Approx. 200 mm (7 7/8 inches) |
| Mass | Approx. 65 g (2.3 oz) |
| Operating | |

| | |
|-----------------------|-----------|
| Operating temperature | 0°C~+40°C |
|-----------------------|-----------|

| | |
|--------------------|---------|
| Operating humidity | 20%~90% |
|--------------------|---------|

| | |
|---------------------|-------------|
| Storage temperature | -20°C~+60°C |
|---------------------|-------------|

USB to RJ45 Adapter: CBK-NA1R

| | |
|-----|----------------|
| USB | USB 2.0 Type A |
|-----|----------------|

| | |
|------------------|---------------------|
| Network terminal | RJ-45 10 /100BASE-T |
|------------------|---------------------|

| | |
|----------------|-----------|
| Feeding system | Bus power |
|----------------|-----------|

| | |
|--------------|---------------------------|
| Cable length | Approx. 100 mm (4 inches) |
|--------------|---------------------------|

| | |
|------|-----------------------|
| Mass | Approx. 20 g (0.7 oz) |
|------|-----------------------|

| | |
|-------------------|-------|
| Power consumption | 1.5 W |
|-------------------|-------|

| | |
|-----------------------|-----------|
| Operating temperature | 0°C~+40°C |
|-----------------------|-----------|

| | |
|--------------------|---------|
| Operating humidity | 20%~90% |
|--------------------|---------|

| | |
|---------------------|-------------|
| Storage temperature | -20°C~+60°C |
|---------------------|-------------|

Related products



CBK-



CBK-

WA100

Wireless adapter for Camcorders and Decks [Mobile network 3G / 4G / LTE / Wireless LAN]

WA101

Wireless adapter for PMW-400 and PXW-X320 [Mobile network 3G / 4G / LTE / Wireless LAN]

Gallery

