


FWD-55X70G/T

55" BRAVIA 4K Ultra HD, HDR,
LED Professional Display



Overview

High quality 4K HDR images with TRILUMINOS Display

Make business more entertaining with the FWD-55X70G/T 55" BRAVIA Professional Display that combines lifelike 4K HDR image quality with easy operation, flexible networking/control and smart content sharing.

Optimised for professional applications, the BRAVIA FWD-55X70G/T delivers richly coloured, high-contrast 4K HDR images, while 4K X-Reality PRO upscales lower-resolution images closer to true 4K quality.

With advanced control, Simple Pro Mode and optional interactive compatibility, it makes it easy to create attractive digital signage so you always present a clear image.

Enrich your audience's display experience with seamless TEOS integration (*2) and a choice of built-in solutions to add extra functionality, from meeting room support to automation.

For even greater peace of mind there's the added reassurance of our 3 Year Advanced Exchange PrimeSupport service. If there's a problem with your display, we'll offer a free, brand new replacement product rather than repair included as standard.

You can also choose to extend your service by 2 additional years.

Features

4K image resolution (3840 x 2160 pixels)

4K offers four times the detail of Full HD, with a resolution of over 8 million pixels bringing extra clarity to corporate display, education and digital signage applications.

See finer detail

4K X-Reality PRO upscales pictures closer to true 4K quality. Images are sharpened and refined in real time, revealing extra detail from lower-resolution picture sources.

More colour with TRILUMINOS Display

TRILUMINOS Display maps colours from a wider palette, faithfully reproducing a world of richer, more lifelike hues and tones.

Smoother movement

Motionflow XR inserts additional picture frames between the originals, ensuring smoother, sharper detail in fast-moving sequences.

Optimised for professional use

The FWD-55X70G/T meets the needs of today's business and educational environments, with flexible installation options plus wired or wireless network connection and serial communication control.

TEOS Integration (*2)

BRAVIA integrates seamlessly with TEOS, Sony's suite of workspace management applications that orchestrate control of devices and content in boardrooms, meeting areas and public spaces.

Smart Plug & Play

Connect a smartphone or USB drive to share video, photos or music content directly on BRAVIA.

Flexible mounting and installation

BRAVIA Professional Displays offer flexible mounting options with VESA standard mounting for easy integration into a wide range of environments.

Greater peace of mind

There's extra reassurance with our 3 Year Advanced Exchange PrimeSupport service that's included as standard. If there's a fault with your BRAVIA Professional Display, we'll provide a replacement unit at no extra charge to keep you up and running.

Specifications

TV System

| | |
|---------------------------------|----------|
| TV System (Digital Terrestrial) | DVB-T/T2 |
|---------------------------------|----------|

| | |
|---------------------------|-------|
| TV System (Digital Cable) | DVB-C |
|---------------------------|-------|

| | |
|-------------------------|----------|
| TV System (Digital Sat) | DVB-S/S2 |
|-------------------------|----------|

| | |
|--------------------------------------|----------------------|
| Number of Tuners (Terrestrial/Cable) | 1 (Digital / Analog) |
|--------------------------------------|----------------------|

| | |
|------------------------|---|
| Number of Tuners (Sat) | 1 |
|------------------------|---|

Display features

| | |
|--------------|---------------|
| Dimming type | Frame Dimming |
|--------------|---------------|

| | |
|----------------|-----|
| Display device | LCD |
|----------------|-----|

| | |
|---|------------|
| Backlight type | Direct LED |
| Brightness (cd/m ²) (*1) | 393 |
| Contrast Ratio (*1) | 6000:1 |
| Dynamic Contrast Ratio | 350000:1 |
| Response Time (ms) (*1) | 12 |

Video specs

| | |
|---------------------|---|
| Wide Mode | Wide Zoom / Normal / Full / Zoom / 14:9 |
| 4:3 Default | Yes |
| Video Processing | 4K X-Reality PRO |
| Motionflow | Motionflow XR 200 Hz (Native 50 Hz) |
| Compatible with HDR | Yes (HDR10, HLG) |
| Video Signal | 4096 x 2160p (24, 50, 60 Hz), 3840 x 2160p (24, 25, 30, 50, 60 Hz), 1080p (30, 50, 60 Hz), 1080/24p, 1080i (50, 60Hz), 720p (30, 50, 60 Hz), 720/24p, 576p, 576i 480p, 480i |

Audio specs

Speaker position Down Firing

Audio Power Output 10 W + 10 W

Network specs

Wi-Fi direct Yes

Wi-Fi Certified Yes

DLNA Home Network Client / Home
Network Renderer

Miracast (screen
mirroring) Yes

Firmware update Yes

Internet Browser VEWD

Wireless LAN Integrated

Convenience features

USB Play (contents) MPEG1 / MPEG2PS / MPEG2TS /
AVCHD / MP4Part10 / MP4Part2 /
AVI(XVID) / AVI (MotionJpeg) /
WMV9 / MKV / WEBM / WAV / MP3

/ WMA / JPEG

| | |
|-----------------|-----|
| On screen clock | Yes |
| Sleep timer | Yes |
| On/Off timer | Yes |

Professional Features

| | |
|---|--|
| Professional Hidden Mode | Yes |
| HDMI auto wake-up | Yes |
| Multicast / IPTV | Yes |
| Compatible with TEOS Workplace Management Solution (*2) | Yes |
| Available storage | 4 GB |
| Compatible TEOS Content | Customised design, text, pictures, videos, YouTube, traffic, weather, public information, Facebook, Twitter, PowerPoint and more |

Inputs and outputs

HDCP

HDCP 2.3 (for HDMI 1 / 2 / 3)

| | |
|-----------------------------|--------------------------------------|
| RF Connection Input(s) | 1 (Side) |
| Composite Video Input(s) | 1 (Bottom) |
| HDMI™ Connection(s) (Total) | 3 (2 Side, 1 Rear) |
| Digital Audio Output(s) | 1 (Bottom) |
| Audio Out | 1 (Rear / Hybrid with Headphone Out) |
| USB | 3 (Side) |
| Ethernet Connection(s) | 1 (Bottom) |

Design features

| | |
|-------------------------------|------------------------------|
| Finish (Surface Color) | Black |
| Table Top Stand | Separate (assembly required) |
| VESA® Hole Spacing Compatible | Yes |
| VESA® Hole Pitch | 20.0 x 20.0 cm |

Eco and energy saving

| | |
|--|-------------------------------|
| Energy Label Rating | A |
| Screen size (measured diagonally) | 55" (54.6") |
| Power Consumption | Standard: 110 W |
| Annual Power Consumption | 161 kWh / Year |
| Power Consumption (in Standby) | 0.50 W |
| Power Consumption (networked standby mode) | 2.00 W (Wi-Fi) / 2.00 W (LAN) |
| Peak Luminance Ratio | 76% |
| Lead content | Yes |
| Mercury content (mg) | 0.0 |
| Power Requirements | AC 220-240 V |
| Power Saving Mode / Back Light Off Mode | Yes |
| Dynamic Backlight Control | Yes |
| AC Power Input | 1 (Rear) |

Measurements

| | |
|------------------------------------|--------------------------------------|
| Display Only (W x H x D) (Approx.) | Approx. 124.1 x 72.1 x 7.9 (1.07) cm |
|------------------------------------|--------------------------------------|

| | |
|--|--------------------------------|
| Display with Stand (W x H x D) (Approx.) | Approx. 124.1 x 78.5 x 33.6 cm |
|--|--------------------------------|

| | |
|--------------------------------------|--------------------------------|
| Package Carton (W x H x D) (Approx.) | Approx. 139.7 x 83.3 x 16.0 cm |
|--------------------------------------|--------------------------------|

Weight

| | |
|--------------|---------|
| Display Only | 15.4 kg |
|--------------|---------|

| | |
|--------------------|---------|
| Display with Stand | 16.5 kg |
|--------------------|---------|

| | |
|----------------|-------|
| Package Carton | 24 kg |
|----------------|-------|

Display specifications

| | |
|------------------------------|--------------------|
| Viewing angle (Right / Left) | 178 (89/89) degree |
|------------------------------|--------------------|

| | |
|---------------------------|--------------------|
| Viewing angle (Up / Down) | 178 (89/89) degree |
|---------------------------|--------------------|

| | |
|--------------------|------|
| Display resolution | QFHD |
|--------------------|------|

| | |
|--------------|------|
| Aspect ratio | 16:9 |
|--------------|------|

| | |
|----|-------|
| OS | Linux |
|----|-------|

Control specs

| | |
|----------------|--------------|
| Hotel Mode Pro | Yes (Simple) |
|----------------|--------------|

| | |
|------------|-----|
| IP Control | Yes |
|------------|-----|

PrimeSupport

| | |
|-----------------------|---|
| Included PrimeSupport | 3 years of Standard helpdesk (Mon-Fri 9:00-18:00 CET) and Advanced Replacement service in case of product fault with all logistics covered. |
|-----------------------|---|

| | |
|----------------------------------|--|
| Optional PrimeSupport Extensions | Optional 2-year support extension available: PSP.FW7G-55.2X |
|----------------------------------|--|

Notes

| | |
|------|----------------------------------|
| (*1) | Typical value of the panel spec. |
|------|----------------------------------|

| | |
|------|-------------------------|
| (*2) | Requires TEP-TX5 Player |
|------|-------------------------|

Gallery

