

HDVF-L10

3.5" Colour LCD HD Viewfinder



Overview

3.5" Colour LCD HD Viewfinder for cameras with a round-type 20-pin viewfinder interface. The applicable cameras output the higher resolution QHD signal to this viewfinder. Camera operators can see the LCD, directly, because the optical loupe and the elbow parts can be flipped-up.

3.5" Colour LCD QHD Viewfinder

Uses round-type 20-pin viewfinder interface

Switchable display mode

Specifications

General

| | |
|--------------|--|
| Power supply | 10.5 to 17.0 V DC (supplied by the camera) |
|--------------|--|

| | |
|-------------------|-------|
| Power consumption | 3.3 W |
|-------------------|-------|

| | |
|-----------------------|-------------|
| Operating temperature | -5°C - 45°C |
|-----------------------|-------------|

| | |
|---------------------|-------------------------------|
| Storage temperature | -20C to +60C (-4 F to +140 F) |
|---------------------|-------------------------------|

| | |
|---------------------|--|
| Mass | 700 g |
| External dimensions | 201mm (8 in) x 255mm (10 1/8 in) x 60mm (2 3/8 in) 89mm (3 5/8 in) |

| | |
|--|--|
| 3.5-inch colour TFT transfective LCD Image display area dimensions | 76.8 × 43.2 mm (3 1/8 × 1 3/4 inches) (H/V, 16:9 aspect ratio) |
|--|--|

Performance

| | |
|--------------------|---|
| Brightness | 200 cd/m ² (typical) (when eyepiece is attached) |
| Resolution | 500 lines or more |
| Colour temperature | 6500 K (typical) |

Connector

| | |
|-----------|-----------------------------|
| Connector | Round-type 20-pin connector |
|-----------|-----------------------------|

Supplied accessories

| | |
|----------------------|----------------------|
| Supplied accessories | Operation manual (1) |
|----------------------|----------------------|

Optional accessories

Viewfinder Rotation Assembly :

Optional accessories BKW-401

Compatible products

Compatible products HXC-FB75KC, HXC-FB75H, HDC-1700, HDC-2400, HDC-2500, HDC-2570, HDC-3300R, HDC-4300, HSC-100R, HSC-100RF, HSC-300R, HSC-300RF, PDW-680, PDW-700, PDW-850, PDW-F800, PMW-500, PXW-X400, PXW-X500

Notes

Notes Design and specifications are subject to change without notice.

Related products



HXC-FB80

Three 2/3-inch
Exmor™ CMOS sensor
HD colour studio
camera

Gallery

