

PXW-Z750

4K 2/3-type 3-chip CMOS
Shoulder-mount Camcorder
with global shutter, high
sensitivity, 4K/HD simultaneous
recording, 120p HFR in HD, 12G-
SDI and advanced wireless
workflow capabilities



Overview

New benchmark for 4K, HDR and HD image quality

Capture beautiful 4K imagery with the deep of depth of field made possible by 3-chip 2/3- type CMOS sensor. The Z750 is Sony's first shoulder-mount camcorder with a global shutter to eliminate flash banding and "jello" effects. It sets a new class-leading standard for 4K, HDR and HD image quality for reality TV, documentary, news and sports production. In fast-moving applications where a second take is impossible, Z750 is the ideal choice.

Saving time and money

Delivering highest quality 4K with HD era workflows wastes time and money. The Z750's latest generation XAVC-L422 QFHD 200 codec combined with high-speed SxS Pro media radically reduce real-world turnaround times. Premium 4K becomes deliverable on almost any project using the PXW-Z750.

Transformative cloud-based collaboration

Z750 is at the vanguard of seamlessly integrating Cloud-based production tools with familiar, easy-to-use interfaces and proven Sony reliability. Build stories fast, with secure, direct access from the studio to camcorders out in the field with XDCAM air.

Distribute content for preview and editing with stakeholders across the world using Sony's Ci Media Cloud.

Features

3-chip 2/3-type CMOS Sensor with Global Shutter

The PXW-Z750 incorporates a newly developed 3-chip 2/3" 4K CMOS sensor optical block with a wide colour gamut provides exquisite picture quality with true-to-life colour reproduction, high sensitivity and low noise level for a wide range of shooting scenarios.

Versatile B4 ENG lens options

Thanks to the versatile 3-chip 2/3-type size sensor block and traditional B4 lens mount, the Z750 allows you to install a variety of B4 ENG lenses including either 4K or HD. This flexible lens options supports a variety of shooting applications while saving cost by leveraging existing lens investments.

High Dynamic Range and wider, richer colours

PXW-Z750 can record HDR using Sony S-Log3 or Hybrid Log Gamma (HLG). The camera's wide colour gamut supports extended Sony S-Gamut3 and S-Gamut3. Cine colour spaces, as well as the industry standard ITU-R BT.2020 colour space.

- S-Log3 has a proven track record for premium applications, capturing the maximum dynamic range from the sensors, for the most creative colour grading processes.*
- Industry standard HLG delivers content quickly without additional colour grading, making it an ideal choice for day-to-day shooting, viewing, editing and broadcasting workflows.

* QFHD only.

High quality at lower bitrates

As well as the established XAVC-I QFHD Class 300 4K and standard MPEG HD422 codecs, the PXW-Z750 also supports the latest generation XAVC-L422 QFHD 200 codec. Compressing 4K Ultra HD images with a LongGOP frame structure, this achieves significant bitrate savings over previous Intra Frame codecs while maintaining superb 4K image quality. Lower data rates increase recording times while reducing storage requirements. Uncompromised picture quality is ensured by 10-bit quantisation and 4:2:2 colour sampling, making the PXW-Z750 ideal for HDR productions. A wide range of 4K codecs provide the flexibility to select the recording format that is best suited for the requirements of the production you are working on.

Superb slow motion

Ideal for sports and nature programmes, the PXW-Z750 can acquire footage in 60fps in QFHD and 120fps in Full HD for beautifully smooth, finely-detailed slow-motion playback.

Cache recording

Never miss a shot with advanced cache recording in both 4K and Full HD modes.

Next generation wireless ENG workflow

Built-in wireless connectivity enables advanced workflow production features including live streaming, recording hi-res and proxy files, FTP transfer and even remote control from a smartphone or tablet* via Wi-Fi. Wireless workflow is made even more efficient using XDCAM air, Sony's professional cloud service including dual-link cellular operation.**

* Requires Content Browser Mobile and device running iOS 9.0-10.3 or Android 4.4-7.1

** Requires XDCAM air subscription and CBK-DL1 USB Extension

Adaptor.

Seamless wireless audio workflow

PXW-Z750 is compatible with Sony's DWX series of digital wireless microphone systems offering ENG and documentary teams the benefits of an all-digital audio workflow, including robust end-to-end encryption for truly secure operation.*

- Wireless transmitter parameters can be controlled directly from the PZW-Z750 using the Cross Remote function.
- Transmitter power save mode synchronises with the camera's on/off control, and is controllable by assignable buttons to save transmitter battery life.
- Audio and video are precisely synchronized, ensuring no delays or lip-sync problems.
- Power save status and receiver RF levels are displayed in the viewfinder.

* For details, please consult local sales company.

Lightning-fast transfers with latest generation media

The PXW-Z750 supports latest-generation SxS Pro X media, enabling very high speed file transfers at up to 10Gbps (1250MB/s)* with the SBAC-T40 Thunderbolt™ 3, SxS card reader/writer. Transfers are approximately three times faster than previous generation media/reader combinations, dramatically accelerating workflows for any application and bringing down production costs.

*Based on Sony internal testing. Transfer speeds vary and are

dependent on host devices, the OS version or usage conditions.

Specifications

General

| | |
|---------------------------|---|
| Mass | Approx. 3.8 kg (body only without lens, VF, Mic) |
| Dimensions (W x H x D) | Approx. 150 × 269 × 332 mm (excluding protrusions, body only) |
| Power Requirements | DC 12 V (11 V to 17.0 V) |
| Power Consumption | Approx. 41 W (while XAVC recording, color LCD on) |
| Operating Temperature | 0~40°C |
| Storage Temperature | -20~+60°C |
| Continuous Operating Time | Approx. 110 min with BP-GL95B |
| Lens Mount | Sony 2/3 type bayonet mount |

Camera Section

| | |
|----------------------|-------------------------|
| Imager | 2/3-type 3-chip 4K CMOS |
| Effective Resolution | 3840 (H) x 2160 (V) |

| | |
|--|--|
| Built-in Optical Filters | 1: Clear, 2: 1/4ND, 3: 1/16ND, 4: 1/64ND |
| Shutter Speed (Time) | 59.94i/p, 50i/p: 1/60 sec. to 1/2000 sec. + ECS 29.97p: 1/40 sec. to 1/2000 sec. + ECS 25p: 1/33 sec. to 1/2000 sec. + ECS 23.94p: 1/32 sec. to 1/2000 sec. + ECS |
| Shutter Speed (Slow Shutter(SLS)) | 2, 3, 4, 5, 6, 7, 8, 16-frame accumulation |
| Slow & Quick Motion | 2160p: Frame rate selectable from 1 fps to 60 fps 1080p: Frame rate selectable from 1 fps to 60 fps /72/75/80/90/96/100/110/120 fps |
| Sensitivity (2000 lx, 89.9% reflectance) | F12 (1080 / 59.94i), F13 (1080 / 50i) *High Sense Mode ON (Typical) F12 (2160 / 59.94p), F13 (2160 / 50p) *High Sense Mode ON (Typical) |
| Minimum Illumination | 0.019 lx (F1.4, +42 dB, 16-frame accumulation) |
| White Balance | Preset (3200K), Memory A, Memory B/ATW |

| | |
|-----------------------|--|
| Gain Selection | -3, 0, 3, 6, 9, 12, 18, 24, 30, 36, 42 dB |
| S/N Ratio | 62dB (Noise Suppression ON, 1920 x 1080 59.94i) (Typical) |
| Horizontal Resolution | 2,000 TV lines or higher (3840 x 2160p mode) 1,000 TV lines or higher (1920 x 1080i mode) |

Recording format (Video)

| | |
|--------------------------------|---|
| XAVC Intra (XAVC-I QFHD 300) | 3840 x 2160: 59.94p, 50p, 29.97p, 25p, 23.98p |
| XAVC Intra (XAVC-I HD 100) | 1920 x 1080: 59.94p, 50p, 59.94i, 50i, 29.97p, 25p, 23.98p |
| XAVC Long (XAVC-L422 QFHD 200) | 3840 x 2160: 59.94p, 50p |
| XAVC Long (XAVC-L420 QFHD 150) | 3840 x 2160: 59.94p, 50p |
| XAVC Long (XAVC-L422 HD 50) | 1920 x 1080: 59.94p, 50p, 59.94i, 50i, 29.97p, 25p, 23.98p |
| MPEG HD422 | 1920 x 1080: 59.94i, 50i, 29.97p, 25p, 23.98p 1280 x 720: 59.94p, 50p, 29.97p, 25p, 23.98p |

| | |
|------------|--|
| MPEG HD420 | 1920 x 1080: 59.94i, 50i, 29.97p, 25p, 23.98p 1440 x 1080: 59.94i, 50i 1280 x 720: 59.94p, 50p |
|------------|--|

Recording Format (Audio)

| | |
|------------------------------|----------------------------------|
| XAVC Intra (XAVC-I QFHD 300) | LPCM 24 bits, 48 kHz, 4 channels |
|------------------------------|----------------------------------|

| | |
|----------------------------|----------------------------------|
| XAVC Intra (XAVC-I HD 100) | LPCM 24 bits, 48 kHz, 4 channels |
|----------------------------|----------------------------------|

| | |
|--------------------------------|----------------------------------|
| XAVC Long (XAVC-L422 QFHD 200) | LPCM 24 bits, 48 kHz, 4 channels |
|--------------------------------|----------------------------------|

| | |
|--------------------------------|----------------------------------|
| XAVC Long (XAVC-L420 QFHD 150) | LPCM 24 bits, 48 kHz, 4 channels |
|--------------------------------|----------------------------------|

| | |
|-----------------------------|----------------------------------|
| XAVC Long (XAVC-L420 HD 50) | LPCM 24 bits, 48 kHz, 4 channels |
|-----------------------------|----------------------------------|

| | |
|------------|----------------------------------|
| MPEG HD422 | LPCM 24 bits, 48 kHz, 4 channels |
|------------|----------------------------------|

| | |
|------------|----------------------------------|
| MPEG HD420 | LPCM 24 bits, 48 kHz, 4 channels |
|------------|----------------------------------|

Recording Format (Proxy Video)

AVC/H.264 Main Profile 4:2:0 Long GOP, VBR
1920 x 1080, 6 Mbps, 9 Mbps (Target)

| | |
|------------|--|
| XAVC Proxy | Rate) 1280 x 720, 6 Mbps , 9 Mbps (Target Rate) 640 x 360, 3 Mbps (Target Rate) 480 x 270, 1 Mbps, 500 kbps (Target Rate) |
|------------|--|

Recording Format (Proxy Audio)

| | |
|------------|------------------------------|
| XAVC Proxy | AAC-LC, 128 kbps, 2 channels |
|------------|------------------------------|

Input / Output

| | |
|----------------|---|
| Genlock Input | BNC (x1), 1.0 Vp-p, 75 Ω, unbalanced |
| Timecode Input | BNC (x1), 0.5 V to 18 Vp-p, 10 kΩ |
| SDI Input | SMPTE ST292/ST259 standard compliant, 4-channel audio 1.5G Poolfeed Recording (upto 1080 59.94i) |
| Audio Input | CH1/CH2: XLR-type 3-pin (female) (x2), Line/AES/EBU/Mic+48V selectable LINE: +4, 0, -3 dBu AES/EBU: AES3 compliant MIC: -70 dBu to -30 dBu |

| | |
|------------------------------------|--|
| Mic In | XLR-type 5-pin, female: -70 dBu to -30 dBu |
| WRR (Wireless Microphone Receiver) | D-sub 15-pin Analog CH1: -40 dBu Digital CH1/CH2: -40 dBFS |
| SDI Output | BNC x2 (Both SDI are selectable from 12G, 3G and 1.5G) 4ch Embedded Audio |
| Sync Output | BNC, SD analog composite/HD-Y selectable |
| Audio Output | XLR-type 5-pin, female: +4/0/-3dBu |
| Timecode Output | BNC, 1.0 Vp-p, 50 Ω |
| Earphone Output | Stereo mini jack (x1) -12 dBu (reference level output, maximum monitor volume, 16 Ω load) |
| DC Input | XLR-type 4-pin, male, 11 V to 17 V DC |
| DC Output | Round type 4-pin, 11 V to 17 V DC, 1.8 A maximum rated current |
| Lens | 12-pin, lens power source (11 V to 17 V DC, 1.0 A maximum rated current) |

| | |
|----------------|---|
| Remote | 8-pin |
| Light | 2-pin |
| Camera Adapter | D-sub, 50-pin (x1) (only for Japan model) |
| Ethernet | RJ-45 (x1), 100BASE-TX: IEEE 802.3u, 10BASE-T: IEEE 802.3 |
| USB | 4pin (A type) x 2, 4pin (B type) |
| HDMI | A type, 19-pin (x1) output up to 3840x2160 |
| Viewfinder | 20-pin IF for HDVF Series Viewfinder |

Audio Performance

| | |
|--------------------|---|
| Frequency Response | 20 Hz to 20 kHz (± 3 dB or less) |
| Dynamic Range | 90 dB (typical) |
| Distortion | 0.08 % or lower (-40 dBu input level) |
| Headroom | 20 dB (factory default) (20, 18, 16, 12 dB), EBUL |

Monitoring

| | |
|------------|--------|
| Viewfinder | Option |
|------------|--------|

| | |
|----------------------|---|
| Built-in LCD Monitor | <p>Color LCD</p> <p>Screen size: 8.8 cm (3.5 inch) diagonal</p> <p>Aspect ratio: 16:9</p> <p>Number of pixels: 960 (H) x 540 (V) for Video display, Audio level, TC, battery and media remaining capacity</p> |
|----------------------|---|

Other Functions

| | |
|-------------------------|---|
| Built-in Speaker | (x1) |
| Media SxS Card Slots | Number of slots: 2 |
| Media SD Card Slots | Proxy (1), Utility (1) |
| HDR | (OETF): HLG/S-Log3, (Color Space): BT.2020/S-Gamut3/S-Gamut3.cine |
| GPS | Yes |
| Built-in Network Module | Yes |
| NFC | Yes |

Supported Media

| | |
|-----------------|---|
| High Resolution | SxS card SDXC card (SD Card Adapter, |
|-----------------|---|

Video/Audio MEAD-SD02)

Proxy Video / Audio
and utility SDXC/SDHC

Supplied Accessories

Shoulder Belt (1)
Cold Shoe Kit (1)
Lens Mount Cap (1)
USB wireless LAN module (IFU-
WLM3) (1)
Protective Cap (1)
Operating Instructions (CD-ROM)
(1)
Before using this unit (1)

Related products



BVM-E171

16.5-inch TRIMASTER EL™ OLED critical reference monitor with wide viewing angle supports 4K production



BVM-HX310

31.1-inch 4K TRIMASTER HX™ Professional Master Monitor



LMD-A170

17-inch lightweight Full HD high grade LCD monitor for studio and field use



LMD-A220

21.5-inch lightweight Full HD high grade LCD monitor for studio and field use



LMD-A240

24-inch lightweight
Full HD high grade
LCD monitor for
studio and field use

PDT-FP1

Portable data
transmitter with 5G,
mmwave and sub6 for
high-speed
transmission of video
and still images

Gallery



