

RCP-1501

Dial type of Remote Control Panel for HDC/HSC/HXC series cameras. 4 units in 19-inch EIA rack.



Overview

The RCP-1501 incorporates an LCD display with direct operation switches and a touch panel, which makes it a remote control panel that offers both ease of operation and multifunctionality that compares favorably with the MSU. The iris and master black adjustment block employs dial (knob) type control. Up to four units can be mounted in a 19-inch EIA rack.

Features

Touch panel and many direct access switches suitable for various camera operations

This remote control panel is equipped with the control functions required to perform various camera operations enabling the simple and accurate operation of the camera. The operation buttons, adjustment knobs, and other controls are arranged on the panel according to function and frequency of use. Guard frames are provided around buttons that are vital to the operation and setup of cameras to prevent the buttons from being unintentionally operated.

Ethernet connection capability

It is possible to connect by LAN cable in addition to connecting using CCA-5 cable. Therefore, when setting up a multi-camera control system, not only can a system be built using the CNU-700 as previously, but a system can also be built using a LAN.

Direct control Scene file

Easily access Scene file to support various scene setting.

Customisable switch and menu.

User's can assign any function to a spare switch and make their own favourite menu as well.

Building of a variety of control systems

HDC/HSC/BVP user's can build a multi-camera control system through use of the CNU-700. In a system that uses CNU-700s, two CNU's can be used to control a camera system of up to 24 cameras. A system that uses a LAN can also be built by connecting to a LAN-compatible CCU.

Specifications

General

| | |
|--------------|-------------------|
| Power supply | DC 10.5 V to 30 V |
|--------------|-------------------|

| | |
|-------------------|-----|
| Power consumption | 4 W |
|-------------------|-----|

| | |
|-----------------------|---------------------------------|
| Operating temperature | 5 °C to 40 °C (41 °F to 104 °F) |
|-----------------------|---------------------------------|

| | |
|---|---|
| Dimensions (W x H x D) (excluding protrusions) | 102 × 310 × 85 mm (4 1/8 × 12 1/4 × 3 3/8 in) |
|---|---|

| | |
|------|-----------------------|
| Mass | 1.8 kg (3 lb. 15 oz.) |
|------|-----------------------|

Input/output connectors

| | |
|----------|------------------|
| Ethernet | RJ-45 8-pin (X1) |
|----------|------------------|

| | |
|---------|------------------------------------|
| CCU/CNU | Multi-connector 8-pin, female (x1) |
| AUX | Multi-connector 8-pin, female (x1) |
| EXT I/O | D-sub 9-pin, female (x1) |

Related products



HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



MSU-3000

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



MSU-3500

Master setup unit, multi camera remote control panel for system cameras (vertical type)



UHC-8300

UHC-8300 8K 3CMOS sensor Camera system includes UHCU-8300 8K Camera Control Unit, UKCU-8001 (8K ST 2110 Interface), UZCU-SNMP80 (SNMP for 8K ST 2110), UKCU-IP01F (Networked Media Interface)

Gallery

