

## Box-type 720p/30 fps Camera - V Series



## Overview

### Features

**CMOS image sensor for HD picture quality**

**View-DR technology for a high contrast ratio**

**Visibility Enhancer for improved performance in challenging lighting conditions**

**XDNR technology for clear low-light images**

**Easy Focus function**

**Power over Ethernet capability (IEEE802.3af)**

**Triple Codec Network Operation**

**ONVIF Compliant**


**Tamper Alarm**

**Advanced Audio Detection**


**Support for IPv6**

**Local Storage / Wireless Capability**


Specifications











Related products



**SNCA-WMFI10PC**  
Wall/Ceiling camera bracket



**SNCA-CEILING**  
Mounting coupling for pendant applications



**SNCA-HRX550EXT/W**  
Outdoor wireless dome camera housing



**UNI-XBS1/T**  
Silver bracket for SNC-CH110S and SNC-CH210S



**SNCA-HRX550/EXT 12V**  
Robust, IP66 rated dome housing for Sony PTZ cameras



**UNI-WMB3**  
Wall mount bracket for PTZ dome mount security camera housings



**UNI-OPL7C3**  
Outdoor Pressurized dome camera housing



**SNCA-POLE30**  
Mounting pipe for pendant mount applications



## **SNCA-WM40**

Heavy duty outdoor wall  
mount for the SNC-RS84P,  
SNC-RS86P and SNC-  
RH164 rapid dome cameras

## Gallery

