

# SNT-RS1U

Video Network Station rack mount for the SNT-EP154 and SNT-EX154



## Overview

SNT-RS1U holds up to 4 Encoder Blades, SNT-EX154/EP154. 16 analogue cameras can be supported.

- 16 channels
- Max. number of blades: 4
- Dimensions (w x h x d): 440 x 44 x 402 (17 3/8 x 1 3/4 x 15 7/8 inches) excluding protrusions

## Specifications

### Camera Features

Tone Correction	No
-----------------	----

Noise Reduction	No
-----------------	----

### Video Server Features

Coaxitron Control	No
-------------------	----

### Video

Resolution	No
------------	----

Compression Format	No
--------------------	----

Maximum Frame Rate	No
--------------------	----

Multi Streaming Capability	No
----------------------------	----

Number of Clients	No
-------------------	----

### Intelligent Video/Audio Analytics

Intelligent Motion Detection	No
------------------------------	----

Advanced Audio Detection	No
--------------------------	----

### Audio

No

Compression Format

Network

Protocols	No
Number of IP Address/Mac ADDRESS	No
Wireless Network	No
Authentication	No

Interface

Analog Video Input	No
Composite Buffered Through Out	No
Microphone Input	No
Audio Interface (IN/OUT)	No
Line Output	No
Network Port	No
Alarm Input (Sensor Input)	No
Alarm Output	No
Serial Interface	No
USB Slots	No

General

Power Requirements	Universal power capability AC 100-240 V
Operating Temperature	0°C to +45°C +32°F to 113°F
Storage Temperature	-20°C to +60°C -4°F to +140°F
Dimensions (W x H x D) *1	440 x 44 x402 mm 17 3/8 x 1 3/4 x 15 7/8 inches
Mass	Approx. 4.6 kg Approx. 10 lb 2 oz

Notes

\*1 The values for dimensions are approximate.

## Related products



### YT-LD124S

Tinted (Smoke) dome cover for YT-ICB124



### SNCA-WMFI10PC

Wall/Ceiling camera bracket



### SNCA-HRX550EXT/W

Outdoor wireless dome camera housing



### SNCA-HRX550/EXT 12V

Robust, IP66 rated dome housing for Sony PTZ cameras



### YT-LD124C

Clear dome cover



### SNCA-CEILING

Mounting coupling for pendant applications



### UNI-XBS1/T

Silver bracket for SNC-CH110S and SNC-CH210S



### UNI-UMB1

Indoor wall mounting bracket for minidome and PTZ cameras



### UNI-WMB3

Wall mount bracket for PTZ dome mount security camera housings



### SNCA-WM40

Heavy duty outdoor wall mount for the SNC-RS84P, SNC-RS86P and SNC-RH164 rapid dome cameras



### SNCA-POLE30

Mounting pipe for pendant mount applications



### UNI-OPL7C3

Outdoor Pressurized dome camera housing



### SNT-EX154

A fully featured four channel blade type video surveillance encoder, utilising state of the art image transmission and enhancement technology

## Gallery



