

AXS-AR1

AXS Memory and SxS Memory
Thunderbolt card reader



Overview

High speed data transfers via Thunderbolt 2 interface*

The AXS-AR1 AXS media reader offers an incredible maximum data read speed of up to 9.6 Gbps (1200MB/s) from AXS memory via Thunderbolt 2. This makes it easier than ever to import 4K/2K RAW/X-OCN/XAVC files recorded onto SxS media by Sony camcorders or AXS-A media by AXS-R7/R5 recorders. The card reader also handles both AXS-A and SxS memory cards.

* Thunderbolt cable is not included. macOS 10.6 or later required. Windows OS not currently supported.

Features

High speed transfer by Thunderbolt 2 interface

The AXS-AR1 AXS media reader offers an incredible maximum data read speed of up to 9.6 Gbps (1200MB/s) from AXS memory via Thunderbolt 2.

Daisy chain

The unit supports a daisy chain function whereby more than one reader can be connected via Thunderbolt 2 to a Mac.

Compatible slot for AXS Memory and SxS Memory

The AXS-AR1 is the best transfer reader for using PMW-F55/F5 and AXS-R7/R5 because it supports not only AXS-A Memory but also

SxS Memory. This can be particularly convenient after a shoot when using simultaneous recording with both media types.

macOS support

The AXS-AR1 is compatible with Mac computers with macOS 10.6 or later that support Thunderbolt 2. Operation is not guaranteed on all computers.

Specifications

Specifications	
Interface	Thunderbolt 2
Power	AC-DC Adaptor (VGP-AC19V77) Input: AC100V-240V, 50Hz/60Hz Output: 19.5V/3.3A (MAX.)
Power Consumption	Approx. 25W
Dimensions	Approx. 100.0 x 71.0 x 193.5 mm (W x H x D) (Without protrusion)
Mass	Approx. 1.0 kg (Without memory card)
Operating Temperature	0°C ~ 40°C
Storage Temperature	20°C ~ 60°C
Operating Humidity	20% ~ 80% (Non-condensing)
Operating System	macOS 10.6 or later required

Supplied Accessories AC Adaptor (1)

Gallery

