


ECM-77BMP

Discrete omni-directional lavalier
Electret condenser microphone



Overview

The ECM-77 is used widely in both studio production and on location. Its popularity is based on a combination of excellent sound quality, robust construction and an attractive cosmetic design. This microphone is the ECM-77BMP which is supplied with a 3.5 mm locking jack for use with UWP-D series wireless transmitters.

Hands Free

As a lavalier microphone, the ECM-77 is an alternative to the traditional hand held microphone and being 'hands free' it allows the presenter to concentrate on her/his performance.

Professional Image

The ECM-77 is probably the most seen microphone on TV and its compact design creates a professional image.

Easy and Familiar Operation

The ECM-77 is an essential tool for achieving good quality voice recording. The microphone's capsule is designed for voice pick-up with an extended frequency response and impressive

sensitivity. The popularity of the microphone in TV production means that most sound people will be familiar with using the ECM-77.

Features

Designed for high quality voice pick-up

The ECM-77's capsule features a voice emphasis curve, extended frequency response and sensitivity.

Minute size

The capsule has a diameter of only 5.6mm and is 12.5mm long.

Ready for wireless systems

The ECM-77BMP is compatible with UWP-D wireless transmitters, providing high quality wireless microphone systems for video production.

Specifications

Audio Section

Capsule Type	Electret Condenser
Frequency Response	40 Hz to 20 kHz
Directivity	Omni-directional
Sensitivity * [1]	-39.0 dB (11.2 mV)
Output Impedance * [2]	2.5kΩ ± 30%, Unbalanced
Dynamic Range	90 dB or more
Signal-to-Noise Ratio * [3]	64 dB or more

Inherent Noise *[4]	30 dB SPL or less
Induction Noise From External Magnetic Field *[5]	5 dB SPL or less
Wind Noise *[6]	40 dB SPL or less (with windscreen)
Maximum Input Sound Pressure Level *[7]	120 dB SPL

General Section

Connector	BMP type. Supplied with ø3.5 mm, 3-pole mini plug.
Mic Cable	3.9 feet 1.2 m
Power Requirements	DC 1.1 V to 10.0V
Power Consumption	0.4 mA or less
Dimensions *[8]	ø5.6 X 12.5 mm (Mic head) ø1/4 X 1/2 inches (Mic head)
Mass	Approx. 22.7 g Approx. 0.8 oz
Supplied Accessories	Single/horizontal type tie clip (1) Metal-mesh type windscreen (1)

Optional Accessories

- Wind screen pack
- Vertical clip pack
- Safety pin type clip pack
- Horizontal double-clip pack
- Horizontal single-clip pack
- ECM-77 accessory kit
- Colored wind screen kit
- Black windscreen for ECM-77

Notes

Note

- *[1] 0 dB = 1 V/Pa, at 1 kHz
- *[2] Output impedance at 1 kHz
- *[3] A-weighted, 1 kHz, 1 Pa.
- *[4] 0dB SPL = 20 μ Pa
- *[5] dB SPL/1E-7 T, 0 dB SPL = 20 μ Pa
- *[6] Wind noise at 2m/s (0 dB SPL = 20 μ Pa)
- *[7] 0 dB SPL = 20 μ Pa
- *[8] The values for dimensions are approximate.

Related products



UWP-D11



UWP-D12



UWP-D16

UWP-D bodypack
wireless microphone
package

UWP-D handheld
wireless microphone
package

UWP-D bodypack and
XLR plug-on wireless
microphone package

Gallery

