

## HDCE-RX30

IP CCU extension adaptor for remote live production (receiver)



**NETWORKED LIVE**

### Overview

The HDCE-RX30 IP Camera Control Unit (CCU) extension adaptor support IP routing with HDCE-TX30 between Camera and CCU for multi studio use in order to reduce the cost and complexity of remote live production.

Used in conjunction with the HDCE-TX30 IP camera extension adaptor, the HDCE-RX30 connects directly to the CCU (camera control unit) that can sited remotely from the camera head. Uncompressed signals from Sony HDC-3500/3100 and HDC-2500/2400/1700 series system cameras are converted to SMPTE ST 2110 and streamed over the IP network with no limitation on distance between camera head and CCU.

Support for leading IP intercom vendors including RTS, Clear-Com and Riedel allows producers and directors at the main production centre to communicate in real time with camera operators at a remote venue.

Used in conjunction with the HDCE-TX30 transmitter, the HDCE-RX30 also simplifies centralised allocation of equipment between multiple studios, control rooms and machine rooms, allowing camera signals to be routed instantly over IP to another part of the facilities.

The software license for IP HDCE to support JPEG XS<sup>\*2</sup> without

any external boxes is currently under development.

\*1 For more details on the JT-NM Tested program in March 2020 and test results, please go to [https://jt-nm.org/jt-nm\\_tested](https://jt-nm.org/jt-nm_tested).

\*2 JPEG XS is a new ultra-low latency compression technology, which is beneficial in live productions with limited bandwidth.

## Features

### **Cost effective IP upgrade**

The HDCE-RX30 IP camera extension adaptor allows broadcasters, OB providers and live production specialists to upgrade to the benefits of IP Live production without needing to replace their current HDC camera investments. The HDCE-RX30 connects directly to the CCU that can be located remotely from the camera head and HDCE-TX30 extension adaptor transmitter.

### **Efficient resource sharing**

The HDCE-RX30 allows faster, more cost-effective use of shared production resource across multiple studios and locations. While conventional SDI infrastructures tie one camera to a single CCU by fibre cable. Used in conjunction with the HDCE-TX30 it allows flexible reconfiguration of cameras, CCUs and other live equipment over IP without time-consuming reconnection of cables. This reduces the quantity of live equipment needing to be kept at each site, allowing resources to be shared efficiently.

### **Power supply from CCU**

The HDCE-RX30 draws power directly from the connected camera control unit.

### **HD 4x HFR capability (PAIR MODE)**

HD 4x HFR output is available with HDC-3500 optical fiber studio camera with HZC-QFR50 HD4x software license. The HDCU-3500 support HD4x SDI output as standard, HD4x IP output with HKCU-SFP50 IP option.

## 4K Upgrade option (PAIR MODE)

4K IP output is available via an optional software license HZCU-UHD35 in the HDCU-3500 with HDC-3500/3100 and HDC-2500 series optical fiber studio cameras. No software license required for IP HDCE.

## MENU setting from web browser

The IP HDCE support menu control from web browser. The status monitoring of multiple IP HDCE and CCU, setting file import/export and remote firmware update enhance the efficiency and convenience of the operation.

## Specifications

### General

|                    |  |
|--------------------|--|
| Power requirements | AC 240 V, 1.7 A (MAX), DC 12 V, 10 A (MAX), DC 240 V, 1.05 A (MAX) |
|--------------------|--|

|                       |                                     |
|-----------------------|-------------------------------------|
| Operating temperature | -10 °C to +40 °C (14 °F to +104 °F) |
|-----------------------|-------------------------------------|

|                     |                                     |
|---------------------|-------------------------------------|
| Storage temperature | -20 °C to +60 °C (-4 °F to +140 °F) |
|---------------------|-------------------------------------|

|      |                              |
|------|------------------------------|
| Mass | Approx. 4.4 kg (9 lb 8.4 oz) |
|------|------------------------------|

### Input/output connectors

|        |   |
|--------|---|
| CAMERA | - |
|--------|---|

|     |  |
|-----|--|
| CCU | Optical fiber connector (LEMO 3K.93C connector) (x1) |
|-----|--|

|     |                            |
|-----|----------------------------|
| RCP | 8-pin multi-connector (x1) |
|-----|----------------------------|

|                  |   |
|------------------|---|
| LAN-COM          | -   |
| NETWORK TRUNK    | 3G/HD/SD-SDI I/O, BNC (x2), 3G-SDI: SMPTE ST424/425 Level-A/B, 0.8 Vp-p, 75 Ω, 2.970 Gbps/2.967 |
| SDI I/O 1 to 2   | Gbps, HD-SDI: SMPTE ST292, 0.8 Vp-p, 75 Ω, 1.485 Gbps/1.4835 Gbps                               |
| REFERENCE IN/OUT | -   |
| EARPHONE         | -   |
| USB              | USB 2.0 type A, 4-pin (x1)  |
| LAN 1 to 2       | 4-pole mni jack (x1)<br>USB 2.0 type A, 4-pin (x1)<br>SFP+, SFP28, 10GBASE-**,<br>25GBASE-**    |

## Input connectors

|           |                                      |
|-----------|--------------------------------------|
| AC IN     | -                                    |
| DC IN     | XLR type 4-pin (x1), 10.5 to 17 V DC |
| SDI RET 1 | -                                    |

## Output connectors

3G/HD-SDI OUTPUT, BNC (x1), 3G-SDI: SMPTE ST424/425 Level-A/B,

|           |   |
|-----------|---|
| SDI OUT 1 | 0.8 Vp-p, 75 Ω, 2.970 Gbps/2.967 Gbps, HD-SDI: SMPTE ST292, 0.8 Vp-p, 75 Ω, 1.485 Gbps/1.4835 Gbps<br>3G-SDI/HD-SDI/SD-SDI, character signal selectable |
|-----------|---|

## Supplied accessories

|                      |   |
|----------------------|---|
| Supplied accessories | Before Using this Unit (1),<br>Operating Instructions (CD-ROM)<br>(1) |
|----------------------|---|

## Optional accessories

|                      |  |
|----------------------|--|
| Optional accessories | HZCE-CNFG50 Configuration<br>Control software, HZCE-SNMP50<br>SNMP Agent software, service<br>manual |
|----------------------|--|

## Related products



### **HZCE-SNMP50**

SNMP license for HDCE-TX30/HDCE-RX30



### **HZCE-CNFG50**

Ember+ license for HDCE-TX30/HDCE-RX30



### **HDCE-TX30**

IP camera extension adaptor for remote live production (transmitter)



### **HDC-1700**

Multi format HD portable system camera



## HDC-2400

3G multi format HD system camera



## HDC-2500

3G double-speed multi format HD system camera



## HDC-3100

Three 2/3-inch CMOS sensors portable system camera for fibre operation



## HDC-3500

Three 2/3-inch 4K CMOS sensors portable system camera for fibre operation

## Gallery

