

ECM-166BC

Uni-directional lavalier
Electret condenser
microphone



Overview

Black coloured uni-directional electret condenser lavalier microphone supplied with a Sony 4-pin connector (SMC9-4P), for use with the WRT-8B/822B Sony bodypack transmitter.

- Resistant to howling by rejecting indirect sound
- Reasonably priced lavalier microphone ideal for institutional use and sound-contracting applications such as speeches, lectures and conferences

Specifications

Audio Section

Capsule Type	Electret Condenser
Frequency Response	100 Hz to 10 kHz
Directivity	Uni-directional
Sensitivity *[1]	-45 dB (5.6 mV) \pm 3 dB
Output Impedance *[2]	2.5k Ω \pm 30%, Unbalanced

Dynamic Range	96 dB or more
Signal-to-Noise Ratio *[3]	60 dB or more
Inherent Noise *[4]	34 dB SPL or less
Maximum Input Sound Pressure Level *[5]	130 dB SPL

General Section

Connector	BC type. Supplied with Sony 4-pin (SMC9-4P) connector
Mic Cable	3.9 feet 1.2 m
Power Requirements	DC 1.1 V to 10.0V
Power Consumption	0.4 mA or less
Dimensions *[6]	φ12.7 X 23.8 mm (Mic head) φ1/2 X 15/16 inches (Mic head)
Mass	Approx. 28.3 g Approx. 1 oz
Supplied Accessories	Urethane type windscreen (1) Single/horizontal type tie clip (1) Operating instructions (1)

Notes

Note	<ul style="list-style-type: none">*[1] 0 dB = 1 V/Pa, at 1 kHz*[2] Output impedance at 1 kHz*[3] A-weighted, 1 kHz, 1 Pa.*[4] 0dB SPL = 20? Pa.*[5] 0 dB SPL = 20? Pa.*[6] The values for dimensions are approximate.
------	--

Gallery

