

## ECM-HZ1UBMP

DWZ Series digital wireless uni-directional electret condenser lightweight headset microphone



### Overview

#### **High quality headset microphone ideal for presenters and vocalists**

The ECM-HZ1UBMP works with the ZTX-B02RC body-pack transmitter and is supplied with the DWZ-B70HL package. The lightweight headset keeps you comfortable and stress-free even when wearing it for long periods of time. The ear-clip-style design allows you to wear it on either your left or right ear.

### Specifications

#### Audio Section

Capsule Type	Electret Condenser
Frequency Response	60 Hz to 18 kHz
Directivity	Uni-directional
Sensitivity *[1]	-31.0 dB $\pm$ 3.0 dB
Output Impedance * [2]	1.4 k $\Omega$ $\pm$ 30% (unbalanced)
Dynamic Range (typ.)	94 dB or more

Signal-to-Noise Ratio (typ.) *[3]	68 dB or more
Inherent Noise (typ.) *[4]	28 dB SPL or less
Maximum Input Sound Pressure Level (typ.) *[5]	120 dB SPL

## General Section

Mic Cable	1.2 m (3.9 feet)
Power Requirements	DC 1.5 V to 10 V
Dimensions *[6]	15 diameter (capsule case) x 170 mm (19/32 diameter x 6 3/4 inch)
Mass (microphone body, excluding cable)	10 g (0.35 oz) without connector
Supplied Accessories	Headband (1), Cord clip (1), Windscreen (1), Operating instructions (1)
Optional Accessories	Windscreen AD-RX7B

## Notes

\*[1] 0 dB = 1 V/Pa, at 1 kHz

## Notes

\*[2] Output impedance at 1 kHz

\*[3] A-weighted, 1 kHz, 1 Pa.

\*[4] 0 dB SPL = 20  $\mu$ Pa.

\*[5] 0 dB SPL = 20  $\mu$ Pa.

\*[6] The values for dimensions are approximate.

---

## Gallery

