

## FWD-32WE615/T

32" BRAVIA HD Ready LED  
Professional Display



### Overview

#### **The display that's designed for business**

Present a clear, professional image with the FWD-32WE615/T 32" BRAVIA Professional Display. It's the superior way to get your message across, with crisp HD ready picture quality, advanced controls and reliable operation.

With advanced control, Simple Pro Mode and optional interactive compatibility, it makes it easy to create attractive digital signage so you always present a clear image.

Enrich your audience's display experience with seamless integration with Manage for TEOS and a choice of built-in solutions to add extra functionality, from meeting room support to automation.

For even greater peace of mind there's the added reassurance of our 3 Year Advanced Exchange PrimeSupport service. If there's a problem with your display, we'll offer a free, brand new replacement product rather than repair included as standard. You can also choose to extend your service by 2 additional years.

### Features

#### **See finer detail**

X-Reality™ PRO picture processing analyses every frame,

matching scenes with our special image database to refine images and reduce noise.

### **Smoother movement**

Motionflow XR inserts additional picture frames between the originals, ensuring smoother, sharper detail in fast-moving sequences.

### **TEOS Integration**

BRAVIA integrates seamlessly with the Manage for TEOS, that orchestrates the control of devices and content in boardrooms, meeting areas and public spaces.

*TEP-X96 player required.*

### **Flexible mounting and installation**

BRAVIA offers flexible mounting options with VESA standard mounting for easy integration into a wide range of environments.

### **Quick set-up with Pro Mode**

Customise and store display settings and features, then copy them easily to multiple displays via USB flash memory.

### **Greater peace of mind**

There's extra reassurance with our 3 Year Advanced Exchange PrimeSupport service that's included as standard. If there's a fault with your BRAVIA Professional Display, we'll provide a replacement unit at no extra charge to keep you up and running.

## Specifications

### Display Features

Brightness (cd/m<sup>2</sup>) 350

Native Contrast Ratio 1500:1

Dynamic Contrast Ratio	300000:1
Response Time (ms)	8
Dimming Type	Frame Dimming
Display Device	LCD
Backlight Type	Edge LED
Bezel Size (Top, Side, Bottom)	11.4/12/18.9
Operation Time	18/7

## Display Specifications

Screen Size for WEB (diagonal, cm, integer or 1st decimal)	80.0 cm
Backlight Type	Edge LED
Display Resolution (H x V, pixels)	1366 x 768
Screen Size (inch, measured diagonally)	32" (31.5")
Aspect Ratio	16:9

## Professional Features

Professional Hidden Mode	Yes
HDMI Auto Wake-Up	Yes
Multicast/IPTV	Yes
Compatible with TDM Digital Signage/TEOS Solutions	Yes (Requires TEP-X96 player)
Operating System	Linux
On-board Storage (GB)	4GB

## Display System

TV System (Digital Terrestrial)	DVB-T/T2
TV System (Digital Cable)	DVB-C
TV System (Digital Sat)	DVB-S/S2
Number of Tuners (Terrestrial/Cable)	1 (Digital/Analog)
Number of Tuners (Sat)	1

---

## Network Features

Wi-Fi Direct	Yes
--------------	-----

---

Wi-Fi Certified	Yes
-----------------	-----

---

Internet Browser	VEWD
------------------	------

---

## Convenience features

USB

Playback Codecs	MPEG1/MPEG2PS/MPEG2TS/AVCHD/MP4Part10/MP4Pa
-----------------	---

---

HDMI-CEC	Yes
----------	-----

---

Sleep Timer	Yes
-------------	-----

---

On/Off Timer	Yes
--------------	-----

---

Display Language	BUL/CAT/CZE/DAN/GER/GRE/ENG/SPA/EST/FIN/FRE/H
------------------	---

---

## Control Specs

IP Control	Yes
------------	-----

---

Pro Mode	Yes (Basic)
----------	-------------

## Inputs & Outputs

HDCP	HDCP 1.4
------	----------

RF (Terrestrial/Cable) Connection Input(s)	1 (Side)
--	----------

IF (Satellite) Input(s)	1 (Side)
-------------------------	----------

HDMI inputs total	2 (Side)
-------------------	----------

Audio Output(s)	1 (Side Hybrid with Headphone Out, Audio Out and Subwoofer Out)
-----------------	---

USB Ports	2 (Side/Stacking)
-----------	-------------------

Ethernet Inputs	1 (Rear)
-----------------	----------

## Audio Specifications

Speaker Type	Open Baffle Speaker
--------------	---------------------

Audio Power Output	5W + 5W
--------------------	---------

## Video Specifications

Video Processing	X-Reality PRO
------------------	---------------

Motion Enhancer	Motionflow XR 400Hz (Native 50Hz)
-----------------	-----------------------------------

---

HDR (High Dynamic Range) compatibility	Yes (HDR10, HLG) *1
--	---------------------

---

## Design Features

Cable Management	Yes
Frame color	Black
Stand Design	Black U Slate
VESA® Hole Spacing Compatible	Yes
VESA® Hole Pitch(W x H)	10.0 x 20.0 cm

---

## Eco & Energy Saving

Energy Label Rating	A
On mode power consumption	Standard: 41.0W
Power Consumption (in Standby)	0.50W
Peak luminance ratio for EU	68%
Mercury content(mg)	0.0

---

Power Saving Mode / Back Light Off Mode	Yes
--	-----

---

Power Requirements (voltage)	DC 19.5V
---------------------------------	----------

---

Power consumption(Networked Standby)	2.00W (Wi-Fi) / 2.00W (LAN)
--	-----------------------------

## Dimensions

---

Display only (W x H x D)	Approx. 73.1 x 44.2 x 7.0 cm
-----------------------------	------------------------------

---

Display with Stand (W x H x D)	Approx. 73.1 x 49.0 x 18.7 cm
-----------------------------------	-------------------------------

## Weights (Approx.)

---

Display only	Approx. 5.8 kg
--------------	----------------

---

Display with Stand	Approx. 6.2 kg
--------------------	----------------

---

Package Carton(Gross)	Approx. 9 kg
--------------------------	--------------

## Optional Accessories

SU-WL450 (Terminal access)



Wallmount Bracket	limitation depends on country selection)
-------------------	--

---

## PrimeSupport

Included PrimeSupport	3 years of Standard helpdesk (Mon-Fri 9:00-18:00 CET) and Advanced Replacement service in case of product fault with all logistics covered.
-----------------------	---

---

Optional PrimeSupport Extensions	Optional 2-year support extension available: PSP.FW6G-32.2X
----------------------------------	--

---

## Gallery

