

FWD-49X80H/T

49" BRAVIA 4K Ultra HD HDR
Professional Display



Overview

High quality 4K HDR images and smart connectivity

Take your business communications to the next level with the FWD-49X80H/T BRAVIA Professional Display that combines lifelike 4K HDR image quality with easy operation, flexible networking/control and extensive integration options.

Optimised for professional applications, the FWD-49X80H/T BRAVIA Professional Display delivers richly coloured, high-contrast 4K HDR images, while 4K X-Reality PRO upscales lower-resolution images closer to true 4K quality.

The display's clean, minimal design keeps your audience focused on what really matters, while Dolby Atmos delivers pure, immersive sound.

Enrich your audience's display experience with seamless TEOS integration and a choice of built-in solutions to add extra functionality, from meeting room support to automation, with no need for any external devices or players.

With advanced control, Pro Mode, optional interactive compatibility and an embedded HTML5 platform, it makes it easy to create attractive digital signage so you always present a

clear image.

For even greater peace of mind there's the added reassurance of our 3 Years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible. You can also choose to extend your support for an additional 2 years.

Features

4K image resolution (3840 x 2160 pixels)

4K offers four times the detail of Full HD, with a resolution of over 8 million pixels bringing extra clarity to corporate display, education and digital signage applications.

More contrast, colour and clarity

Our 4K HDR Processor X1™ cleans and refines picture signals, using advanced algorithms to cut noise and boost detail. Even lower-resolution images are upscaled closer to 4K with lifelike colour and textures, for a more impactful signage.

See finer detail

4K X-Reality PRO upscales pictures closer to true 4K quality. Images are sharpened and refined in real time, revealing extra detail from lower-resolution picture sources.

Wider colour with TRILUMINOS Display

Powered by our X1 processor, TRILUMINOS Display maps colours from a wider palette, faithfully reproducing a world of more vivid, lifelike hues and tones.

Smoother movement

Motionflow XR inserts additional picture frames between the originals, ensuring smoother, sharper detail in fast-moving sequences.

Refined style to match your space

BRAVIA features a slim, contemporary blade design, with a

narrow screen bezel that adds an extra touch of refinement to any interior.

Do more with Android TV

Discover a world of apps and online content powered by Android. Use Voice Search to find content easily without typing.

Google Chromecast built-in and Apple Airplay

With Google Chromecast built-in, and Apple Airplay, easily mirror your content and enjoy it on your BRAVIA.

Quick set-up with Pro Mode

Customise and store display settings and features, then copy easily to multiple displays via USB flash memory.

Easily create digital signage

Integrated support for HTML5 makes it easy to produce compelling digital signage. Combine graphics, text, video and live web content to create attractive signage in minutes with no extra hardware or special training.

Versatile remote control

Control BRAVIA remotely – including on/off, input signal select and adjust volume – over IP via RJ45 by web API.

TEOS integration

BRAVIA integrates seamlessly with TEOS, Sony's suite of workspace management applications that orchestrate control of devices and content in boardrooms, meeting areas and public spaces.

Greater Peace of Mind

There's the added reassurance of our 3 Years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible. You can also choose to extend your support for an additional 2 years.

Specifications

Display Features

Brightness (cd/m ²)	430
Native Contrast Ratio	1100:1
Dynamic Contrast Ratio	390000:1
Response Time (ms)	4.8
Panel Type	IPS
Dimming Type	Frame Dimming
Display Device	LCD
Bezel Size (Top, Side, Bottom)	11.4 / 11.4 / 18.6
Operation Time	18/7

Display Specifications

Screen Size for WEB (diagonal, cm, integer or 1st decimal)	123 cm
Backlight Type	Edge LED
Display Resolution (H x V, pixels)	3840 x2160

Screen Size (inch, measured diagonally)	49" (48.5")
Viewing Angle (Right/Left)	178 (89/89) degree
Viewing Angle (Up/Down)	178 (89/89) degree
Display Resolution	QFHD
Aspect Ratio	16:9

Professional Features

Professional Hidden Mode	Yes
HDMI Auto Wake-Up	Yes
Multicast / IPTV	Yes
Compatible with TDM Digital Signage / TEOS Solutions	Yes
Operating System	Android 9.0 Pie
On-board Storage (GB)	16GB

Display System

TV System (Digital Terrestrial)	DVB-T/T2
TV System (Digital Cable)	DVB-C
TV System (Digital Sat)	DVB-S/S2
Number of Tuners (Terrestrial/Cable)	1 (Digital/Analog)
Number of Tuners (Sat)	1

Network Features

Wi-Fi Direct	Yes
Wi-Fi Certified	Yes
Apple AirPlay	Yes
Chromecast Built-in	Yes
Internet Browser	VEWD
Wireless LAN	Integrated

Convenience Features

USB Playback Codecs	MPEG1:MPEG1 / MPEG2PS:MPEG2 / MPEG2TS(HDV,AVCHD) MP4AAC / FLAC / JPEG
---------------------	--

HDMI-CEC	Yes
----------	-----

i-Manual	Yes
----------	-----

On Screen Clock	Yes
-----------------	-----

Sleep Timer	Yes
-------------	-----

On/Off Timer	Yes
--------------	-----

Display Language	AFR,AMH,ARA,ASM,AZE,BEL,BUL,BEN,BOS,CAT,CZE,DAN,DEU,ENG,ESP,FIN,FRN,GER,GRK,HUN,ITA,JAP,KOR,LAT,LTU,LUX,NLD,NOR,POR,ROM,RUS,SRB,SWE,SWH,TUR,UKR,URD,VIE,VIS,WAL,XHO,ZUL
------------------	---

Control Specs

IP Control	Yes
------------	-----

Pro Mode	Yes
----------	-----

Inputs & Outputs

4096 x 2160p (24,50,60 Hz), 3840 x

HDMI Signal	2160p (24,25,30,50,60 Hz), 1080p (30,50,60 Hz), 1080/24p, 1080i (50,60 Hz), 720p (30,50,60 Hz), 720/24p, 576p, 480p
HDCP	HDCP2.3 (for HDMI 1/2/3/4)
AC Power Input	AC ADAPTER
RF (Terrestrial/Cable) Connection Input(s)	1 (Side)
IF (Satellite) Input(s)	1 (Side)
Composite Video Input(s)	1 (Bottom)
HDMI Inputs total	4 (3 Side, 1 Bottom)
USB Ports	2 (Side)
Ethernet Inputs	1 (Bottom)
PCMCIA Slot(s)	1 (Top)

Audio Specifications

Speaker Position	Down Firing
Audio Power Output	10W + 10W

Video Specifications

Wide Mode	Auto / Wide zoom / Normal / Full / Zoom / 14:9
4:3 Default	Yes
Video Processing	4K X-Reality PRO
Motion Enhancer	Motionflow XR 400Hz (Native 50Hz)
4K Processor	X1 4K HDR Processor
HDR (High Dynamic Range) compatibility	Yes (HDR10, HLG, Dolby Vision)
Panel Refresh Rate (Native Hertz)	50Hz

Design Features

Cable Management	Yes
Frame Colour	Black
Stand Design	Slim Blade Stand
VESA® Hole Spacing Compatible	Yes
VESA® Hole Pitch (W x H)	20.0 x 20.0 cm

Eco & Energy Saving

Energy Label Rating	A
On-mode Power Consumption	74.0W
Standby Power Consumption	0.50W
Peak Luminance Ratio for EU	71%
Mercury Content (mg)	0.0
Power Saving Mode / Back Light Off Mode	Yes
Power Requirements (voltage)	AC 220-240V, 50Hz DC 19.5V
Power Consumption (Networked Standby)	2.00W (Wi-Fi) / 2.00W (LAN) / 1.00W (Bluetooth)

Dimensions

Display Only (W x H x D)	Approx. 110.1 x 64.5 x 5.7 (1.30) cm
Display with Stand (W x H x D)	Approx. 110.1 x 70.4 x 28.6 cm

Weights (Approx.)

Display Only	Approx. 11.6 kg
--------------	-----------------

Display with Stand	Approx. 12.1 kg
--------------------	-----------------

Package Carton (Gross)	Approx. 17 kg
---------------------------	---------------

Optional Accessories

Wallmount Bracket	SU-WL450 (Terminal access limitation, refer to SU-WL450 product page)
-------------------	---

PrimeSupport

Included PrimeSupport	3 years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible.
-----------------------	---

Optional PrimeSupport Extensions	Optional 2-year support extension available: PSP.FDWXH49.2X
----------------------------------	---

Gallery

