

FWD-65X95K

65" Bravia 4K HDR Professional Displays

Overview

Take your business to a whole new level with the FWD-65X95K Professional BRAVIA display that unites exquisite pictures and sound in our finest 4K HDR professional display, and a premium flush design that keeps your audience focused on your message without distractions.

Optimised for professional applications, the FWD-65X95K BRAVIA is powered by the ingenious Cognitive Processor XR™ that takes vision and sound to a whole new level by boosting colour, contrast, clarity, and motion. Enjoy exceptional contrast from a 4K Mini LED screen that delivers dynamic range like never before. See incredibly deep blacks, dazzling lights and beautifully natural mid tones.

For even greater peace of mind there's the added reassurance of our 3 Years warranty with advanced exchange handled by local partner, on premise where possible. You can also choose to extend your support for an additional 2 years.

Features

4K Image Resolution (3840 x 2160 pixels)

4K offers four times the detail of Full HD, with a resolution of over 8 million pixels bringing extra clarity to corporate display, education, and digital signage applications.

Beautifully Realistic 4K HDR Images

Our revolutionary cognitive Processor XR™ HDR remaster, 4K XR Super Resolution, XR Contrast booster and more, making you appreciate the difference with enhanced depth, more realistic

textures, and pure, natural colours at higher brightness levels.

Unique dynamic range with the 4K Mini LED screen

Our XR Backlight Master Drive utilises a unique local dimming algorithm to divide the tiny and high-dense Mini LED backlight into small LED units, precisely and independently controlling each unit, focusing light for maximum brightness, and displaying an unprecedented dynamic range with scenes full of incredibly deep blacks, dazzling lights and natural mid tones.

See Finer Detail

XR 4K Upscaling takes 2K pictures closer to true 4K quality. Images are sharpened and refined in real time, revealing extra detail from lower-resolution picture sources.

Clearer, Brighter Fast-moving Scenes

Our Cognitive Processor XR™ with XR Motion Clarity™ analyses motion across several frames to ensure action stays smooth, bright, and clear.

Wider Colour with XR TRILUMINOS Pro™

Powered by our Cognitive Processor XR™, XR TRILUMINOS Pro™ enables X95K to access over a billion colours and reproduce each one with the subtle differences seen in the real world. Together with our wide colour gamut panel and human-centric processor, it can detect colour from saturation, hue, and brightness to deliver natural shades in every detail.

Flush Surface, No Distractions

BRAVIA Professional Displays feature a slim, flush design with discrete stand and thin bezel that keeps you focused on what's important - the picture.

Google Chromecast and Apple Airplay

With Google Chromecast built-in, and Apple Airplay, easily mirror your content and enjoy it super-sized on your BRAVIA.

Do More with Android TV

Discover a world of apps and online content powered by Android TV. Use Voice Search to find content easily without typing. Easily share content with Google Cast.

Flexible Mounting and Installation

BRAVIA Professional Displays offer flexible mounting options with VESA standard mounting for easy integration into a wide range of environments.

Greater peace of mind

There's the added reassurance of our 3 Years warranty with advanced exchange handled by local partner, on premise where possible. You can also choose to extend your support for an additional 2 years.

Specifications

| Display features | |
|---------------------------------|---------------|
| Brightness (cd/m ²) | 730 |
| Native contrast ratio | 2,800:1 |
| Dynamic contrast ratio | 700000:1 |
| Response time | 8 |
| Panel type | VA |
| Backlight dimming type | Local Dimming |
| Display type | LCD |

Display specifications

Screen Size for
WEB(diagonal, cm, integer or 1st decimal) 164 cm

Backlight type Direct(Full Array Mini LED)

Display resolution (H x V, pixels) 3840 x 2160

Screen Size (inch, measured diagonally) 65"(64.5")

Viewing Angle (Right/Left) 178(89/89)degree

Viewing Angle (Up/Down) 178(89/89)degree

Display Resolution QFHD

Aspect Ratio 16:09

Professional features

Operating System Android 10

On-board Storage (GB) 16GB

Display system

| | |
|--------------------------------------|----------------------|
| TV System (Digital Terrestrial) | DVB-T/T2 |
| TV System (Digital Cable) | DVB-C |
| TV System (Digital Sat) | DVB-S/S2 |
| Number of Tuners (Terrestrial/Cable) | 2(Digital)/1(Analog) |
| Number of Tuners (Sat) | 2 |

Network features

| | |
|---------------------|------------|
| Apple AirPlay | Yes |
| Wi-Fi Direct | Yes |
| Wi-Fi Certified | Yes |
| Chromecast built-in | Yes |
| Internet Browser | Vewd |
| Wireless LAN | Integrated |

Convenience features

| | |
|---------------------|--|
| USB playback codecs | MPEG1:MPEG1/MPEG2PS:MPEG2/MPEG2TS(HDV,AVCHD) |
|---------------------|--|

| | |
|----------|-----|
| HDMI-CEC | Yes |
|----------|-----|

| | |
|----------|-----|
| i-Manual | Yes |
|----------|-----|

| | |
|-----------------|-----|
| On Screen Clock | Yes |
|-----------------|-----|

| | |
|-------------|-----|
| Sleep Timer | Yes |
|-------------|-----|

| | |
|--------------|-----|
| On/Off Timer | Yes |
|--------------|-----|

| | |
|------------------|---|
| Display Language | AFR,AMH,ARA,ASM,AZE,BEL,BUL,BEN,BOS,CAT,CZE,DAN |
|------------------|---|

Control specs

| | |
|------------|-----|
| IP Control | Yes |
|------------|-----|

| | |
|----------|----|
| Pro Mode | No |
|----------|----|

Inputs & outputs

4096x2160p(24,50,60Hz),

| | |
|---|---|
| HDMI Signal | 3840x2160p(24,25,30,50,60,100,120Hz) *1 , 1080p(30,50,60,100,120Hz), 1080/24p, 1080i(50,60Hz), 720p(30,50,60Hz), 720/24p, 576p, 480p |
| HDCP | HDCP2.3(for HDMI1/2/3/4) |
| AC Power Input | Pigtail (REAR) |
| RF (Terrestrial/Cable) Connection Input(s) | 1(Bottom) |
| IF (Satellite) Input(s) | 2(Bottom) |
| Composite Video Input(s) | Hybrid w/S-Center Speaker Input x1(Side, Mini jack) |
| HDMI inputs total | 4(1Side,3Bottom) |
| Digital Audio Output(s) | 1 (Bottom) |
| USB ports | 1(Side)/1(Bottom) |
| Ethernet inputs | 1(Bottom) |
| PCMCIA Slot(s) | 1(side) |

Audio Specifications

| | |
|------------------------------------|---|
| Speaker Position | Front + Side Back |
| Audio Power Output | 10W + 10W + 10W + 10W + 10W + 10W |
| Digital audio out (Optical) format | Two channel linear PCM: 48kHz 16bits, Dolby Audio, DTS |
| HDMI Audio Return Channel(ARC) | Yes (eARC/ARC) |
| HDMI input Audio format | 5.1 channel linear PCM: 32/44.1/48/88.2/96/176.4/192kHz 16/20/24bits, Dolby Audio, Dolby Atmos, DTS |
| ARC output format | Two channel linear PCM: 48kHz 16bits, Dolby Audio, Dolby Atmos, DTS |

Video specifications

| | |
|------------------|---|
| Wide Mode | Wide zoom/Normal/Full/Zoom/14:9,Normal/Full1/Full2 for PC |
| 4:3 Default | Yes |
| Video Processing | XR 4K Upscaling |
| Motion | XR Motion Clarity, Auto mode |

enhancer

4K Processor Cognitive Processor XR

HDR (High Dynamic Range) compatibility Yes(HDR10,HLG,Dolby Vision)

Panel Refresh Rate (Native Hertz) 100Hz

Dynamic Contrast Enhancer Yes

Design Features

Stand Position 3way position (Standard position/Narrow position/Soundbar position)

Stand Color Titanium Silver

Bezel Design Seamless Edge

Cable Management Yes

Frame color Titanium Silver

| | |
|--------------------------------------|--|
| Stand Design | Aluminum Edge Stand |
| VESA® Hole Spacing Compatible | Yes |
| VESA® Hole Pitch(W x H) | 30.0 x 30.0 cm |
| Eco & energy saving | |
| On mode power 1000h SDR(New lot5) | 113 kWh/1000h |
| Mercury content(mg) | 0.0 |
| Power Requirements (voltage) | 220 V - 240 V AC |
| Power Requirements (frequency) | 50Hz |
| Rated Power Consumption | 380 W |
| Power Consumption (in Standby) | 0.50 W |
| Power consumption(Networked Standby) | 2.00W(Wi-Fi) / 2.00W(LAN) / 0.50W(CEC) |
| Power Saving Mode / | Yes |

Back Light Off Mode

Dimensions

| | |
|--------------------------|--------------------------------------|
| Display only (W x H x D) | Approx. 144.3 x 83.5 x 6.0 (3.64) cm |
|--------------------------|--------------------------------------|

| | |
|---|--------------------------------|
| Display with Stand (Standard position) (W x H x D) | Approx. 144.3 x 84.6 x 34.3 cm |
|---|--------------------------------|

| | |
|---|--------------------------------|
| Display with Stand (Narrow position) (W x H x D) | Approx. 144.3 x 85.9 x 34.3 cm |
|---|--------------------------------|

| | |
|---|--------------------------------|
| Display with Stand (Soundbar position) (W x H x D) | Approx. 144.3 x 90.7 x 34.3 cm |
|---|--------------------------------|

| | |
|--|--------------------------------|
| Dimension of Package Carton (W x H x D) | Approx. 157.4 x 97.2 x 20.0 cm |
|--|--------------------------------|

Weights (Approx.)

| | |
|--------------|-----------------|
| Display only | Approx. 32.1 kg |
|--------------|-----------------|

| | |
|---|---------------|
| Display with Stand (Standard position) | Approx. 33 kg |
|---|---------------|

| | |
|---|---------------|
| Display with Stand (Narrow position) | Approx. 33 kg |
|---|---------------|

| | |
|---|---------------|
| Display with Stand (Soundbar position) | Approx. 33 kg |
|---|---------------|

| | |
|------------------------------------|---------------|
| Weight of Package Carton(Gross) | Approx. 43 kg |
|------------------------------------|---------------|

Supplied Accessories

Voice

| | |
|-------------------------------|------------|
| Remote Control (Supply) | RMF-TX900U |
|-------------------------------|------------|

| | |
|-------------------|------------|
| Remote Control | RMT-TX440E |
|-------------------|------------|

| | |
|-----------|----------|
| Batteries | LR03+R03 |
|-----------|----------|

| | |
|-----------------------|--|
| AC Power Cord Spec | (Pig-tail43mm) (EUROPE) (2pin) (round pins Type C) |
|-----------------------|--|

| | |
|---------------------------|--|
| Operating Instructions | GB,FR,ES,NL,DE,PT,IT,SE,DK,FI,NO,PL,CZ,SK,HU,RO,BG |
|---------------------------|--|

| | |
|--|--|
| Quick Setup Guide / Supplement CUE (GA) | GB,FR,ES,NL,DE,PT,IT,DK,NO,SE,FI,PL,CZ,SK,HU,RO,BG |
|--|--|

| | |
|--------------------|-----------------------------|
| Table Top Stand | Separate(assembly required) |
|--------------------|-----------------------------|

Optional Accessories

| | |
|-------------------|--|
| Wallmount Bracket | SU-WL450(Terminal access limitation, refer to SU-WL450 product page), SU-WL850(Refer to Country/Area Handling Chart) |
|-------------------|--|

PrimeSupport

| | |
|-----------------------|--|
| Included PrimeSupport | 3 Years warranty with advanced exchange handled by local partner, on premise where possible. |
|-----------------------|--|

Notes

| | |
|----|--|
| *1 | 100Hz and 120Hz is supported by HDMI IN 3 and IN 4 |
|----|--|
