

## PDW-HD1500

XDCAM HD422 Professional Disc recorder up to 50 Mb/s



### Overview

The XDCAM production system was first introduced in 2003, offering revolutionary file-based acquisition onto optical Professional Disc. In 2005, XDCAM HD was launched with camcorders and decks recording high definition pictures at up to 35 Mb/s onto the same 23 GB Professional Discs.

At IBC 2007, Sony demonstrated the latest development of products to expand of the XDCAM HD line up - the PDW-700 camcorder and the PDW-HD1500 deck.

The PDW-HD1500 will record and replay XDCAM HD 50 Mb/s 4:2:2 data onto 50 GB Dual-layer Professional Disc. With interfaces including i.LINK and Ethernet, the PDW-HD1500 can operate at the heart of small or large scale file-based networked systems. VTR-like JOG/shuttle operation and video interfaces including HD-SDI and SD-SDI also makes the PDW-HD1500 ideal for operation in more traditional vide-based installations.

The PDW-HD1500 has been designed to increase the appeal of XDCAM HD for high-end applications such as drama, documentary and natural history and for mainstream entertainment programmes that required a prestige quality look.

File-based acquisition onto Professional Disc, with thumbnail and proxy operation will also make the PDW-HD1500 ideal for

networked applications where speed of production is a critical.

## Features

**High definition recording using MPEG-2 422P@HL compression at 50Mb/s data rate**

**Support for existing XDCAM HD and XDCAM SD formats**

**8 channels of digital audio**

**Dual-layer Disc (50GB) and Single-layer Disc (23.3GB) support**

**Dual optical pick-up for higher speed file transfer**

**4.3-inch colour LCD**

**VTR-like JOG/SHUTTLE operation**

**TBC control (via front panel and remote)**

**Compact and lightweight at 6.3kg and half-rack width**

**AC, DC or battery powered**

**Built-in up/down converter and 1080/720 cross converter**

**HD up-conversion from SDI input (recording)**

**HD/SD conversion and cross conversion output between 1080 and 720 (playback)**

**Ethernet interface (100Base-T)**

**i.LINK interface**

## Specifications

### General

Power Requirements	AC 100 V to 240 V, 50/60 Hz, DC 12 V
Power Consumption	AC: 80 W, DC: 65 W, SAVEMODE (DC): 55 W
Operating Temperature	5°C to 40°C 42°F to 104°F
Storage Temperature	-20°C to +60°C -4°F to +140°F
Humidity	25% to 90% (relative humidity)
Mass	6.5 kg 14 lb 5 oz
Dimensions (W x H x D) *1	210 x 132 x 396 mm (excluding protrusions) 8 3/8 x 5 1/4 x 15 5/8 inches (excluding protrusions)
Recording/Playback Format (Video)	MPEG HD422 (CBR, 50 Mbps) MPEG HD: - HQ mode (VBR, maximum bit rate: 35 Mbps) - SP mode (CBR, 25 Mbps) - LP mode (VBR, maximum bit rate: 18 Mbps) *2 MPEG IMX *3 (CBR, 50/40/30 Mbps) DVCAM *3 (CBR, 25 Mbps)

Recording/Playback Format (Audio)	MPEG HD422: 8 ch/24 bits/48 kHz MPEG HD: 4 ch/16 bits/48 kHz MPEG IMX *3 : 4 ch/24 bits/48 kHz or 8 ch/16 bits/48 kHz DVCAM *3 : 4 ch/16 bits/48 kHz
Recording/Playback Format (Proxy Video)	MPEG-4
Recording/Playback Format (Proxy Audio)	A-law (8 ch/8 bits/8 kHz)
Recording/Playback Time (MPEG HD422)	50 Mbps: Approx. 95 min (PFD50DLA), Approx. 43 min (PFD23A)
Recording/Playback Time (MPEG HD)	35 Mbps, 4-ch audio: More than 145 min (PFD50DLA), More than 65 min (PFD23A) 35 Mbps, 2-ch audio (playback only): More than 150 min (PFD50DLA), More than 68 min (PFD23A) 25 Mbps, 4-ch audio: Approx. 190 min (PFD50DLA), Approx. 85 min (PFD23A) 25 Mbps, 2-ch audio (playback only): Approx. 200 min (PFD50DLA), Approx. 90 min (PFD23A)

	<p>18 Mbps, 4-ch audio (playback only): More than 248 min (PFD50DLA), More than 112 min (PFD23A)</p> <p>18 Mbps, 2-ch audio (playback only): More than 265 min (PFD50DLA), More than 122 min (PFD23A)</p>
Recording/Playback Time (MPEG IMX)	<p>50 Mbps: Approx. 100 min (PFD50DLA), Approx. 45 min (PFD23A)</p> <p>40 Mbps: Approx. 120 min (PFD50DLA), Approx. 55 min (PFD23A)</p> <p>30 Mbps: Approx. 150 min (PFD50DLA), Approx. 68 min (PFD23A)</p> <p>Optional PDBK-S1500 hardware key is required for MPEG IMX recording.</p>
Recording/Playback Time (DVCAM)	<p>25 Mbps: Approx. 185 min (PFD50DLA), Approx. 85 min (PFD23A) *3</p>
Search Speed Range (Shuttle Mode)	-20 times to +20 times normal speed
Search Speed Range	

(Variable Mode) -2 times to +2 times normal speed

---

Search Speed Range (Jog Mode) -1 time to +1 time normal speed

---

Search Speed Range (Fast Forward/Reverse) -35/+35 times normal speed

## Media Drive

---

Media Type Professional Disc Drive (x1)

## Input/Output

---

Reference Input BNC (x2) (including loop-through), HD Tri-level sync (0.6 Vp-p/75 Ω/negative) or SD blackburst/composite sync (0.286 Vp-p/75 Ω/negative)

---

HD-SDI Input BNC (x1) (HD/SD switchable)  
 HD-SDI: SMPTE 292M (w/embedded audio)  
 SD-SDI: SMPTE 259M (w/embedded audio)

---

XLR-type 3-pin (female) (x2)

Analog Audio Input	(channel selectable), +4/0/-3/-6 dBu (selectable), 10 k $\Omega$ , balanced
Digital Audio Input (AES/EBU)	BNC (x2), 4 ch (2 ch each, 1/2 ch and 3/4 ch), AES-3id-1995
Timecode Input	BNC (x1), SMPTE timecode, 0.5 Vp-p to 18 Vp-p/3.3 k $\Omega$ /unbalanced
Analog Composite Output	BNC (x2), 1: 1.0 Vp-p/75 $\Omega$ /negative, SMPTE 170M 2: 1.0 Vp-p/75 $\Omega$ /negative, SMPTE 170M, character On/Off
HD-SDI Output	BNC (x2), 1: SMPTE 292M (w/embedded audio) 2: SMPTE 292M (w/embedded audio), character on/off
SD-SDI Output	BNC (x2), 1: SMPTE 259M (w/embedded audio) 2: SMPTE 259M (w/embedded audio), character on/off
Analog Audio Output	XLR-type 3-pin (male) (x2) (channel selectable), +4/0/-3/-6 dBu (selectable), 600 $\Omega$ , Lo-z, balanced

Analog Audio Monitor	XLR-type 3-pin (male) (x2), +4 dBu, 600 $\Omega$ , Lo-Z, balanced
Digital Audio Output (AES/EBU)	BNC (x2), 4 ch (2 ch each, 1/2 ch and 3/4 ch), AES-3id-1995
Headphone Output	JM-60 Stereo phone jack (x1), -13 dBu, 8 $\Omega$ , unbalanced
Timecode Output	BNC (x1), SMPTE timecode, 1.0 Vp-p/75 $\Omega$ /unbalanced
Video Control	D-sub 9-pin (female) (x1), EIA RS-423
i.LINK	IEEE 1394 6-pin (x1)* File Access Mode or HDV TS* (1080i/720p) (selectable) *Optional PDBK-201 is required for HDVIN/OUT.
Ethernet	RJ-45 (x1) 1000BASE-T: IEEE 802.3ab 100BASE-TX: IEEE 802.3u 10BASE-T: IEEE 802.3
Remote Input (9-pin)	D-sub 9-pin (female) (x1), RS-422A
DC Input (12 V)	XLR-type 4-pin (male) (x1)
DC Output (12 V)	4-pin (female) (x1), DC 12 V, 7.5 W



Maintenance	USB (x2)
-------------	----------

---

AC Input	AC Input (x1), 100 V to 240 V, 50/60Hz
----------	---

---

## Video Performance

Sampling Frequency	Y: 74.25 MHz, Pb/Pr: 37.125MHz
--------------------	--------------------------------

---

Quantization	8 bits/sample
--------------	---------------

---

Error Correction	Reed Solomon Code
------------------	-------------------

---

## Processor Adjustment Range

Video Level	$-\infty$ to +3 dB
-------------	--------------------

---

Chroma Level	$-\infty$ to +3 dB
--------------	--------------------

---

Set Up/Black Level	-30 IRE to +30 IRE/-210 mV to +210 mV
--------------------	--

---

Chroma Phase	$-30^\circ$ to $+30^\circ$
--------------	----------------------------

---

System Sync Phase	$-15 \mu\text{s}$ to $+15 \mu\text{s}$
-------------------	--

---

System SC Phase	0 ns to 400 ns
-----------------	----------------

---

## Audio Performance

48 kHz

## Sampling Frequency

Quantization	24 bits
Frequency Response	20 Hz to 20 kHz +0.5/-1.0 dB (0 dB at 1 kHz)
Dynamic Range	More than 90 dB
Distortion	Less than 0.05% (at 1 kHz)
Headroom	20/18/16/12 dB (selectable)

## Other Equipment

Built-in Display	4.3-inch type color LCD monitor
Built-in Speaker	Monaural (x1)

## Supplied Accessories

Supplied Accessories	Operation manual (1) Installation manual (1) XDCAM Application Software CD-ROM (1)
----------------------	--

## Notes

[\*1] The values for dimensions are approximate.

Note

[\*2] Playback only.

[\*3] Optional PDBK-S1500 hardware key is required for DVCAM and MPEG IMX recording.

---

## Gallery

