

RCP-1000

Joystick type of simple Remote Control Panel for HDC/HSC/HXC series cameras. 6 units in 19-inch EIA rack.



Overview

The RCP-1000 is simple remote control panel with specialised basic operations. The iris and master black adjustment block employs a joystick type control. Up to six units can be mounted in a 19-inch EIA rack. Various settings can be configured according to the operation configuration and the frequency with which functions are used.

Features

Simple and compact.

This remote control panel is provided with the control functions required to perform the basic operations of cameras and enables the simple and accurate operation of various functions.

IRIS/MB (master black) display window.

The IRIS window displays the iris setting as an F number. If the lens is closed, "CLS" is displayed. The Master black display window displays the master black setting value.

Direct control filters and master gain buttons

Easily access ND/CC filters as well as master gain control

Customisable switch.

Customer can assign any function to a spare switch.

Compatible with a variety of control systems

HDC/HSC/BVP system camera users can build a multi-camera control system through the use of the CNU-700. In a system that uses CNU-700's, two CNU's can be used to control a camera system of up to 24 cameras.

A system that uses a LAN can also be built by connecting to a LAN-compatible CCU.

Specifications

General	
Power supply	DC 10.5 V to 30 V
Power consumption	2 W
Operating temperature	5°C to 40°C (41°F to 104°F)
Dimensions (W x H x D) (excluding protrusions)	68 × 244 × 123.7 mm (2 3/4 × 9 5/8 × 4 7/8 in)
Mass	1.1 kg (2 lb 9 oz)

Input/output connectors

CCU/CNU

Multi-connector 8-pin, female (x1)

EXT I/O

D-sub 9-pin, female (x1)

Information on EU Data Act: [Click here](#) to check if your Sony product and/or related service is subject to the EU Data Act.

Related products



HDCU-3100

IP enabled next generation Camera Control Unit



HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



MSU-3000

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



MSU-3500

Master setup unit, multi camera remote control panel for system cameras (vertical type)



HDC-3500V

2/3-type 4K 3-CMOS sensor portable system camera with pre-installed variable ND filter and HD 4x HFR capability



HDC-5500V

2/3-type 4K 3-CMOS sensor portable system camera with pre-installed variable ND filter and 4K 4x HFR capability

Gallery

