

## PWS-100PR1

### Production Control Workstation



#### Overview

#### **Provides live operational control of PWS-4400 in 4K and HD**

The PWS-100PR1 is a 1RU production control workstation to control the PWS-4400 4K/HD multi-port AV storage unit for live operation. It includes pre-installed PWA-PRC1 production control software and video input card required to support this operation. An optional touch-screen monitor can be provided to enhance the operational experience even further. The system provides a variety of screen variations, including split-screen mode, playlist mode, clip management mode and cut-out mode. With the PWS-4400, the unit provides full control of ground-breaking 4K and HD workflows to help you produce amazing live action and highlights content.

#### **Control of PWS-4400**

The PWS-100PR1 provides live operational control of the PWS-4400. It allows connection to the PWSK-4403 USB control device for live slow-motion operation and optional touch-screen monitor.

#### **Operation flexibility**

With the PWS-4400, the unit provides full control of ground-breaking 4K and HD workflows.

#### **Multi-port inputs/outputs**

The PWS-100PR1 is equipped with two graphic cards to monitor up to 6 inputs that are fed to the PWS-4400 (when using the PWS-4400 in HD operation). In addition, the PWS-100PR1 has six USB 3.0 ports allowing you to connect USB HDDs (Hard Disk Drives), as well as two RJ-45 (1000BASE-T, 100BASE-TX), one HDMI port and one DisplayPort connector V1.1a for display support.

## Features

### **Operational flexibility**

The PWS-100PR1 gives you operational flexibility for live production control, providing a variety of screen variations, including split-screen mode, playlist mode, clip management mode and cut-out mode.

### **Display operation and sub-monitor options**

The PWS-100PR1 works seamlessly with a touch-screen monitor. It is also possible to work without a monitor, using only a small LCD menu monitor attached to a PWSK-4403 controller. Providing further flexibility to the PWS-100PR1, up to two PWSK-4403 can be connected with two LCD monitors, in addition to a touch-screen monitor.

### **Fast boot up time**

The PWS-100PR1 takes less than one minute to boot up, allowing you to be operational as quickly as possible.

## Related products



### **PWS-4400**

4K / HD multi-port AV  
storage unit

## Gallery

