

VPL-HW45ES

Full HD SXRD Home Cinema Projector with 1,800 lumens brightness (colour availability may vary by country)



Overview

The value-packed introduction to true Home Cinema

Expand your horizons beyond the TV screen - and create a spectacular cinematic experience in your own home. Available in a choice of black or white finishes to flatter any interior, the value-packed VPL-HW45ES Home Cinema projector lets you enjoy your favourite entertainment at its best in 2D or 3D.

Made for movie lovers, it's packed with technology developed for our professional Digital Cinema projectors, including SXRD panels and our own Advanced Reality Creation upscaling technology for fabulously detailed Full HD images. Generous 1,800 lumens brightness ensures that films and TV shows look clear and sharp, even in daylight living rooms.

Compact and easy to set up, the VPL-HW45ES fits neatly into any home theatre or living room, with quiet fan noise that won't disturb the show and a front-facing exhaust port for extra installation flexibility. The projector's long-lasting lamp is rated for an extra-generous 6,000 hours operation, for fewer interruptions and reduced maintenance costs.

Colour availability may vary by country

Features

Spectacular Full HD pictures with Reality Creation

Cinema-quality SXRD panel technology is teamed with Reality Creation - Sony's Super Resolution processing that refines subtle details, colours and textures. You'll see the difference with crisp, sharp Full HD pictures that take you closer than ever to the original 1080p source.

1,800 lumens brightness for vibrant images

With an impressive 1,800 lumens brightness, Full HD images stand out with clear, bright highlights - even in well-lit rooms.

Choice of white or black colour finish

The VPL-HW45ES is available in a choice of sleek white or black finishes: take your pick to suit any contemporary or traditional décor.

Smooth, fluid on-screen action

Coupled with the panel's super-fast response rate, Motionflow technology means you'll see every detail with minimal blur - no matter how fast the action.

Long-lasting lamp

6000 hour rated lamp operating life means simpler maintenance, with fewer lamp swaps and reduced running costs.

Flexible home installation with wide zoom and shift lens

The manual zoom lens with a 1.6x zoom ratio and wide lens shift range gives greater installation flexibility in any room size, even with high ceilings.

Front-facing fan

With the fan exhaust positioned at the front of the projector, you don't need to worry about wall clearance and room for air intake/exhaust when installing. This helps maximise throw distance, for the biggest possible projected images.

Home automation with IP control

The VPL-HW45ES is compatible with a wide range of home automation systems via RS-232C/D-sub 9-pin and IR IN interfaces.

Industry standard RF 3D compatible

The projector's built-in RF transmitter synchronises with any RF 3D glasses for wider coverage and greater stability, so there's no need for an external transmitter.

USB updates

You're always up to date with the latest features and firmware updates via the projector's USB port.

Specifications

Display System

Display System	SXRD panel, projection system
----------------	-------------------------------

Display device

Size of effective display area	0.61" x 3
--------------------------------	-----------

Number of pixels	6,220,800 (1920 x 1080 x 3) pixels
------------------	------------------------------------

Projection lens

Focus	Manual
-------	--------

Zoom	Manual (Approx. x1.6)
------	-----------------------

Lens shift	Manual, Vertical: +/- 71%, Horizontal: +/- 25%
------------	--

Light source

Light source	High-pressure mercury lamp, 215 W type
--------------	--

Recommended lamp replacement time *1

Recommended lamp replacement time	6000 H (Lamp mode: Low)
-----------------------------------	-------------------------

Filter replacement cycle (Max.)

Filter replacement cycle (Max.)	Same time as the lamp replacement is recommended
---------------------------------	--

Screen size

Screen size	40" to 300" (1,016 mm to 7,624 mm)
-------------	------------------------------------

Light output

Light output	1800 lm (Lamp mode: High) *2
--------------	------------------------------

Colour light output

Colour light output	1800 lm (Lamp mode: High) *2
---------------------	------------------------------

Displayable scanning frequency

Horizontal	19 kHz to 72 kHz
------------	------------------

Vertical	48 Hz to 92 Hz
----------	----------------

Display resolution

Computer signal input	Maximum display resolution: 1920 x 1080 dots (HDMI Input only)
-----------------------	--

Video signal input	480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i The following items are available for HDMI input only. 1080/60p, 1080/50p, 1080/24p
--------------------	--

OSD languages

OSD languages	17-languages (English, Dutch, French, Italian, German, Spanish, Portuguese, Russian, Swedish, Norwegian, Japanese, Simplified Chinese, Traditional Chinese, Korean, Thai, Arabic, Polish)
---------------	---

INPUT OUTPUT (Computer / Video / Control)

HDMI1 / HDMI2	Digital (RGB/Y Pb/Cb Pr/Cr)
---------------	-----------------------------

Remote	RS-232C, D-sub 9-pin (female)
--------	-------------------------------

IR IN	Mini Jack
-------	-----------

USB	DC 5V, Max. 500 mA
-----	--------------------

Acoustic noise

Acoustic noise	22 dB
----------------	-------

Operating temperature / Operating humidity

Operating temperature / Operating humidity	5°C to 35°C (41°F to 95°F) / 35% to 85% (no condensation)
--	---

Storage temperature / Storage humidity

Storage temperature / Storage humidity	-20°C to +60°C (-4°F to +140°F) / 10% to 90% (no condensation)
---	---

Power requirements

Power requirements	AC 100 V to 240 V, 3.1 A to 1.3 A, 50/60 Hz
--------------------	---

Power consumption

Power consumption	Max 310 W
-------------------	-----------

Power consumption (Standby)

Power consumption (Standby)	0.4 W
-----------------------------	-------

Standby Mode Activated

Standby Mode Activated	After about 10 Minutes
------------------------	------------------------

Dimensions (W x H x D) (without protrusions)

Dimensions (W x H x D) (without protrusions)	407.4 x 179.2 x 463.9 mm 16 1/8 x 7 1/8 x 18 3/8 inches
---	--

Mass

Mass	Approx. 9 kg / 20 lb
------	----------------------

Supplied accessories

Supplied accessories	RM-PJ28 Remote Commander (1) Size AA (R6) Manganese Batteries (2) AC Power Cord (1) Lens Cap (1) Operating Instructions (CD-ROM) (1) Quick Reference Manual (1)
----------------------	--

Optional Accessories

3D Glasses	Please contact your Sony representative for specific models available in your region.
------------	--

Replacement lamp

Replacement lamp	LMP-H210
------------------	----------

*1

The figures are expected maintenance time and not guaranteed. They will depend on the environment or how the projector is used.

*2

The values are estimate.

Environmental notice for customers in the USA

Lamp in this product contains mercury. Disposal of these materials may be regulated due to environmental considerations. For disposal or recycling information, please contact your local authorities or see www.sony.com/mercury for additional information.

Information on EU Data Act: [Click here](#) to check if your Sony product and/or related service is subject to the EU Data Act.

Gallery

