

LKRL-Z511

2D Projection Lens (1.05:1 to 1.75:1)



Overview

1.05x - 1.75x Zoom Lens

Optional zoom lens for use with the SXR4 4K projector 1.05x to 1.75x zoom lens with memory feedback. This lens uses a feedback circuit that reports focus and zoom position to the projector. This allows the operator to preset and recall different lens settings from the projector function memories. This offers instant and automated screen sizing for video formats using different aspect ratios.

Specifications

General

Operating temperature	0°C to +40°C
-----------------------	--------------

Storage temperature	-20°C to +60°C
---------------------	----------------

Operating humidity	0% to 90% (without condensation)
--------------------	----------------------------------

Storage humidity	0% to 90% (without condensation)
------------------	----------------------------------

Dimensions(W/H/L)	Approx.256 x 315 x 429 mm(10 x 12.4 x 16.8 inches)
-------------------	----------------------------------------------------

Mass.

Approx. 14.5kg (31.9 lb)

Gallery

