

## MSU-1000

Master setup unit, multi camera remote control panel for HDC / HSC cameras (horizontal type)



### Overview

The MSU-1000 master setup unit is a control panel for camera configuration and maintenance. It is a horizontally-oriented device (as opposed to the MSU-1500, which has a compact, vertically oriented panel) and can control multiple camera systems, using either the CNU-700 Camera Command Network Unit, or using a LAN, in which case up to 96 cameras can be controlled.

**This product contains pre-installed software and requires the purchase of licence keys to activate some functions.**

### Features

#### **Large and flexible system configuration**

The MSU-1000 is part of a family of products that provides flexibility in the configuration of large and small camera control systems.

#### **Ethernet LAN capability**

The MSU-1000 supports inter-connectivity using an Ethernet LAN as well as a CNU-700

#### **Customisable Switch and menu**

MSU-1000 users can map any function to an assignable switch or menu item

## Specifications

### General

Power supply	AC 100 - 240 V. 50/60 Hz 0.35 A (Max.) DC 10.5 - 17 V 1.2 A (Max.)
Operating temperature	5 °C to 40 °C (41 °F to 104 °F)
Dimensions (W x H x D) (excluding protrusions)	482 × 222 × 67 mm (19 × 8 3/4 × 2 3/4 in.)
Mass	Approx. 4.6 kg (10 lb. 2 oz.)

### Input/output connectors

Ethernet	RJ-45 8-pin (X1)
CCU/CNU	Multi-connector 8-pin, female (x1)
AUX	Multi-connector 8-pin, female (x1)
EXT I/O	D-sub 50-pin, female (x1)
AC IN	3-pin (x1)
DC IN	4-pin (x1)

## Related products



## HDC-P43

4K/HD POV Camera



NETWORKED **LIVE**

## HDCU-3100

IP enabled next generation Camera Control Unit



## HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



NETWORKED **LIVE**

## HDC-5500

High performance three 2/3-inch 4K CMOS sensor portable system camera with direct 4K output



NETWORKED **LIVE**

## HDC-3500

Three 2/3-inch 4K CMOS sensors portable system camera for fibre operation



NETWORKED **LIVE**

## HDC-3100

Three 2/3-inch CMOS sensors portable system camera for fibre operation



NETWORKED **LIVE**

## HDC-3170

Three 2/3-inch CMOS sensors portable system camera for triax operation



## MSU-3000

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



## MSU-3500

Master setup unit, multi camera remote control panel for system cameras (vertical type)



NETWORKED **LIVE**

## HDC-P31

HD compact POV system camera with enhanced remote features and advanced HDR workflows



NETWORKED **LIVE**

## RCP-3500

Remote-control panel for HDC/HSC/HXC series cameras



NETWORKED **LIVE**

## RCP-3501

Remote-control panel for HDC/HSC/HXC series cameras



NETWORKED **LIVE**

## UHC-8300

UHC-8300 8K 3CMOS sensor Camera system includes UHCU-8300 8K Camera Control Unit, UKCU-8001 (8K ST 2110 Interface), UZCU-

SNMP80 (SNMP for 8K  
ST 2110), UKCU-IP01F  
(Networked Media  
Interface)

## Gallery

