

## PSS-650

Projector Ceiling Bracket for Installation



Overview

### Projector Ceiling Bracket for Installation

Specifications

#### Adjustable range

Up/down position	300~375mm / 11 13/16~14 3/4 inches 475~625 mm / 18 11/16~24 19/32 inches (with Supplied extension pole) (25mm pitch adjustment)
Horizontal angle of rotation	$\pm 10$ deg
Left/right tilt angle	$\pm 5$ deg (Fine adjustment function with adjustment knob)
Up/down tilt angle	$\pm 5$ deg (Fine adjustment function with adjustment knob)
Front/back position	$\pm 50$ mm / $\pm 1$ 31/32 inches (Fine adjustment function with

adjustment knob)

Left/right position

$\pm 25$  mm /  $\pm 31/32$  inch (Fine adjustment function with adjustment knob)

## Dimensions (W x H x D)

Dimensions (W x H x D)

299 x Height\* x 453.5 mm / 11 25/32 x H x 17 27/32 inches

\*Height: 300~375mm / 11 13/16~

14 3/4 inches

475~625mm / 18 11/16~24 19/32 inches (with Supplied extension pole)

## Dimensions (W x H x D) \*without protrusions (Adjustment knob)

Dimensions (W x H x D)

\*without protrusions (Adjustment knob)

246 x Height\* x 322 mm / 9 11/16 x H x 12 11/16 inches

\*Height : 300~375mm / 11 13/16 ~14 3/4 inches

475~625mm / 18 11/16~24 19/32 inches (with Supplied extension pole)

## Mass

Mass    Approx. 8.6 kg / 19 lb

---

## Maximum load

Maximum load                                  30 kg / 66 lb

---

## Optional accessories

Optional accessories                          PSS-650P

---

## Color

Color    Black

---

## Gallery

