

SNC-EP521

Standard Definition (PAL) PTZ
Network Camera



Overview

Stylish, easy to install network camera with powerful optical zoom

This stylishly designed PTZ (pan tilt zoom) camera is ideal for video monitoring of wide areas like shopping malls and airport concourses.

The SNC-EP521 captures crisp Standard Definition (PAL) images in a choice of three popular video coding standards to suit your needs and network conditions.

The autofocus lens with powerful 36x optical zoom range pulls distant subjects closer for detail-packed close-ups. Combined with digital zoom, maximum magnification ratio is an impressive 432x, helping identify far-away subjects even in the largest airport concourse.

Even high-contrast or backlit scenes aren't a problem with DynaView technology that can handle extremes of light and shade for a clearer view.

Images can be optionally recorded onto an on-board memory card for fail-safe data backup. The camera can be conveniently controlled from a smartphone or tablet, letting you view images remotely and adjust pan, tilt, and zoom.

The SNC-EP521 is easy to install, with HPoE (High Power over Ethernet) sharing power and data signals over the same cable to reduce infrastructure costs and labour.

Features

Detail-packed close-ups with 36x optical zoom

Easily find and track targets with powerful 36x optical zoom. Combined with 12x digital zoom it provides an impressive total zoom ratio of 432x.

Three codecs with dual streaming capability

Pick the video compression format that's appropriate for your application needs and network resources. JPEG is the best choice for capturing high-quality still images; MPEG-4 or H.264 provide clear video images over limited-bandwidth networks. Dual streaming allows two video streams to be sent independently – ideal for viewing live video while recording simultaneously onto a server.

Better pictures, day or night

True Day/Night function switches the camera between Day (colour) and Night (B/W) modes, boosting sensitivity to near-IR light to see images in conditions of near-darkness.

Effortlessly handle varied lighting conditions with DynaView

DynaView with Wide-D technology expands video dynamic range, improving visibility of images in scenes with high or poor contrast.

DEPA Intelligent Video Analytics

Sony's DEPA (Distributed Enhanced Processing Architecture) technology also transmits metadata – like object size and position – to a DEPA-enabled recorder. Image processing is performed by the camera, reducing the load on the recorder

compared with conventional analytic systems.

Simpler installation with H PoE

High Power over Ethernet (HPoE – IEEE802.3at) uses the same network cable for camera powering and data transfer, reducing physical infrastructure costs and allowing simpler, more rapid installation.

On-board recording

Images can be recorded directly to an optional SD memory card for fail-safe data backup.

View and control with your smartphone

Securely access the camera using a smartphone or tablet (Android or iOS) to view images remotely and control pan, tilt, and zoom functions. You don't even need to download a special app.

ONVIF compliance for compatibility and confidence

The SNC-EP521 conforms to ONVIF (Open Network Video Interface Forum) Profile S, the widely-accepted protocol for information exchange between network video devices. This gives extra confidence in the camera's breadth of compatibility with other devices.

Specifications

Camera

Image Sensor	1/4-type EXview HAD CCD sensor
Number of Effective Pixels	Approx. 0.44 Megapixels
Sync System	Internal synchronization

Minimum Illumination (50 IRE)	Color: 1.4 lx (F1.6, AGC On, 1/50 s, 50 IRE) B/W: 0.15 lx (F1.6, AGC On, 1/50 s, 50 IRE, Night Mode)
Minimum Illumination (30 IRE)	Color: 0.9 lx (F1.6, AGC On, 1/50 s, 30 IRE) B/W: 0.1 lx (F1.6, AGC On, 1/50 s, 30 IRE, Night Mode)
Dynamic Range	Theoretically 92 dB by DynaView Technology
S/N Ratio (Gain 0 dB)	50 dB (Gain 0 dB)
Gain	Auto/Manual (-3 to +28 dB)
Shutter Speed	1/1 s to 1/10,000 s
Exposure Control	Full auto, Shutter priority, Iris priority, Manual
White Balance	Auto, ATW, Indoor, Outdoor, One-push, Manual, Sodium vapour lamp
Lens	Auto-focus zoom lens
Powered Zoom	Yes
Zoom Ratio	Optical zoom 36x Digital zoom 12x

	Total zoom 432x
Powered Focus	Yes
Auto Focus	Yes
Horizontal Viewing Angle	57.8° to 1.7°
Vertical Viewing Angle	43.4° to 1.3°
Focal Length	f = 3.4 mm to 122.4 mm
F-Number	F1.6 (Wide) to F4.5 (Tele)
Minimum Object Distance	10 mm (Wide) to 1500 mm (Tele)
Pan/Tilt Angle (powered)	340 ° endless rotation/105 °
Pan Speed	300 °/s (max.)
Tilt Speed	300 °/s (max.)
Number of Preset Positions	256
Number of Tour Programs	5

Camera Features

Day/Night	True D/N
-----------	----------

Wide-D	Dyna View
Noise Reduction	NR
Image Stabilizer	Electronic
Privacy Masking (number)	24
Privacy Masking (shape)	Quadrangle
Privacy Masking (color/effect)	Opaque 14 colors (Black, White, Red, Green, Blue, Cyan, Yellow, Magenta, Gray (6 scales)), Mosaic
Edge Storage	Yes
Voice Alert	Yes
Superimpose Number	3 independent positions for characters (Codec, Date & Time, Event, Text (Max. 64 characters)), 1 independent position for a logo mark
Superimpose Language	English
	English, Japanese, Chinese (simplified), Chinese (traditional),

Menu Language	French, Spanish, German, Italian, Korean, Portuguese, Russian, Arabic, Hindi, Vietnamese, Thai, Turkish, Polish
---------------	-----------------------------------------------------------------------------------------------------------------

Smartphone viewer	Yes
-------------------	-----

Video

Resolution	720 x 576, 704 x 576, 640 x 480, 384 x 288, 320 x 240
------------	-------------------------------------------------------

Compression Format	H.264, MPEG-4, JPEG
--------------------	---------------------

Maximum Frame Rate	H.264: 25 fps (720x576)
	MPEG-4: 25 fps (720x576)
	JPEG: 25 fps (720x576)

Bitrate Control Mode	CBR/VBR (selectable)
----------------------	----------------------

Range of Bit Rate Setting	64 Kbps to 8 Mbps
---------------------------	-------------------

Adaptive Rate Control	H.264
-----------------------	-------

Bandwidth Control	JPEG
-------------------	------

Multi streaming Capability	Dual streaming *1
----------------------------	-------------------

Number of Clients	5
-------------------	---

Intelligent Video/Audio Analytics

Analytics Architecture	DEPA
------------------------	------

Intelligent Motion Detection	Yes
------------------------------	-----

Tamper Alarm	Yes
--------------	-----

Advanced Audio Detection	Yes
--------------------------	-----

Audio

Compression Format	G.711/G.726
--------------------	-------------

System Requirements

Operating System	Windows XP (32 bit) Professional Edition
	Windows Vista (32 bit) Ultimate, Business Edition
	Windows 7 (32/64 bit) Ultimate, Professional Edition

Processor	Intel Core2 Duo 1.8 GHz or higher Intel Pentium4 2.4GHz or higher
-----------	----------------------------------------------------------------------

Memory	1 GB or more
--------	--------------

	Microsoft Internet Explorer Ver. 6.0,
--	---------------------------------------

Web Browser	Ver. 7.0, Ver. 8.0 Firefox Ver. 3.5 (plug-in free viewer only) Safari Ver. 4.0 (plug-in free viewer only) Google Chrome Ver.4.0 (plug-in free viewer only)
-------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------

SNC toolbox	Yes
-------------	-----

SNC toolbox mobile	Yes
--------------------	-----

Network

Protocols	IPv4, IPv6, TCP, UDP, ARP, ICMP, IGMP, HTTP, HTTPS, FTP (client/server), SMTP, DHCP, DNS, NTP, RTP/RTCP, RTSP, SNMP(MIB-2)
-----------	----------------------------------------------------------------------------------------------------------------------------

Number of IP Address/Mac ADDRESS	1
----------------------------------	---

QoS	DSCP
-----	------

Multicast Streaming Support	Yes
-----------------------------	-----

ONVIF Conformance	Profile S
-------------------	-----------

Authentication	IEEE802.1X
----------------	------------

Interface

Microphone Input	Mini jack (monaural), MIC IN: 2.5 V DC plug-in power
------------------	------------------------------------------------------

Line Output	Mini jack (monaural) Maximum output level: 1 Vrms
-------------	---------------------------------------------------

Network Port	10BASE-T/100BASE-TX (RJ-45)
--------------	-----------------------------

Alarm Input (Sensor Input)	x2
----------------------------	----

Alarm Output	x1 (mechanical relay outputs electrically isolated from the camera)
--------------	---------------------------------------------------------------------

Card Slots	SD/SDHC x1
------------	------------

Confirmed SD Card Type	SDHC (Max. 32 GB)
------------------------	-------------------

General

Power Requirements	IEEE 802.3at compliant (PoE+) Class 4, AC 24 V
--------------------	------------------------------------------------

Power Consumption	Approx. 25 W
-------------------	--------------

Operating	-5°C to +50°C
-----------	---------------

Temperature	+23°F to +122°F
Cold Start Temperature	0 °C to +50°C +32°F to +122°F
Storage Temperature	-20 °C to + 60 °C -4 °F to + 140 °F
Operating Humidity	20 % to 80 %
Storage Humidity	20 % to 95 %
Dimensions *2	φ147.4 mm x 190.9 mm φ5 7/8 inches x 7 5/8 inches
Mass	Approx. 1.7 kg (including ceiling bracket) Approx. 3 lb 12 oz (including ceiling bracket)
External Material	Base cabinet: PC+ABS Camera cabinet: PC+ABS Side cabinet: PC+ABS
External Color	Base cabinet: 9.3G 8.5/0.2 Camera cabinet: 6.9PB 1.9/0.3 Camera cabinet: 6.9PB 1.9/0.3
	JATE Technical standard (LAN) UL2044, IEC60950-1(CB) VCCI (Class A), FCC(Class A), IC (Class A)

Safety Regulations	Emission: EN55022(Class A)+EN50130-4 Immunity: EN55022(Class A)+EN55024 Emission: AS/NZS CISPR22(Class A)
--------------------	-----------------------------------------------------------------------------------------------------------------

Supplied Accessories	Installation Manual (1) Ceiling bracket (1) Screws (2) Template (1) 24V AC connector (1) I/O connector (1) 3 years warranty booklet (1)
----------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------

Notes

*1	Dual streaming (Any combination with JPEG/MPEG-4/H.264, including multiple streams of the same format)
----	--------------------------------------------------------------------------------------------------------

*2	The values for dimensions are approximate.
----	--------------------------------------------

Related products



UNI-UMB1

Indoor wall mounting bracket for minidome and PTZ cameras



SNCA-POLE30

Mounting pipe for pendant mount applications



SNCA-WM40

Heavy duty outdoor wall mount for the SNC-RS84P, SNC-RS86P and SNC-RH164 rapid dome cameras



UNI-WMB3

Wall mount bracket for PTZ dome mount security camera housings



SNCA-CEILING

Mounting coupling for pendant applications



UNI-OPL7C3

Outdoor Pressurized dome camera housing



SNCA-HRX550EXT/W

Outdoor wireless dome camera housing

Gallery



