

## VPL-SW636C

3,300 lumens WXGA Ultra Short Throw interactive projector



### Overview

**Bright, high contrast widescreen projector for mid-size classrooms and meeting rooms: with easy installation, a wide range of enhanced interactivity functions and low ownership costs.**

The VPL-SW636C Ultra Short Throw projector is ideal for classroom or corporate use, with simple, flexible installation, low ownership costs, enhanced interactivity and easy connection to other devices.

Present big, bright images over 2m across with the projector as little as 47cm from the screen or whiteboard, with less distracting glare and shadows.

Advanced 3LCD BrightEra™ panel technology by Sony ensures high contrast, widescreen WXGA images with excellent colour stability. The projector's powerful 3,300 lumens colour light output ensures that presentations are always seen clearly, even in brightly-lit environments.

Seamless integration with school or office networks can be enhanced with an optional Wi-Fi module, letting students wirelessly share homework, images and graphics from PCs, smartphones and tablets. Learning's made richer and more collaborative with dual pen interactivity, allowing teacher and

pupil to write on screen simultaneously. In PC-free interactive mode, you don't even need a connected PC to write, draw and annotate on-screen presentations.

There's a wide range of smart energy-saving features built in. An extra-long lamp replacement time of up to 10,000 hours minimises costs and reduces downtime in busy classrooms and offices. A newly-designed wall mount bracket makes installation easier in rooms with low ceilings.

## Features

### **Bright, clear images with maximum 3,300 lumens colour light output**

The projector's high light output ensures that presentations are seen clearly in any classroom or meeting room. There's a choice of three brightness modes to suit any environment, from bright daylight to darkened rooms.

### **Ultra short throw distance**

Present images up to 80" across (2.03m diagonal) with the projector just 47cm from the screen or whiteboard. Distracting glare and shadows are greatly reduced, as well as saving space in a classroom or meeting room.

### **WXGA resolution for detail-packed presentations**

WXGA (1280 x 800) resolution gives lots of crisp, fine detail: perfect for making presentations direct from a laptop or PC.

### **3LCD BrightEra™ technology**

The projector's efficient 3LCD panel system is enhanced by advanced BrightEra™ technology by Sony. You'll see the difference with impressively bright, consistent, high resolution images and increased panel reliability.

### **Gamma adjustment**

A new gamma curve adjustment offers three settings for accurate

tonal reproduction with rich, vibrant colours and clear, easy-to-read text.

### **Up to 10,000 hours (in Low mode) long-lasting lamp for reduced maintenance and down time**

Present for longer without interruption, with reduced maintenance that contributes directly to lower lifetime ownership costs. Filter cleaning cycles are synchronised with lamp replacement, cutting scheduled maintenance visits even further.

### **Energy-saving features**

Advanced lamp technology enables a range of energy-saving features. Auto Light Dimming mode saves energy when the projector is left on without being used. During projection, Auto Picture Mode automatically adjusts light output to suit the scene being projected. Picture Mute dims the projected image when it's not needed to minimise energy consumption.

### **Wired or wireless network presentation**

Upgraded Network Presentation software (included) makes it easier than ever to deliver presentations from a networked PC or Mac with simple one-click connection. Up to four users can project PC/Mac images simultaneously, and up to eight users can connect to one projector. Add the optional IFU-WLM3 USB wireless LAN module and present wirelessly from your tablet or smartphone, using the VueMagic app from Pixelworks (see <https://www.vuemagic.com/?q=node/17>)

### **Remote control from iOS mobile devices**

Download free Projector Remote app for iOS and easily control projector features from anywhere in the room with your iPhone or iPad.

### **USB Media viewer**

Insert a USB drive and display photos, images or graphics with no PC needed.

## **USB display for easy one-cable PC connection**

Present pictures and audio\* from a connected PC or Mac with just one USB cable - you don't even need to install a software driver.

\* There may be a time lag between video and audio. For low-latency applications it is recommended to use projector's line-in or HDMI-in connection.

## **Dual-pen PC interactivity**

Teacher and pupil can write on screen simultaneously, or annotate images from an external source with mouse control and a wide range of drawing tools: two interactive pens and IPU2 PC software included.

## **PC-free interactivity**

Up to two people can sketch, draw, write and annotate on-screen presentations with no need for a connected computer. Now with richer drawing functions and Auto Pen Speed for even smoother drawing.

## **Whiteboard mode**

Instantly turn any projection surface into an interactive whiteboard. Make annotations on presentations or images from an external source such as a document camera. Save annotations as snapshots for instant recall.

## **Input label function**

It's easier to keep track of various sources with a new input label function that lets you see the name of connected PCs, cameras, BD/DVD players and other devices on screen.

## **Clear, rich audio from built-in speaker**

There's no need to add an extra audio system: enjoy rich, room-filling sound from the powerful 16W speaker.

## **Quick and easy to install**

Adjustable optical zoom and lens shift simplify speedy, fuss-free

installation in any classroom. Generous connections simplify hook-ups with PCs, DVD players, microphones and other AV devices.

## Easy wall mounting

Installation's even easier with a new wall mounting bracket design that gives extra flexibility in rooms with low ceilings.

## Specifications

### Display System

Display System	3 LCD system
----------------	--------------

### Display Device

Size of effective display area	0.59”(15 mm) x 3 BrightEra LCD Panel Aspect ratio 16:10
--------------------------------	--

Number of pixels	3,072,000 (1280x800 x 3) pixels
------------------	---------------------------------

### Projection lens

Focus	Manual
-------	--------

Zoom - Powered/Manual	Manual
-----------------------	--------

Zoom - Ratio	Approx. x1.03
--------------	---------------

Throw Ratio	0.27:1-0.27:1 (0.267:1-0.274:1)
-------------	---------------------------------

Lens shift - Fix	0.81V
------------------	-------

Lens shift - Powered/Manual	Manual
-----------------------------	--------

Lens shift - Range Vertical	+/-3.7%
-----------------------------	---------

Lens shift - Range Horizontal	+/-2.3%
-------------------------------	---------

## Light source

Type	Ultra high pressure mercury lamp
------	----------------------------------

Wattage	225W type
---------	-----------

## Recommended lamp replacement time \*3

Lamp mode: High	4000 H
-----------------	--------

Lamp mode: Standard	6000 H
---------------------	--------

Lamp mode: Low	10000 H
----------------	---------

## Filter cleaning / replacement cycle (Max.)

Filter cleaning / replacement cycle (Max.)	Same time as the lamp replacement is recommended
--	--

## Screen size

Screen size 65"-110" (measured diagonally)

---

## Light output \*1

Lamp mode: High 3300 lm

---

Lamp mode: Standard 2300 lm

---

Lamp mode: Low 1900 lm

---

## Color light output \*1

Lamp mode: High 3300 lm

---

Lamp mode: Standard 2300 lm

---

Lamp mode: Low 1900 lm

---

## Contrast ratio (full white / full black) \*2

Contrast ratio (full white / full black) \*2 3000:1

---

## Speaker

Speaker 16W (monaural)

---

## Displayable scanning frequency

Horizontal	15 kHz to 92 kHz
Vertical	48 Hz to 92 Hz

## Display resolution

Computer signal input	Maximum display resolution: 1600 x 1200 dots, fV:60Hz
Video signal input	480/60i, 480/60p, 575/50p, 720/60p, 720/50p, 1080/60i, 1080/50i, 1080/60p, 1080/50p

## Color system

Color system	NTSC3.58, PAL, SECAM, NTSC4.43, PAL-M, PAL-N, PAL-60
--------------	---

## Keystone correction (Max) \*4

Vertical	+4/-1 degrees
----------	---------------

## OSD language

27-language (English, French,  
German, Italian, Spanish,  
Portuguese, Japanese,



OSD language	Chinese(簡・繁) , Korean, Russian, Dutch, Norwegian, Swedish, Thai, Arabic, Turkish, Polish, Vietnamese, Farsi, Finnish, Indonesian, Hungary, Greek, Czech, Slovakia, Romania)
--------------	---

## INPUT OUTPUT (Computer/Video/Control)

INPUT A	RGB / Y PB PR input connector: Mini D-sub 15 pin female Audio input connector: Stereo mini jack
INPUT B	RGB input connector: Mini D-sub 15 pin female Audio input connector: Stereo mini jack
INPUT C	HDMI input connector: HDMI 19-pin, HDCP support, Audio input connector: HDMI audio support
S VIDEO IN	S Video input connector: Mini DIN 4-pin
VIDEO IN	Video input connector: Phono jack
OUTPUT	MONITOR output connector: Mini D-sub 15 pin female

OUTPUT	Audio output connector: Stereo mini
REMOTE	D-sub 9-pin male/RS232C
LAN	RJ-45, 10BASE-T/100BASE-TX
USB	Type-A
USB	Type-B
MICROPHONE IN	Microphone jack: Mini Jack

## Acoustic Noise \*5

Lamp mode: Low      28dB

## Operating temperature / Operating humidity

Operating temperature / Operating humidity      0°C to 40°C (32°F to 104°F) /20-80%(no condensation)

## Storage temperature / Storage humidity

Storage temperature / Storage humidity      -10 °C to +60°C (-4°F to +140°F) /20% to 80% (no condensation)

## Power requirements

Power requirements	AC 100 V to 240 V, 3.5 A to 1.6 A, 50 Hz / 60 Hz
--------------------	--

## Power consumption

AC 100 V to 120 V - Lamp mode: High	341 W
--	-------

AC 220 V to 240 V - Lamp mode: High	328 W
--	-------

## Power Consumption (Standby Mode)

AC 100 V to 120 V	0.5W (when "Standby mode" is set to "Low")
-------------------	--

AC 220 V to 240 V	0.5W (when "Standby mode" is set to "Low")
-------------------	--

## Power Consumption (Networked Standby Mode)

AC 100 V to 120 V	5.3W (LAN) / 5.9W (optional WLAN module) / 6.1W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")
-------------------	--

AC 220 V to 240 V	5.6W(LAN) / 6.2W (optional WLAN module) / 6.4W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")
-------------------	---

## Standby Mode / Networked Standby Mode Activated

Standby Mode / Networked Standby Mode Activated	Approx. 10 Minutes
---	--------------------

## Wireless Network(s) On/Off Switch

Wireless Network(s) On/Off Switch	Press the MENU button, then select [Connection/Power] 2) [WLAN Settings] 3) [WLAN Connection] 4) Select On or Off
--------------------------------------	---

## Heat dissipation

AC 100 V to 120 V	1163 BTU
AC 220 V to 240 V	1119 BTU

## Dimensions (W x H x D)

Dimensions (W x H x D)    Aprox. 372 × 138 × 382mm  
 (without protrusions)    (14 21/32 x 5 7/16 x 15 1/32 inches)

---

## Mass

Mass                                    Approx. 6.3 kg (14 lb)

---

## Supplied accessories

Supplied accessories                Remote commander: RM-PJ8  
    Size Battery  
    AC power cord  
    Operating Instructions (CD-ROM)  
    Quick Reference Manual  
    Safety Regulation  
    Warranty card  
    flyers (Warning)  
    flyers (WEEE)  
    flyers (EU Battery direction)  
    Application Software (CD-ROM):  
    PJS for Net. Presen x1, IPU2 x1  
    Interactive Pen (W/Batteries AAA):  
    IFU-PN250A (x1), IFU-PN250B (x1)  
    USB cable 5m

---

## Optional Accessories

Optional Lamp: LMP-E220

Optional Accessories      Ceiling Mount: PSS-645  
Other Accessories: IFU-WLM3  
(WLAN module)

---

## Notes

\*1      The values are estimate.

---

\*2      This value is average with lamp dimming.

---

\*3      The figures are approximate. They vary depending on the environment or how the projector is used. Jigyobu cannot guarantee them.

---

\*4      The picture quality may deteriorate when the V Keystone function is used for it is an electrical correction.

---

\*5      The figures are approximate. They vary depending on the environment or how the projector is used.

---

Environmental notice      Lamp in this product contains mercury. Disposal of these materials may be regulated due to environmental considerations. For

---

for customers in the  
USA

disposal or recycling information,  
please contact your local  
authorities or see  
[www.sony.com/mercury](http://www.sony.com/mercury) for  
additional information.

---

## Gallery

