

CAC-12

Adjustable camera microphone holder



Overview

Provides two-axis adjustment of microphone arm

Allows microphone direction to be adjusted. For attaching the ECM-647/678 or the C-74 condenser microphone to cameras and camcorders.

Multi camera compatible

Can be used with: DSR-250P/1, DSR-400PK, DSR0400PL, DSR-400WSPL, DXC-D55PH, DXC-D55PK, DXC-D55PL, DXC-WSPL, DXC-D55WSPH.

Features

Multi camera compatible

Can be used with these cameras: DSR-250P/1, DSR-400PK, DSR0400PL, DSR-400WSPL, DXC-D55PH, DXC-D55PK, DXC-D55PL, DXC-WSPL, DXC-D55WSPH.

Holds a variety of microphones

Includes rubber adapter for 19mm diameter microphones like the ECM-672 and C-74.

Related products



HXC-FB80

Three 2/3-inch
Exmor™ CMOS sensor
HD colour studio
camera

HDLA- 3501

Large Lens Adaptor

HDLA- 3505

Large Lens Adaptor

Gallery

