

## HXR-FMU128

128 GB flash memory recording unit



### Overview

The HXR-FMU128 Flash Memory Unit is an optional solid-state memory recorder designed for NEX-FS700E, NEX-FS700EK, NEX-FS100E, NEX-FS100EK, NEX-EA50E and HXR-NX5E camcorders, and attaches directly to the right side of the camera with ease. Hybrid recording functionality is possible by being able to record on both the HXR-FMU128 and Memory card at the same time. The unit also offers long recording times of up to 10 hours at the highest HD quality (28Mbps) and 11 hours at 24 Mbps

#### **Hybrid Recording**

The HXR-FMU128 is capable of simultaneous recording of HD and HD video footage, along with the combination of HD and SD, offering instant backup and fast NLE workflow coupled with flexibility of recording in the field.

#### **Simple Direct Attachment**

The HXR-FMU128 is designed exclusively for the HXR-NX5E camcorder, and attaches directly to the back of the camera with ease.

#### **Long Recording Time**

The memory unit offers approximately 10 hours of continuous HD recording in the highest 28 Mbps mode and 11 hours at 24 Mbps. This is particularly useful for corporate and event videographers looking at extended recording times.

## Specifications

### General

Capacity	128GB (Fat32)
Supported Operating Systems	Windows XP SP3 (64-bit Editions and Starter Edition are not supported) Windows Vista SP2 (Starter Edition is not supported) Windows 7 Mac OS X (v10.4 or Later)
Operating Temperature	0-40°C (3-104°F)
Inputs/Outputs	USB: USB 2.0 Mini-B (x1 Output)
Power Requirements	5V DC (Power Supplied by Camera)
Power Consumption	0.9W (Power Supplied by Camera)
Dimensions (WxHxD)	5.4 x 8.5 x 1.7cm (2.3 x 3.4 x 0.7 inches)
Weight	80 g (2 oz)

### Recording Durations

Linear PCM 2-Channel	PS (28 Mbps): 10 Hours, 0 Minutes
	FX (24Mbps): 11 Hours, 40 Minutes
	FH (17Mbps): 15 Hours, 30 Minutes

	HQ (9Mbps): 26 Hours, 10 Minutes LP (5Mbps): 41 Hours, 30 Minutes
Dolby Digital 2-Channel	PS (28 Mbps): 10 Hours, 35 Minutes FX (24Mbps): 12 Hours, 20 Minutes FH (17Mbps): 16 Hours, 20 Minutes HQ (9Mbps): 29 Hours, 50 Minutes LP (5Mbps): 51 Hours, 20 Minutes
Standard Definition	HQ Mode: 32 Hours, 40 minutes

## Gallery

