

## RM-C950

Remote Control Unit For Colour Video Cam



### Overview

Full remote control of the DXC-9000/950/ H10/390/990 camera functions and lens zoom/ focus/iris functions via RS-232C. Facilitated operation with knob control of gain, detail, master pedestal, red and blue gain functions. Power is supplied through the DXC-9000/ 950/990 connected to the CMA-D2 Camera Adaptor or CCU-M5 Remote Control Unit. Power is supplied through the DXC-H10 connected to the CMA-H10 Camera Adaptor

### Specifications

#### Generic Specifications

Power requirements:	DC 12 V (supplied from DXC-9000/950 connected to CMA-D2 or CCU-M5)
---------------------	--

Operating temperature:	-5 to 45°C (23 to 113°F)
------------------------	--------------------------

Connectors:	CAMERA (8-pin)
-------------	----------------

Mass:	212 (W) x 41 (H) x 132 (D) mm
-------	-------------------------------

	212 (W) x 41 (H) x 132 (D) mm (8 3/8)
--	---------------------------------------

Dimensions: x 1 5/8 x 5 1/4 inches) (excluding projecting parts and controls)

---

## Supplied Accessories

Connection cable (3  
m) (1) Operation  
manual (1)

---

## Gallery

