

# MDR-M1

New reference closed monitor headphones for creators with ultra-wideband playback.



## Specifications

| General                 |                                                                                                                                                 |
|-------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| Type                    | Closed dynamic                                                                                                                                  |
| Driver Unit             | 40 mm (1.58 in)                                                                                                                                 |
| Power Handling Capacity | 1,500 mW (IEC *1)                                                                                                                               |
| Impedance               | 50 Ω at 1kHz                                                                                                                                    |
| Sensitivity             | 102 dB/mW                                                                                                                                       |
| Frequency Response      | 5 Hz - 80,000 Hz (JEITA)                                                                                                                        |
| Mass                    | Approx. 216 g (without cable)                                                                                                                   |
| Included Items          | Headphones cable (approx. 1.2m/2.5 m, Stereo mini plug); Plug adaptor (Stereo standard plug - Stereo mini plug); Warranty card; Reference Guide |
| Notes                   |                                                                                                                                                 |
| *1                      | IEC International Electrotechnical Commission                                                                                                   |

## Related products




### MDR-MV1

Open back Studio Monitor Headphones for creating spatial and stereo sound with wide frequency range and soundstage feel



### MDR-7506

Stereo professional headphones



---

© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.

Export PDF : October 12 2026