

HDVVF-C35W



Specifications

General	
Power supply	10.5 to 17.0 V DC (supplied by the camera)
Power consumption	
Operating temperature	-20 °C to +45 °C (-4 °F to +113 °F)
Storage temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Mass	
Performance	
Brightness	
Resolution	500 or more lines
Supported formats	
Colour temperature	
Indicators	
Y	
Connector	
Camera connector	Round type 20-pin
Supplied Accessories	
Operation manual (1)	

